



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2020 (205) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought

TE Part #45219-2
DAHT AMP CLOSED END SPLICES 22-10 ASSY


TE Part #171505-1
PIDG RING UL.CSA(22-18)

TE Part #499786-9
040 UNIV HDR RA 4S 15DP STD L1

TE Part #1375963-3
PC104 CON NONSTKTRU NO STND LF



TE Part #1461078-5
OJ-SS-112HMF,000




TE Part #8-2176307-9
RP 1E 0.1W 102K 0.1% 25PPM 5K RL



TE Part #2315539-1
COVER, LIGHT CONTROLLER, 81MM DIA., 62MM



TE Part #4-1419145-0
OUAZ-SH-105L,900



TE Part #745779-5
HD SQZ TO RELEASE KIT



TE Part #4-1393766-1
R10-E1Y2-V2.5K=R10

Documents

Product Drawings

06P SL156 HSG W/LCK RAMP

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_770707-6_P_c-770707-6-p.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_770707-6_P_c-770707-6-p.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_770707-6_P_c-770707-6-p.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Application Specification

Japanese

Application Specification

English

MTA 156 Ribbon Cable Connector Assemblies (English And Spanish)

English



MTA 156 Ribbon Cable Connector Assemblies (English And Spanish)

Japanese

Agency Approvals

UL Report

English