




**Part Number :** [1200900032](#)  
**Product Description :** Nano-Change (M8)  
Receptacle, 4 Poles, A-Coded, M8 x 0.5  
Mounting Threads, Male (Straight) to 24 AWG  
Leads, 0.30m (11.81") Length  
**Series Number :** 120090  
**Status :** Active  
**Product Category :** Circular Industrial  
Connectors  
**Engineering Number :** 4R4P06A27C300




Documents & Resources

Drawings  
[1200900032\\_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead; Triphenyl-phosphate; Lead monoxide per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## EU RoHS Certificate of Compliance

---

### Part Details

#### General

Status	Active
Category	Circular Industrial Connectors
Series	120090
Description	Nano-Change (M8) Receptacle, 4 Poles, A-Coded, M8 x 0.5 Mounting Threads, Male (Straight) to 24 AWG Leads, 0.30m (11.81") Length
IP Rating	IP67
NEMA Rating	NEMA 6
Product Name	Nano-Change (M8)
Type	Single Ended (pigtail)
UPC	78678833057

#### Agency

CSA	LR6837
UL	E46237

#### Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	60V AC / 75V DC

#### Physical

Coupling Type	External Thread
Gender	Male
Keyway	A-Coded
Length	0.30m
Material - Component	Nickel-plated Brass
Mounting Thread Size	M8 x 0.5
Net Weight	95.400/g

Orientation	Straight
Panel Mount	Front
Poles	4
Temperature Range - Operating	-20° to +105°C
Wire/Cable Type	UL 1569
Wire Size (AWG)	24

---

This document was generated on Mar 27, 2025