

## FEATURES

- Contact rating 20A 125-250Vac
- Rugged cast iron housing for strength and durability
- Anti-skid base for stability
- Available in single and twin versions
- Twin version (116-928) has a divider bar
- Ingress protection rating IP20
- Fixing holes for floor or equipment mounting

## RS PRO Medium Duty Momentary Clipper Foot Switch - Cast Iron Case Material, SP-CO, 20 A @ 250 V ac Contact Current

RS Stock No.: 116-928



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description ATTRIBUTE 1

RS PRO foot switch is manufactured from robust cast iron and has SPDT contacts. This foot controller pedal is black in colour and designed with an ergonomic shape. It can be mounted securely to the floor or on equipment for extra protection. This foot switch is ideal for medium duty electrical devices which includes material handling and operating communication equipment.

This range includes:

116-928- Momentary SPDT, Twin

116-732 - Maintained SPDT, Single

## General Specifications

<b>Contact Configuration</b>	SP-CO
<b>Switch Operation</b>	Momentary
<b>Case Material</b>	Cast Iron
<b>Switch Environment</b>	Medium Duty
<b>Colour</b>	Black
<b>Applications</b>	Foot switches are commonly used in applications where hands-free control is more practical or safer. They can be found on: Industrial machinery and smaller power tools, Hospital beds, Dentist Chairs, Lamps
<b>Cable Connection</b>	Adjustable strain relief connector

## Electrical Specifications

<b>Contact Voltage Rating (AC)</b>	250V
<b>Contact Current Rating</b>	20A @ 250V ac

## Mechanical Specifications

Length	115.42mm
Height	47.6mm
Dimensions	115.42mm x 212.75mm x 47.6mm
Width	212.75mm
Weight	2.2kg

## Protection Category

IP Rating	IP20
-----------	------

## Approvals

Standards Met	EN 60529
Compliance/Certifications	CE, RoHS





**Size**

(See below)

