

Hedge Trimmer LXT®

DUH502

18V • 500 mm

Model DUH502 is brushless trimmer powered by an 18V Li-ion battery.

A cordless hedge trimmer with a brushless motor and a 500 mm special coated two cutting blade for gardening. Two-handed safety switches offer added safety and the tool has low noise levels. Three speed settings to suit different applications.



Technical specifications

Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Strokes per Minute (SPM)	2000 / 3600 / 4400 min ⁻¹
Length Of Blade	500 mm
Max blade opening	21,5 mm
Tooth Spacing	35 mm
Sound Power Level (L _{WA})	87 dB(A)
Sound Pressure Level (L _{pA})	79 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Vibration Level, Hedge Trimming	2,5 / ≤ 2,5 m/s ²
Vibration Uncertainty (K Factor), Hedge Trimming	1,5 m/s ²
Product Dimensions (L x W x H):	1016 x 192 x 225 mm
Tool weight with battery	3,8 - 4,1 kg
Product net weight	3,5 kg

User benefits

- Brushless maintenance-free and long-life motor
- Specially coated two-way cutting blade with long service life.
- Electric brake for maximum productivity and increased operator safety
- Double action switch for increased safety
- Rear handle swivels on both sides
- Variable speed
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Battery protection circuit protects against overloading, over-discharging and over-heating

Link to product - www.makita.uk.com



Related products

■ Optional AC

459120-1

Blade Cover 500 Mm



■ Other

User manual

Parts drawing