



Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Type: **PCB Mount Receptacle**

PCB Mount Orientation: **Right Angle**

Connector System: **Board-to-Board**

Number of Positions: **80**

Number of Rows: **2**

Features

Product Type Features

Connector Shape	Rectangular
PCB Connector Type	PCB Mount Receptacle
Connector System	Board-to-Board
Header Type	Fully Shrouded
Connector & Contact Terminates To	Printed Circuit Board
Connector Product Type	Connector Assembly

Configuration Features

Number of Columns	40
Connector Contact Load Condition	Fully Loaded
Number of Loaded Positions	80
Board-to-Board Configuration	Perpendicular
PCB Mount Orientation	Right Angle
Number of Positions	80
Number of Rows	2



Electrical Characteristics

Insulation Resistance	100 MΩ
Dielectric Withstanding Voltage (Max)	500 Vrms

Body Features

Primary Product Color	Black
-----------------------	-------

Contact Features

PCB Contact Termination Area Plating Material Thickness	4 – 6 μm[157.48 – 236.22 μin]
Contact Layout	Matrix
Contact Base Material	Copper Alloy
PCB Contact Termination Area Plating Material	Tin
Contact Mating Area Plating Material	Gold (Au)
Contact Type	Socket

Termination Features

Termination Method to PCB	Surface Mount
---------------------------	---------------

Mechanical Attachment

Mating Alignment Type	Polarization
PCB Mount Alignment Type	Pegs
Mounting Alignment Feature Length	.7 mm[.027 in]
PCB Mount Retention	With
PCB Mount Alignment	With
Connector Mounting Type	Board Mount
Mating Alignment	With

Housing Features

Housing Material	LCP
Mating Entry Location	Side
Centerline (Pitch)	.8 mm[.031 in]

Usage Conditions

Operating Temperature (Max)	125 °C[257 °F]
Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards



UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Tape & Reel
------------------	-------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts


TE Part # 294141-E
DRCQ 0,80 80 M 2 SMD M1 137 E009
176 GU-

TE Part # 294153-E
DRCQ 0,80 80 M 2 SMD M2 137 E009
176 GU-

Also in the Series | ERNI MicroCon



Board-to-Board Headers & Receptacles(44)



PCB Headers & Receptacles(44)



Rectangular Power Connectors(44)


Customers Also Bought



TE Part #294290-E
DRCB 0,80 80 M SMD * 137 E009 196 GURT *




TE Part #294646-E
SRCP 2,54 2 M 1 SMD 137 E1 166 * GU-H *



TE Part #254700-E
SRCA 2,54 6 M 1 SMD 137 E1 166 * GURT *



TE Part #284658-E
SRCP 2,54 3 M 1 SMD 137 E1 167 * GU-H *



TE Part #294648-E
SRCP 2,54 2 M 1 SMD 137 E1 168 * GU-H *



TE Part #294651-E
SRCP 2,54 8 M 1 SMD 137 E1 167 * GU-H *



TE Part #234712-E
STVR 96 MI ABC WV 4-00 EE 6,0 * 247 E00



TE Part #284659-E
SRCP 2,54 3 M 1 SMD 137 E1 168 * GU-H *



TE Part #5-147377-2
20 SYS50 SMT HDR DR SHD SN



TE Part #3-644894-3
03P CST100 SHRD HDR ASSY LF

Documents

Product Drawings

DRCQ 0,80 80 F * SMD * 137 E009 094 GURT

German

CAD Files

Customer View Model

ENG_CVM_CVM_294259-E_1.3d_igs.zip

English

Customer View Model



[ENG_CVM_CVM_294259-E_1.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_CVM_294259-E_1.2d_dxf.zip](#)

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

ERNI MicroCon Connector

English

ERNI MicroCon 0.8 mm Connectors

German

ERNI MicroCon 0.8 mm Connectors

English