

Material - Plating Mating Material - Plating Termination

## This document was generated on 01/19/2015 PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

| Part Number:                                   | 43045-0421             |  | $\sim$  |  |
|--|------------------------|--|---|--|
| Status:  | Active                 |  |   |  |
| Overview: Micro-Fit 3.0 <sup>™</sup> Connector |                        | S  |   |  |
| Description:                                   |                        | urface Mount Compatible, Dual Row, Right Angle, with Press-  |   |  |
|  |                        | Circuits, Tin (Sn) Plating, Glow Wire Compatible   |   |  |
|  |                        |  |   |  |
| Documents:                                     |                        |  |   |  |
| <u>3D Model</u>                                |                        | Test Summary TS-43045-001 (PDF)  |   |  |
| Drawing (PDF)                                  |                        | RoHS Certificate of Compliance (PDF)   |   |  |
| Product Specification                          | <u> PS-43045 (PDF)</u> | Product Literature (PDF)   | Series Series   |  |
|  |                        |  | image - Reference only                                |  |
| Agency Certification                           |                        |  |   |  |
| CSA  |                        | LR19980  | EU RoHS China RoHS                                    |  |
| TUV  |                        | R72081037  | ELV and RoHS  |  |
| UL   |                        | E29179   | Compliant   |  |
| Gonoral  |                        |  | REACH SVHC  |  |
| General<br>Breduct Femily                      |                        | DCD Headers  | Not Reviewed  |  |
| Product Family<br>Series                       |                        | PCB Headers<br>43045   | Low-Halogen Status                                    |  |
| Application                                    |                        | 43045<br>Power, Wire-to-Board  |   |  |
| Comments                                       |                        | "High Temperature/Square Pin/Solder Type <p><p>This</p></p>  | Need more information on product                      |  |
| Commento                                       |                        | Molex product is manufactured from material that has   | environmental compliance?                             |  |
|  |                        | the following ratings, tested by independent agencies:.  | Email productcompliance@molex.com                     |  |
|  |                        | a) A Glow Wire Ignition Temperature (GWIT) of at   | For a multiple part number RoHS Certificate of        |  |
|  |                        | least 775 deg C per IEC 60695-2-13. b) A Glow  | Compliance, click here                                |  |
|  |                        | Wire Flammability Index (GWFI) above 850 deg C   |   |  |
|  |                        | per IEC 60695-2-12.and hence complies with the   | Please visit the <u>Contact Us</u> section for any    |  |
|  |                        | requirements set out in the International Standard IEC   | non-product compliance questions.                     |  |
|  |                        | 60335-1 5th edition - household and similar electrical   |   |  |
|  |                        | appliances - safety, section 30 Resistance to heat   |   |  |
|  |                        | and fire. <p><p> The customers using this product<br/>must determine its suitability for use in their particular</p></p> | Search Parts in this Series                           |  |
|  |                        | application through testing or other acceptable means  | 43045Series   |  |
|  |                        | as described in end-product glow-wire flammability test  |   |  |
|  |                        | standard IEC 60695-2-11 and any applicable product   | Motoo With  |  |
|  |                        | end-use standard(s). <p> If it is determined during</p>  | Mates With<br>43025 Micro-Fit 3.0™ Receptacle Housing |  |
|  |                        | the customer's evaluation of suitability, that higher  |   |  |
|  |                        | performance is required, please contact Molex for  |   |  |
|  |                        | possible product options."   |   |  |
| Overview                                       |                        | Micro-Fit 3.0 <sup>™</sup> Connectors  |   |  |
| Product Literature Or                          | der No                 | 987650-5984<br>Micco Ett 8 0 0 M   |   |  |
| Product Name                                   |                        | Micro-Fit 3.0™   |   |  |
| UPC  |                        | 800753813069   |   |  |
| Physical                                       |                        |  |   |  |
| Breakaway                                      |                        | No   |   |  |
| Circuits (Loaded)                              |                        | 4  |   |  |
| Circuits (maximum)                             |                        | 4  |   |  |
| Color - Resin                                  |                        | Black  |   |  |
| Durability (mating cycles max)                 |                        | 30   |   |  |
| Flammability                                   |                        | 94V-0  |   |  |
| Glow-Wire Compliant                            |                        | Yes  |   |  |
| Mated Height                                   |                        | 10.06mm  |   |  |
| Material - Metal                               | ting                   | Brass  |   |  |

Tin Tin

| Material - Resin<br>Net Weight<br>Number of Rows<br>Orientation<br>PCB Locator<br>PCB Retention<br>PCB Thickness - Recommended<br>Packaging Type<br>Pitch - Mating Interface<br>Plating min - Mating<br>Polarized to PCB<br>Shrouded<br>Stackable<br>Surface Mount Compatible (SMC)<br>Temperature Range - Operating<br>Termination Interface: Style | High Temperature Thermoplastic<br>0.914/g<br>2<br>Right Angle<br>Yes<br>Yes<br>1.60mm<br>Tray<br>3.00mm<br>0.254µm<br>Yes<br>Fully<br>No<br>Yes<br>-40°C to +105°C<br>Through Hole |  |  |
|--|--|--|--|
| <b>Electrical</b><br>Current - Maximum per Contact<br>Voltage - Maximum  | 5A<br>600V   |  |  |
| <b>Solder Process Data</b><br>Duration at Max. Process Temperature (seconds)<br>Lead-free Process Capability<br>Max. Cycles at Max. Process Temperature<br>Process Temperature max. C  | 30<br>SMC & Wave Capable (TH only)<br>3<br>260   |  |  |
| Material Info  |  |  |  |
| <b>Reference - Drawing Numbers</b><br>Product Specification<br>Sales Drawing<br>Test Summary   | PS-43045, RPS-43045-003, RPS-43045-004<br>SD-43045-008<br>TS-43045-001   |  |  |

This document was generated on 01/19/2015 PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION