

Eaton 230255

Catalog Number: 230255

Eaton Moeller® series DILEM Auxiliary contact module, 2 pole, 1 N/O, 1 NC, Front fixing, Spring-loaded terminals, DILE(E)M...-C

General specifications



Product Name	Catalog Number
Eaton Moeller® series DILEM Accessory 230255	
Auxiliary contact module	EAN
	4015082302559
Product Length/Depth	Product Height
39 mm	37 mm
Product Width	Product Weight
45 mm	0.032 kg

Certifications

CSA Class No.: 3211-03
VDE 0660
IEC/EN 60947-4-1
CE
CSA-C22.2 No. 14-05
UL 508
CSA
IEC/EN 60947
UL File No.: E29184
CSA File No.: 012528
UL Category Control No.: NKCR
UL

Features & Functions

Electric connection type

Spring clamp connection

Features

Interlocked opposing contacts within an auxiliary contact module (according to IEC 60947-5-1 Annex L)

Fitted with:

Interlocked opposing contacts

Functions

For standard applications

Number of poles

Two-pole

General

Lifespan, mechanical

200,000 Operations (at 240 V, AC-15)

20,000,000 Operations (DC operated)

10,000,000 Operations (AC operated)

150,000 Operations (at 240 V, DC, L/R = 50 ms: 2 contacts in series 0.5 A)

Model

Top mounting

Mounting method

Front fastening

Mounting position

As required (except vertical with terminals A1/A2 at the bottom)

Operating frequency

9000 Operations/h

Overvoltage category

III

Pollution degree

3

Protection

Finger and back-of-hand proof, Protection against direct contact when actuated from front (EN 50274)

Rated impulse withstand voltage (Uimp)

6000 V AC

Shock resistance

10 g, N/O contact, Mechanical, according to IEC/EN 60068-2-27, Half-sinusoidal shock 10 ms

8 g, N/C contact, Mechanical, according to IEC/EN 60068-2-27, Half-sinusoidal shock 10 ms

Climatic environmental conditions

Ambient operating temperature - min

-25 °C

Ambient operating temperature - max

50 °C

Ambient operating temperature (enclosed) - min

-25 °C

Terminal capacities

Terminal capacity (flexible with ferrule)

2 x (1 - 2.5) mm²

1 x (1 - 2.5) mm²

Terminal capacity (solid)

1 x (1 - 2.5) mm²

2 x (1 - 2.5) mm²

Terminal capacity (solid/stranded AWG)

Ambient operating temperature (enclosed) - max

40 °C

Ambient storage temperature - min

-40 °C

Ambient storage temperature - max

80 °C

Climatic proofing

Damp heat, cyclic, to IEC 60068-2-30

Damp heat, constant, to IEC 60068-2-78

Single 16 – 14, double 16 – 14

Screwdriver size

0.6 x 3.5 mm, Spring-loaded terminals

Electrical rating

Rated operational voltage (Ue) at AC - max

600 V

Rated insulation voltage (Ui)

690 V

Rated operational current (Ie)

2.5 A at 24 V, DC L/R \leq 15 ms (with 1 contact in series)

2.5 A at 60 V, DC L/R \leq 15 ms (with 2 contacts in series)

1.5 A at 110 V, DC L/R \leq 15 ms (with 3 contacts in series)

0.5 A at 220 V, DC L/R \leq 15 ms (with 3 contacts in series)

Rated operational current (Ie) at AC-15, 220 V, 230 V, 240 V

4 A

Rated operational current (Ie) at AC-15, 380 V, 400 V, 415 V

2 A

Rated operational current (Ie) at AC-15, 500 V

1.5 A

Safe isolation

300 V AC, Between auxiliary contacts, According to EN 61140

300 V AC, Between coil and auxiliary contacts, According to EN 61140

Short-circuit rating

Short-circuit protection rating

10 A fast, 500V, Maximum fuse, Short-circuit rating without welding, Contacts

Short-circuit protection rating without welding

6 A gG/gL, 500 V, Max. Fuse, Contacts

Conventional thermal current Ith

Conventional thermal current Ith of auxiliary contacts (1-pole, open)

10 A

Switching capacity

Switching capacity (auxiliary contacts, general use)

10 A, 600 V AC, (UL/CSA)

0.5 A, 250 V DC, (UL/CSA)

Switching capacity (auxiliary contacts, pilot duty)

A600, AC operated (UL/CSA)

P300, DC operated (UL/CSA)

Contacts

Control circuit reliability

$< 2 \lambda$, < 1 failure at 100,000,000 Operations (at $U_e = 24$ V DC, $U_{min} = 17$ V, $I_{min} = 5.4$ mA)

Number of contacts (change-over contacts)

0

Number of contacts (normally closed contacts)

1

Number of contacts (normally open contacts)

1

Design verification

Equipment heat dissipation, current-dependent P_{vid}

0 W

Heat dissipation capacity P_{diss}

0 W

Heat dissipation per pole, current-dependent P_{vid}

0.24 W

Rated operational current for specified heat dissipation (I_n)

4 A

Static heat dissipation, non-current-dependent P_{vs}

0 W

10.2.2 Corrosion resistance

Meets the product standard's requirements.

10.2.3.1 Verification of thermal stability of enclosures

Meets the product standard's requirements.

10.2.3.2 Verification of resistance of insulating materials to normal heat

Meets the product standard's requirements.

10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects

Meets the product standard's requirements.

10.2.4 Resistance to ultra-violet (UV) radiation

Meets the product standard's requirements.

10.2.5 Lifting

Does not apply, since the entire switchgear needs to be evaluated.

Resources

Catalogs

Product Range Catalog Switching and protecting motors

Switching and protecting motors - catalog

[eaton-product-overview-for-machinery-catalogue-ca08103003zen-en-us.pdf](#)

Characteristic curve

[eaton-contactors-short-time-loading-dilm-characteristic-curve.eps](#)

Declarations of conformity

[DA-DC-00004747.pdf](#)

[DA-DC-00004764.pdf](#)

Drawings

[eaton-contactors-dimensions-210x002.eps](#)

[eaton-contactors-module-dile-accessory-3d-drawing.eps](#)

eCAD model

[ETN.230255.edz](#)

Installation instructions

[IL03407009Z](#)

mCAD model

[DA-CD-hs_dile_c](#)

[DA-CS-hs_dile_c](#)

Wiring diagrams

[eaton-contactors-contact-sdainl-combination-wiring-diagram.eps](#)

10.2.6 Mechanical impact

Does not apply, since the entire switchgear needs to be evaluated.

10.2.7 Inscriptions

Meets the product standard's requirements.

10.3 Degree of protection of assemblies

Does not apply, since the entire switchgear needs to be evaluated.

10.4 Clearances and creepage distances

Meets the product standard's requirements.

10.5 Protection against electric shock

Does not apply, since the entire switchgear needs to be evaluated.

10.6 Incorporation of switching devices and components

Does not apply, since the entire switchgear needs to be evaluated.

10.7 Internal electrical circuits and connections

Is the panel builder's responsibility.

10.8 Connections for external conductors

Is the panel builder's responsibility.

10.9.2 Power-frequency electric strength

Is the panel builder's responsibility.

10.9.3 Impulse withstand voltage

Is the panel builder's responsibility.

10.9.4 Testing of enclosures made of insulating material

Is the panel builder's responsibility.

10.10 Temperature rise

The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

10.11 Short-circuit rating

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.12 Electromagnetic compatibility

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.13 Mechanical function

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



Eaton.com/socialmedia