




Part Number : [2286580001](#)

Product Description : Universal Serial Bus (USB)
Shielded I/O Receptacle, Type C, Upright, Surface
Mount, Straight Tab, 24 Circuits, 0.076µm Gold (Au)
Plating

Series Number : 228658

Status : Active

Product Category : I/O Connectors



Documents and Resources

Drawings

[2286580001 sd.pdf](#)

[2286580001-PK1.pdf](#)

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[2286580001-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	I/O Connectors
Series	228658
Description	Universal Serial Bus (USB) Shielded I/O Receptacle, Type C, Upright, Surface Mount, Straight Tab, 24 Circuits, 0.076µm Gold (Au) Plating
Application	Wire-to-Board
Component Type	Receptacle
IEC Compliance	62680-1-3:2024, 62680-1-2:2024
Product Name	USB
Standard	USB 3.2 Gen 2
Type	C
UPC	198930710530
USB-IF/TID	15145

Electrical

Current - Maximum per Contact	0.25A,1.25A,5.0A, See Product Specification
Shielded	Yes
Shield Type	Full Shield
Voltage - Maximum	48V AC/DC

Physical

Circuits (Loaded)	24
Circuits (maximum)	24
Color - Resin	Black
Durability (mating cycles max)	10000
Gender	Female
Keying to Mating Part	No
Lock to Mating Part	No
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	High Temperature Thermoplastic
Mounting Style	Upright
Net Weight	1.565/g
Number of Rows	2
Orientation	Right Angle
Packaging Type	Embossed Tape on Reel
Panel Mount	Yes
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Pitch - Mating Interface	0.50mm
Pitch - Termination Interface	0.50mm
Plating min - Mating	0.076µm
Plating min - Termination	0.025µm
Polarized to Mating Part	No
Polarized to PCB	No
Ports	1
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	Surface Mount
Waterproof / Dustproof	No

Mates With / Use With

Mates with Part(s)

Description	Part Number
USB Shielded I/O Type C Plugs	<u>105444</u>
USB Type C Vertical Shielded I/O Plugs	<u>218847</u>
Mates With	USB Type C Plug/Cable

This document was generated on Aug 03, 2026