





回路番号 1 マーク
CIRCUIT NO. 1 MARK


ターミナル
TERMINAL






36.6	34.85	31.2	29	52610-3033	30
34.6	32.85	29.2	27	52610-2833	28
32.6	30.85	27.2	25	52610-2633	26
31.6	29.85	26.2	24	52610-2533	25
30.6	28.85	25.2	23	52610-2433	24
29.6	27.85	24.2	22	52610-2333	23
28.6	26.85	23.2	21	52610-2233	22
27.6	25.85	22.2	20	52610-2133	21
26.6	24.85	21.2	19	52610-2033	20
25.6	23.85	20.2	18	52610-1933	19
24.6	22.85	19.2	17	52610-1833	18
23.6	21.85	18.2	16	52610-1733	17
22.6	20.85	17.2	15	52610-1633	16
21.6	19.85	16.2	14	52610-1533	15
20.6	18.85	15.2	13	52610-1433	14
19.6	17.85	14.2	12	52610-1333	13
18.6	16.85	13.2	11	52610-1233	12
17.6	15.85	12.2	10	52610-1133	11
16.6	14.85	11.2	9	52610-1033	10
15.6	13.85	10.2	8	52610-0933	9
14.6	12.85	9.2	7	52610-0833	8
13.6	11.85	8.2	6	52610-0733	7
12.6	10.85	7.2	5	52610-0633	6
11.6	9.85	6.2	4	52610-0533	5
D	(C)	B	(A)	EMBOSSED PACKAGE ORDER NO. オーダー番号	極数 CKT.
CONNECTOR SERIES NO.: 52610-**22					

GENERAL TOLERANCES (UNLESS SPECIFIED)	
10 UNDER	± 0.2
10 OVER 30 UNDER	± 0.25
30 OVER	± 0.3
ANGULAR	± 3 °
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
DIMENSION UNITS		SCALE		CURRENT REV DESC: REVISED			molex		
mm		8:1							
GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 600129 DRWN: YCHEN128 2018/04/11 CHK'D: KTAKAHASHI 2018/04/12 APPR: NUKITA 2018/04/13			1.0 FPC CONN ZIF S/T HOUSING ASSY		
ANGULAR TOL ± 3.0 °									
4 PLACES ± 0.2									
3 PLACES ± 0.25									
2 PLACES ± 0.3									
1 PLACE ±		INITIAL REVISION: DRWN: NASANUMA 2012/09/12 APPR: KMORIKAWA 2013/03/15			PRODUCT CUSTOMER DRAWING				
0 PLACES ±									
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES	
						A3-SIZE		52610	
				DOCUMENT NUMBER		DOC TYPE		DOC PART	REVISION
				SD-52610-048		PSD		001	C
				MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
				SEE TABLE		GENERAL MARKET		1 OF 2	



マスク厚 : 120μm
マスク開口率 : 100%
SCREEN THICKNESS : 120 MICROMETER
SCREEN OPEN RATIO : 100%



FPC構成推奨仕様

RECOMMENDED STRUCTURE OF FPC

FFC構成推奨仕様

RECOMMENDED STRUCTURE OF FFC

FPC/FFCについて：

抜き方向は、導体側から補強板側を推奨致します。

尚、接着剤の接点部への付着は導通不良の原因になりますので、
染み出しが無い様お願い致します。

ABOUT FPC/EFC:

RECOMMENDED PUNCHER DIRECTION:

RECOMMENDED TENSIONER DIRECTION:
FROM CONDUCTOR SIDE TO STIFFNER SIDE

PLEASE PUT APPROPRIATE AMOUNT OF ADHESIVE ON ADHEREND
BECAUSE THERE IS A POSSIBILITY THAT THE EXTRA ADHESIVE
CAUSES THE DEFECT IN ELECTRICAL CONTINUITY.

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																	
DIMENSION UNITS		SCALE		CURRENT REV DESC: REVISED				molex									
mm		5:1															
GENERAL TOLERANCES (UNLESS SPECIFIED)		EC NO: 600129								1.0 FPC CONN ZIF S/T HOUSING ASSY							
		DRWN: YCHEN128 2018/04/11															
		ANGULAR TOL ± 2.0°		CHK'D: KTAKAHASHI 2018/04/12													
		5 PLACES ± 0.2		APPR: NUKITA 2018/04/13													
		3 PLACES ± 0.25		INITIAL REVISION:						PRODUCT CUSTOMER DRAWING							
2 PLACES ± 0.3		DRWN: NASANUMA 2012/09/12								DOCUMENT NUMBER		DOC TYPE		DOC PART		REVISION	
1 PLACE ±		APPR: KMORIKAWA 2013/03/15								SD-52610-048		PSD		001		C	
0 PLACES ±		THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER					
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				A3-SIZE		52610		SEE TABLE		GENERAL MARKET		2 OF 2					

GENERAL TOLERANCES (UNLESS SPECIFIED)	
10 UNDER	± 0.2
10 OVER 30 UNDER	± 0.25
30 OVER	± 0.3
ANGULAR $\pm 3^\circ$	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	

DOCUMENT STATUS	P1	RELEASE DATE	2018/04/13	03:51:01
-----------------	----	--------------	------------	----------

