

FEATURES

- **Nickel Plated Brass Construction:** Provides excellent durability and corrosion resistance.
- **Male Hose Barb Connection:** Ensures a secure fit with 10 mm hoses.
- **Female BSPP Threaded Connection:** Compatible with 3/8 inch BSPP threaded fittings for versatile use.
- **High Maximum Operating Pressure:** Supports up to 75 bar, suitable for demanding applications.
- **High Maximum Operating Temperature:** Withstands temperatures up to 300 °C, ideal for high-temperature environments.

RS PRO 10 mm Hose Barb Hose Connector, 3/8 in BSPP Threaded

RS Stock No: 665-602



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

The RS PRO hose connector is designed for secure and efficient fluid transfer in industrial applications. Featuring a robust nickel-plated brass construction, it ensures durability and resistance to corrosion. Ideal for connecting hoses to threaded fittings, this connector supports high-pressure and high-temperature environments.

General Specifications

Connection Gender A	Male
Connection Gender B	Female
Connection Size A	10 mm
Connection Size B	3/8 in
Connection Standard B	BSPP
Connection Type A	Hose Barb
Connection Type B	Threaded
Maximum Operating Pressure	75 bar
Product Type	Hose Connector
Sub Type	Hose Connector

Mechanical Specifications

Body Material	Nickel Plated Brass
Hose Inside Diameter	10 mm

Operation Environment Specifications

Maximum Operating Temperature	300 °C
-------------------------------	--------

Approvals

Standards/Approvals	PED 2014-68-UE, REACH 1907-2006, RoHS 2011-65-CE
---------------------	--

