


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
G	14		W2	REVISED PER ECO-11-004587	11MAR11	RK	HMR



STYLE 1

STYLE 2
INSULATION RESTRICTING

- 1
- STAMP " AMP ", APPROX AS SHOWN

2

3

4

5

6

7

8

9

10

	100	LOOSE PIECE, BOX	#6	.145	.050-.082	26-22	--	A	6	7	4	8-326875-1
OBSOLETE	100	LOOSE PIECE, SM. BOX	#6	.145	.050-.082	26-22	--	A				3-326875-0
OBSOLETE	1000	LOOSE PIECE, LG. BOX	#6	.145	.050-.082	26-22	--	A				2-326875-9
OBSOLETE	5000	2-326875-4 ON TAPE, REEL	#6	.145	.031-.055	24	BLUE	B	5	6	9	2-326875-8
OBSOLETE	5000	2-326875-3 ON TAPE, REEL	#10	.197	.026-.055	26	BLACK	B				2-326875-7
OBSOLETE	5000	2-326875-2 ON TAPE, REEL	#6	.145	.026-.055	26	BLACK	B				2-326875-6
	500	LOOSE PIECE	#10	.197	.031-.055	24	BLUE	B	6	9	9	2-326875-5
	500	LOOSE PIECE	#6	.145	.031-.055	24	BLUE	B				2-326875-4
OBSOLETE	500	LOOSE PIECE	#10	.197	.026-.055	26	BLACK	B				2-326875-3
OBSOLETE	500	LOOSE PIECE	#6	.145	.026-.055	26	BLACK	B	9	9	9	2-326875-2
	4000	326875-1 ON TAPE, REEL	#6	.145	.050-.082	26-22	--	A				2-326875-1
	500	LOOSE PIECE	#6	.145	.050-.082	26-22	--	A				326875
QTY		PACKAGE TYPE	STUD SIZE "D"	DIM "C"	WIRE INSUL. DIA	WIRE SIZE	COLOR CODE	STYLE	BODY FINISH	SLEEVE FINISH	MATERIAL	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

MATERIAL
SEE TABLE

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± .008
4 PLC ± -
ANGLES ± 5°
FINISH
SEE TABLE

DWN JR RUTH 14JAN10
CHK TOM MICHELUTTI 14JAN10
APVD MIKE PERCHERKE 14JAN10
PRODUCT SPEC
APPLICATION SPEC
WEIGHT -

CUSTOMER DRAWING

SCALE 10:1

SHEET 1 of 1

REV W2

TE Connectivity

NAME
TERMINAL, NYLON - PIDG - RING TONGUE
WIRE SIZE: 26-22

SIZE A2
CAGE CODE 00779
DRAWING NO C-326875
RESTRICTED TO -