





## C(D)G5-S, Stainless Steel Cylinder, Double Acting, Single Rod CDG5BN32TFSR-50

### Datasheet

- Double acting, single rod CG5-S cylinder
- All stainless steel external parts
- Special scraper prevents water from entering cylinder
- Bore sizes (mm): 20, 25, 32, 40, 50, 63, 80 and 100
- Auto switch capability



Double-acting, single-rod cylinder


### Standard specifications

|                                                    |                                           |
|----------------------------------------------------|-------------------------------------------|
| Magnet                                             | D (Built-in)                              |
| Mounting                                           | B (Basic Style)                           |
| Style                                              | N (Non-lube Rubber Cushion)               |
| Bore Size                                          | 32mm                                      |
| Thread                                             | TF (G Ports)                              |
| Seal Material                                      | R (NBR)                                   |
| Stroke                                             | 50                                        |
| Auto Switch                                        | None                                      |
| Lead Wire or Prewired Connector                    | 0.5m (Or None in the Case of No Switch)   |
| Number                                             | 2 pcs. (Or None in the Case of No Switch) |
| Rod End Options                                    | None                                      |
| Temperature Resistance                             | None                                      |
| Pressure medium                                    | Air;Air                                   |
| Maximum temperature of pressure medium with magnet | 60 °C                                     |
| Minimum temperature of pressure medium with magnet | -10 °C                                    |
| Maximum operating pressure                         | 1.0 MPa                                   |
| Minimum operating pressure                         | 0.05 MPa                                  |
| Proof pressure                                     | 1.5 MPa                                   |
| Maximum ambient temperature with magnet            | 60 °C                                     |


|                                         |                  |
|-----------------------------------------|------------------|
| Minimum ambient temperature with magnet | -10 °C           |
| Number of pneumatic connections         | 2 pcs.           |
| Pneumatic input connection              | G 1/8            |
| Mode of operation of drive              | Double acting    |
| Maximum piston speed                    | 1000 mm/s        |
| Piston rod end                          | External thread  |
| Geometric form of the piston rod        | Round piston rod |
| Male thread of rod end                  | M10 x 1.25       |
| Minimum piston speed                    | 50 mm/s          |
| Weight                                  | 0.750 Kg         |

## Dimensions


基本形(B)/C□G5BN□S<sup>R</sup><sub>V</sub>: ラバークッション付




基本形(B)/C□G5BA□S<sup>R</sup><sub>V</sub>: エアクッション付




軸方向フート形(L)/C□G5L□S<sup>R</sup><sub>V</sub>




ロッド側フランジ形(F)/C□G5F□S<sup>R</sup><sub>V</sub>



ヘッド側フランジ形(G)/C□G5G□S<sup>R</sup><sub>V</sub>




クレスピー一体形(E)/C□G5E□S<sup>R</sup><sub>V</sub>



## Constructions

### Construction

With rubber bumper



### Component Parts

| No. | Description   | Material                                 |
|-----|---------------|------------------------------------------|
| 1   | Rod cover     | Stainless steel 304                      |
| 2   | Head cover    | Stainless steel 304                      |
| 3   | Cylinder tube | Stainless steel 304                      |
| 4   | Piston rod    | Stainless steel 304   Hard chrome plated |
| 5   | Bumper        | Urethane                                 |
| 6   | Rod end nut   | Stainless steel 304                      |
| 17  | Bushing       | Bearing alloy                            |
| 18  | Piston        | Aluminium alloy                          |
| 19  | Wearing       | Resin                                    |

Note 1) Component part material and surface treatment other than listed above are the same as the standard type of Series CG1.

Note 2) For cylinders with an auto switch, the piston is fixed with a magnet.

| No. | Description             | Material |          |
|-----|-------------------------|----------|----------|
|     |                         | CG5□□□SR | CG5□□□SV |
| 8   | Water resistant scraper | NBR      | FKM      |
| 9   | Rod seal                |          |          |
| 10  | Piston seal             |          |          |
| 21  | Piston gasket           |          |          |
| 13  | Label protector         | PET      |          |

## Additional information

Catalogue

[CJ5-CG5-B\\_EU.pdf](#)