

PACK&G'O®

REF.
NUS57P

**FULL BODY HARNESS WITH
INTEGRATED BAG PAD**

MAX
140 KG






INNOVATION

Patented product
Integrated transport bag
2 attachment points harness
Automatic buckles



TECHNICAL SPECIFICATIONS

REF.
NUS57P

- 1 • Water repellent webbing in polyester 44 mm (R≥25kN)
 - 2 • **Reversible bag made of fluo neoprene fitted with a comfort back pad**
 - 3 • Shoulder straps adjustment pulling downwards with steel black powder coated quick buckles male/female
 - 4 • Chest strap 44 mm and legs straps fastening through black zinc plated automatic buckles with locking indicator
 - 5 • Front fall arrest textile loop and back fall arrest D ring in metal
 - 6 • Patented anti-trauma buckles in steel black powder coated
 - 7 • **Removable tool-holder**
 - 8 • Large back plate in polypropylene
 - 9 • Drop indicators
- Static resistance ≥ 15 kN
 • Weight : 1,4 kg

DESCRIPTION

Pack&G'O® is a full body harness with an integrated transport bag. It offers to the user a better comfort and allows its quick storage. this harness includes 2 fall arrest attachment points: 1 in the front with textile loop and 1 in the back with metallic D ring. **Pack&G'O®** is an innovative harness with its anti trauma buckles on legs which reduces the arrest force in case of a fall. It is fitted with automatic buckles on chest and legs straps. Available in 3 sizes it can be easily adjusted by pulling downwards the shoulder straps through the quick buckles.

USE

Full body harness to use in case of fall hazard. Intended to maintenance works in industry and the construction area.



+ PRODUCT

Transparent user sleeve sewn on back of the bag. Dimensions 90*50mm