

Eaton 183039

Catalog Number: 183039

Eaton xEffect - XNH circuit protection. NH fuse-switch 3p flange connection M8 max. 95 mm², busbar 60 mm, electronic fuse monitoring, NH000 & NH00



General specifications

Product Name	Catalog Number
Eaton xEffect XNH device for busbar system	183039
	EAN
	4015081779666
Product Length/Depth	Product Height
204 mm	161 mm
Product Width	Product Weight
106 mm	0.907 kg
Compliances	Certifications
RoHS conform	IEC/EN 60947-3

Product specifications

Type

Fuse control - electronic

Special features

Permanent operation (rated operating mode)

Current paths of electrolytic copper, silver-plated

Cable connection optionally at the top or bottom

With electronic monitoring of fuse-links

Features

Electronic fuse monitoring and EMC (Electromagnetic compatibility) as of IEC 61000-4-4

Standard sealable

Halogen free

Electronic fuse monitoring and EMC (Electromagnetic compatibility) as of IEC 61000-4-5

10.10 Temperature rise

The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

10.11 Short-circuit rating

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.12 Electromagnetic compatibility

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.13 Mechanical function

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

10.2.2 Corrosion resistance

Meets the product standard's requirements.

10.2.3.1 Verification of thermal stability of enclosures

Meets the product standard's requirements.

10.2.3.2 Verification of resistance of insulating materials to normal heat

Meets the product standard's requirements.

10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal

Resources

Brochures

[eaton-xeffect-xnh-fuse-switch-disconnector-brochure-br019002en-en-us.pdf](#)

Catalogs

[eaton-panel-building-accessories-catalog-ca008008en-en-us.pdf](#)

Certification reports

[eaton-xeffect-xnh-fuse-switch-disconnector-declaration-of-conformity-en-us.pdf](#)

Drawings

[eaton-circuit-breaker-xeffect-xeffect-xnh-circuit-protection-dimensions-011.eps](#)

eCAD model

[ETN.XNH00-FCE-S160.edz](#)

Installation instructions

[IL0131111ZU](#)

mCAD model

[eaton-XNH00-FCE-S160-3d-model.stp](#)

[eaton-XNH00-FCE-S160-drawing.dwg](#)

Wiring diagrams

[eaton-switch-xeffect-xeffect-xnh-circuit-protection-wiring-diagram.eps](#)

[eaton-switch-xeffect-xeffect-xnh-circuit-protection-wiring-diagram-002.eps](#)

elect. effects

Meets the product standard's requirements.

10.2.4 Resistance to ultra-violet (UV) radiation

Meets the product standard's requirements.

10.2.5 Lifting

Does not apply, since the entire switchgear needs to be evaluated.

10.2.6 Mechanical impact

Does not apply, since the entire switchgear needs to be evaluated.

10.2.7 Inscriptions

Meets the product standard's requirements.

10.3 Degree of protection of assemblies

Does not apply, since the entire switchgear needs to be evaluated.

10.4 Clearances and creepage distances

Is the panel builder's responsibility.

10.5 Protection against electric shock

Does not apply, since the entire switchgear needs to be evaluated.

10.6 Incorporation of switching devices and components

Does not apply, since the entire switchgear needs to be evaluated.

10.7 Internal electrical circuits and connections

Is the panel builder's responsibility.

10.8 Connections for external conductors

Is the panel builder's responsibility.

10.9.2 Power-frequency electric strength

$U_i = 800 \text{ V AC}$

10.9.3 Impulse withstand voltage

Is the panel builder's responsibility.

10.9.4 Testing of enclosures made of insulating material

Is the panel builder's responsibility.

Fitted with:

Connectors

Error protection

Frequency rating

40 Hz - 60 Hz

Pollution degree

3

Creepage resistance

CTI 600

Equipment heat dissipation, current-dependent

14 W

Rated uninterrupted current (I_u)

160 A

Switching current of electronic fuse monitoring - max

1 A

Total heat dissipation without fuses at I_{th}

14 W

Voltage rating at AC - max

250 VAC

Voltage rating at DC - max

24 VDC

Ambient operating temperature details

Ambient temperature range:

-25 °C - 55 °C

Operating temperature

range: -5 °C - 55 °C

Voltage rating at AC

400 V (AC-23B)

500 V (AC-22B)

690 V (AC-21B)

Voltage rating at DC

250 V DC at DC-22B

440 V DC at DC-21B

Conditioned rated short-circuit current I_q

120 kA

Number of poles

Three-pole

Rated operation power at AC-23, 400 V

0 kW

Size

NH000 / NH00 fuse

Rated impulse withstand voltage (Uimp)

8 kV

Color

Gray

Connection type

Flat connection

Degree of protection

IP3X

IP20 (operating status, XNH installed)

IP2XC (contact protection, XNH installed)

IP10 (handle cover open, XNH installed)

Rated short-time withstand current (Icw)

7 kA

Direction of incoming supply

As required (FLEX System)

Electrical connection type of main circuit

Screw connection

Activation type

Dependent manual activation

Actuator position

Front side

Actuator type

Cover grip

Voltage inputs

400 V AC - 500 V AC (+/-10%)

Voltage test

Yes, sliding inspection windows

Heat dissipation at 80% without fuses

9 W

Heat dissipation per pole, current-dependent

4.7 W

Mounting position

Vertical or horizontal

Suitable for

Busbar mounting

Rated conditional short-circuit current (Iq)

120 kA

Overvoltage category

II (500 V)

III

III (230/400 V)

Suitable for fuses

NH00

Material

Polyamide

Cable entry type

Other

Frequency rating of contacts

40 Hz - 60 Hz

Mounting method

Busbars of 60 mm

Rated operation current (Ie)

160 A

Locking facility

Yes, optional

Flammability characteristics (UL)

Self-extinguishing (UL 94)

Degree of protection (front side)

Other

Heat deflection temperature

125 °C

Lifespan, electrical

300 operations

Lifespan, mechanical

1400 operations

Electronic fuse monitoring

1.5 VA

1 NC

> 1 kOhm/V

NH with live handle straps

Self-supplied

Test button for relay + LEDs

1 LED green

3 LEDs (F1, F2, F3) red

1 NO

Terminal capacity (copper busbar)

20 mm x 10 mm

Max. 25 mm cable lug width at flange connection

Bolt diameter at flange connection: M8

Terminal capacity (copper band)

9 mm x 0.8 mm (6x) at box terminal

Terminal capacity (stranded cable)

1.5 mm² - 50 mm² at box terminal

1.5 mm² - 95 mm² at box terminal

10 mm² - 70 mm² at clamp-type terminal

Frequency rating (electronic fuse monitoring)

50 - 60 Hz

Rated operational current

160 A

160 A (AC-23B)

160 A (AC-22B)

160 A (AC-21B)

Operating altitude without derating - max

2000 mm

Permitted power loss per fuse link - max

12 W

Power rating at AC-23, 400 V

0 kW

Rated insulation voltage (Ui)

800 VAC

Rated operating voltage (Ue) at AC - max

500 V

Rated operational current for specified heat dissipation (In)

160 A

Rated conditional short-circuit rating

100 kA (690 V)

120 kA (500 V)

Terminal capacity (copper strip)

9 mm x 0.8 mm (9x) at box terminal



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



Eaton.com/socialmedia