



Connectors > Connector Accessories > Connector Hardware



Connector Hardware Accessory Type: **Military Polarizer**

Primary Product Color: **Black**

Primary Product Material: **Thermoplastic**

Hardware Accessory Function: **Position Assurance**

Features

Product Type Features

Connector Hardware Accessory Type	Military Polarizer
Hardware Accessory Function	Position Assurance

Body Features

Primary Product Color	Black
Primary Product Material	Thermoplastic

Dimensions

Product Length	8.5 mm[.335 in]
----------------	-----------------

Industry Standards

Compatible With Agency/Standards Products	CSA, UL
Compatible With Approved Standards Products	CSA LR7189, UL E28476

Packaging Features

Packaging Method	Bag & Box
Packaging Quantity	50

Product Compliance



For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 1-111446-4
10 UNIV I/O, NO EARS,LEAD FREE

TE Part # 1-111504-4
10 UNIV I/O, NO EARS,LEAD FREE

TE Part # 1-111446-7
50 UNIV I/O, NO EARS,LEAD FREE

Also in the Series | [AMP-LATCH Universal Headers](#)



Connector Hardware(13)



Ribbon Cable Connectors(523)


Customers Also Bought




TE Part #5-1393239-5
RT214024



TE Part #2-2176070-0
3521 62R 1% 2W



TE Part #61134-3
110 FASTON TAB TPBR



TE Part #1-87756-6
MOD IV RECP LP



TE Part #2-1761603-3
IDC LOW PRO HDR 10P VERT BLUE




TE Part #1393766-3
R10-E1X2-S800=R10



TE Part #2-1393143-4
27E212=SOCKET,R10,10,PC,PHEN



TE Part #2154829-1
High Power Inverted Thru Board Con 2 Pos



TE Part #2-1393143-1
27E193=SOCKET,R10,11,PC,PHEN



TE Part #6-1393231-5
RP7SL012

Documents

Product Drawings

POLARIZER AMP-LATCH 50/BAG

English

CAD Files

Customer View Model

ENG_CVM_CVM_499991-2_H.2d_dxf.zip

English

3D PDF



3D

Customer View Model
[ENG_CVM_CVM_499991-2_H.3d_igs.zip](#)

English

Customer View Model
[ENG_CVM_CVM_499991-2_H.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages
[AMPMODU_INTERCONNECTION_SYSTEM_SECTION5_CONT](#)

English

[Ribbon Cable Interconnect Solutions](#)

English

Agency Approvals
[Agency Approval Document](#)

English