



Connectors > Connector Accessories > Connector Hardware > Double Sided QLPIN Bulkhead



Connector Hardware Accessory Type: Quick Lock Pins

Operating Temperature (Max): 90 °C [194 °F]

Operating Temperature Range: -40 – 90 °C [-40 – 194 °F]

Hardware Accessory Function: Latching, Locking & Retention

[All Double Sided QLPIN Bulkhead \(6\)](#)

Features

Product Type Features

Connector Hardware Accessory Type	Quick Lock Pins
Hardware Accessory Function	Latching, Locking & Retention

Mechanical Attachment

Thread Size	None
-------------	------

Usage Conditions

Operating Temperature (Max)	90 °C[194 °F]
Operating Temperature Range	-40 – 90 °C[-40 – 194 °F]

Packaging Features

Packaging Method	Box
Packaging Quantity	500

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247)



Candidate List Declared Against: JAN 2025
(247)

SVHC > Threshold:

Pb (3.5% in Component Part)

Article Safe Usage Statements:
Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
-----------------	---

Solder Process Capability	Not reviewed for solder process capability
---------------------------	--





Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts


 TE Part # 1-2308338-1 QL-FULL METAL HOODS SIZE 5 (1 CABLE CLP)	 TE Part # 1-2308327-1 FULL METAL HOODS SIZE 3 (1)	 TE Part # 1-2308321-1 FULL METAL HOODS SIZE 2, (1)	 TE Part # 1-2308330-1 FULL METAL HOODS SIZE 4 (1)
--	---	--	---

Also in the Series | Rail D-Sub Backshells

 Connector Backshells(55)	 Connector Contacts(5)	 Connector Hardware(19)	 Connector Strain Relief(67)
---	---	---	--



Crimp D-Sub Connectors(10)



D-Sub Backshells & Clamps(55)




Insertion & Extraction Tools(2)

Customers Also Bought



TE Part #1-2308298-2
QL-SET FOR VAR. E LATCH PIN WITH GUIDE 2



TE Part #CAT-R131-C1121
Cable Clamp for Size 1-3 STD/1-4 QL Shell

Documents

Product Drawings

QL-SET FOR VAR. E LATCH PIN WITH GUIDE 6

English

Datasheets & Catalog Pages

Rail D-Sub Backshells Flyer

English