



Switches > Keylock Switches



Contact Current Rating: **5 A**

Configuration (Pole-Throw): **Double Pole - Double Throw**

Operating Voltage: **20 VDC**

Operating Function: **1 NO & 1 NC**

Features

Product Type Features

Switch Type	Key Lock Switch
Actuator Style	Key Actuator

Configuration Features

Number of Positions	2
Number of Actuators	Single
Configuration (Pole-Throw)	Double Pole - Double Throw
Operating Function	1 NO & 1 NC
Panel Cutout Size	16 (Diameter) mm[.625 (Diameter) in]

Electrical Characteristics

Dielectric Withstanding Voltage (Max)	1500 VAC
Insulation Resistance	100 MΩ
Contact Current Rating	5 A
Operating Voltage	20 VDC
Contact Resistance	20 mΩ

Contact Features

Contact Finish	Gold
----------------	------

Mechanical Attachment

Product Mount Type	Panel Mount
--------------------	-------------

Housing Features

Remove Key	Both Positions
------------	----------------



Usage Conditions

Oil-Tight	No
Operating Temperature (Max)	50 °C

Operation/Application

Durability Rating	100000 Cycles
-------------------	---------------

Other

Soldering Type	Hand
----------------	------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #2331410-1
DET SW4.2X3.6X1.2 GW VERT.(UP)
NO AG RL



TE Part #2232044-2
2P, RAST 5 Tab Header, THV



TE Part #1-6609107-6
PSL0XSS60=C1043



TE Part #643326-4
13P MTA156 HDR ASSY W/O#4



TE Part #1-480350-2
01P CMNL CAP HSG F/H RED



TE Part #30926
TERMINAL,DG R 16-14 6



TE Part #5-104439-7
2X8 MTE RCPT SR PLAIN .100CL



TE Part #5-104439-3
5X4 MTE RCPT SR PLAIN .100CL



TE Part #DTS20F13-35AA
RECP ASSY



TE Part #5-104439-6
2X7 MTE RCPT SR PLAIN .100CL

Documents

Product Drawings

164J2B11=REC 2-POS KY PLL BOTH

English

CAD Files

Customer View Model

ENG_CVM_CVM_1-1437569-3_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-1437569-3_B.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_1-1437569-3_B.2d_dxf.zip

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



SWITCHES_CORE_PROGRAM_CATALOG

English