



Connectors > PCB Connectors > Wire-to-Board Connectors > FFC, FPC & Ribbon Connectors > Ribbon Cable Connectors



Connector System: **Wire-to-Board**

Number of Positions: **30**

Centerline (Pitch): **2.54 mm [.1 in]**

Row-to-Row Spacing: **2.54 mm [.1 in]**

Number of Rows: **2**

Features

Product Type Features

Connector Product Type	Connector Assembly
Connector System	Wire-to-Board
Connector & Housing Type	Receptacle
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	30
Number of Rows	2

Body Features

Primary Product Color	Blue
-----------------------	------

Contact Features

Contact Mating Area Plating Material	Gold (Au)
Wire Contact Termination Area Plating Thickness	.127 μm[5 μin]
	30 μin
Wire Contact Termination Area Plating Material	Gold Flash
Mating Square Post Dimension	.64 mm[.025 in]
Contact Current Rating (Max)	1 A

Termination Features

Termination Method to Wire & Cable	Insulation Displacement (IDC)
------------------------------------	-------------------------------

Mechanical Attachment

Mating Alignment Type	Polarization
Mating Retention	Without
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Centerline (Pitch)	2.54 mm[.1 in]
--------------------	----------------

Dimensions

Row-to-Row Spacing	2.54 mm[.1 in]
--------------------	----------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2023 (233) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.



Compatible Parts




TE Part # 3-1761712-0
IDC LOW PRO HDR 30P RA LAT



TE Part # 3-1761603-0
IDC LOW PRO HDR 30P VERT BLUE




TE Part # 1-1761606-0
IDC LOW PRO HDR 30P VERT LA




TE Part # 2-111504-0
030 UNIV I/O 30DP NO EARS LTCH




TE Part # 102320-3
A/L UNIV HDR EJT LATCH BLUE



TE Part # 1-104128-2
30 LOPRO HDR SP 30DP LATCH



TE Part # 2-111446-1
030 UNIV I/O 30DP NO EARS



TE Part # CAT-AM74-UN384H
AMP-LATCH UNIVERSAL HEADERS

Customers Also Bought



TE Part #1-794374-1
SINGLE CIRCUIT MINI UMNL ASSY



TE Part #41532
250 FASTON FLAG REC 18-12 AWG TPBR




TE Part #3-2176058-9
RLP73K 3A R39 5% 2K RL



TE Part #2-2176339-5
CRGCQ 0603 1K0 1%



TE Part #3-2176339-8
CRGCQ 0603 12K 1%




TE Part #1586041-6
6P VAL-U-LOK R/A HDR V2



TE Part #350218-2
UMNL PIN 20-14 .0126AUBR



TE Part #2-1761603-6
IDC LOW PRO HDR 16P VERT BLUE



TE Part #CAT-AM74-UN384H
AMP-LATCH UNIVERSAL HEADERS



Documents

Product Drawings

622-3041LF=FSKT IDC S 30 30AU

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-1658527-7_C.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2-1658527-7_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2-1658527-7_C.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Ribbon Cable Interconnect Solutions

English

Instruction Sheets

Instruction Sheet (U.S.)

English