




Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **.32 – .82 mm²**

Mating Tab Width: **6.35 mm [.25 in]**

Mating Tab Thickness: **.81 mm [.032 in]**

Features

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
Connection Capacity	Single

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	6.35 mm[.25 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Orientation	Straight
Contact Base Material	Brass
Terminal Plating Material	Gold
Crimp Type	F-Crimp
Barrel Type	Open

Termination Features

Product Terminates To	Wire & Cable
-----------------------	--------------

Mechanical Attachment

--



Wire Insulation Support	With
-------------------------	------

Dimensions

Compatible Insulation Diameter Range	1.02 – 2.54 mm[.04 – .1 in]
Wire Size	.32 – .82 mm²

Usage Conditions

Insulation Option	Uninsulated
-------------------	-------------

Packaging Features

Packaging Quantity	500
Packaging Method	Loose Piece/Carton

Other

Line	AMP POSITIVE LOCK
------	-------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

TE Part # 927853-6
PL 250 REC TERMINAL 20-17 PTPB LP

TE Part # 170265-2
PL 250 REC 12-10 AWG 0.406 X 42.3

TE Part # 927853-8
PL 250 REC 20-17 AWG AgBR

TE Part # 341002-6
PL 250 REC TERMINAL 18-14 PTPB LP

TE Part # 928901-3
PL 250 REC TERMINAL 17-13 AWG TPBR LP

TE Part # 341001-3
PL 250 REC TERMINAL 13-11 TPBR LP

TE Part # 341001-6
PL 250 REC TERMINAL 13-11 PTPB LP

TE Part # 1-160773-0
PL 250 REC TERMINAL 20-15 NIPPB LP

TE Part # 341001-1
FASTON 250 REC 13-11 AWG BR LP

TE Part # 737015-3
PL TERMINAL RECEPTACLE 4-6 MM2 PTPBR

TE Part # 341002-1
PL 250 REC TERMINAL 18-14 AWG BR LP

Also in the Series | Positive Lock 250

Automotive Terminals(1)

Crimp Terminal Housings(177)

Insertion & Extraction Tools(3)

Insulation Boots & Sleeves(5)

Quick Disconnects(173)



Customers Also Bought



TE Part #A40182-000
HEX40-AB-00-09-A1-1



TE Part #892583-000
HEX40-AB-90-13-A3-1




TE Part #BAA0093-00
EN3660-033AF



TE Part #1577640-1
TERMINAL RT PIDG PEEK STRATO 14-12 AWG



TE Part #531090-000
342A012-3/86-0



TE Part #1577646-1
TERMINAL RT PIDG PEEK STRATO 10 AWG



TE Part #509753-000
HEX40-AB-00-21-A9-1



TE Part #648686-000
HEX40-AB-90-25-A17-1



TE Part #327913-000
HEX40-AB-00-17-A6-1



TE Part #F48658-000
D-SCE-18-50-4-CS34034

Documents

Product Drawings
POS LOCK RECEPTACLE GOLD

English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_1337265-1_A.2d_dxf.zip

English

Customer View Model
ENG_CVM_CVM_1337265-1_A.3d_igs.zip

English

Customer View Model
ENG_CVM_CVM_1337265-1_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

1337265-1

Quick Disconnect Receptacle, 22 – 18 AWG, .32 – .82 mm² Wire, 6.35 mm [.25 in] Tab Width, Straight, Brass, Gold Plating, Positive Lock 250

