

# Product datasheet

Specifications



## ABS box IP66 IK07 RAL7035 Int.H105W105D55 Ext.H116W116D62 Opaque cover H10

Local distributor code:

387531166

NSYTBS11116

**EAN Code: 3606480165252**

### Main

Range	PanelSeT
Device application	Multi-purpose
Category	Industrial box
Height	116 mm
Width	116 mm
Depth	62 mm
Internal height	105 mm
Internal width	105 mm
Internal depth	55 mm
Enclosure mounting	Wall mounted
Device composition	1 body 1 cover 4 cover screw
Quantity per set	Set of 5
Body type	One piece moulded
Type of front cover	Low plain cover
Cover fixing	Plastic screws
Lock type	Captive screw flat outside sealed area
Removable parts	Cover by captive screws

### Complementary

Material	ABS with 45% of post-industrial recycled content
Colour	Grey (RAL 7035)
Standards	IEC 62208
Product certifications	TÜV
Electrical insulation class	Class II
IP degree of protection	IP66 conforming to NEMA 4.4X
IK degree of protection	IK07 conforming to IEC 62262
Glow wire resistance	650 °C conforming to IEC 60695-2-11
Ambient air temperature for storage	-15...40 °C
Operating temperature	-25...60 °C
Net weight	0.151 kg

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.200 cm
Package 1 Width	11.600 cm
Package 1 Length	11.600 cm
Package 1 Weight	149.000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Height	12.200 cm
Package 2 Width	12.500 cm
Package 2 Length	33.100 cm
Package 2 Weight	748.000 g
Unit Type of Package 3	CAR
Number of Units in Package 3	75
Package 3 Height	40.000 cm
Package 3 Width	40.000 cm
Package 3 Length	60.000 cm
Package 3 Weight	12.700 kg

## Logistical informations

Country of origin	HU
-------------------	----

## Contractual warranty

Warranty (in months)	18
----------------------	----



## Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



### Environmental footprint

Total lifecycle Carbon footprint	1 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	0.5 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	0.3 kg CO2 eq.
Carbon footprint of the installation phase [A5]	0 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	0 kg CO2 eq.
Carbon footprint of the end-of-life phase [C1 to C4]	0.3 kg CO2 eq.
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Use Better



### Materials and Substances

Average percentage of recycled plastic content	45 %
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	<a href="#">Compliant</a>
REACH Regulation	<a href="#">Free of Substances of Very High Concern above the threshold</a>

## Use Longer



### Lifetime extension

Repair	No
--------	----

## Use Again



### Repack and remanufacture

Recyclability potential, in %	1
End of life manual availability	No need of specific recycling operations
Take-back	Nej

Technical Illustration

Dimensions

---




Image of product / Alternate images

Alternative

---

