

Product data sheet

Specifications



auxiliary latch block TeSys Deca - 256...277 V DC/AC 50...60 Hz

LA6DK10U

Product availability : Stock - Normally stocked in distribution facility

Main

Range	TeSys
Product or Component Type	Mechanical latch block
Product compatibility	LC1D40 3 phases + neutral AC LP1D40 3 phases + neutral DC LP1D65 3 phases + neutral DC LC1D65 3 phases + neutral AC
[Uc] control circuit voltage	256/277 V AC 50/60 Hz 256/277 V DC

Complementary

Mounting Location	Front side
Tripping control	Manual Electrical
[Ui] rated insulation voltage	690 V IEC 60947-5-1
Power required in VA	25 AC
Power required in W	30 W DC
Mechanical durability	500000 cycles
Maximum operating rate	1200 cyc/h
On-load factor	10 %
Net Weight	0.15 lb(US) (0.07 kg)

Environment

Product Certifications	UL CSA
IP degree of protection	IP2XVDE 0106
Protective treatment	THIEC 60068
Ambient Air Temperature for Operation	-13...131 °F (-25...55 °C)
Ambient Air Temperature for Storage	-40...176 °F (-40...80 °C)

Ordering and shipping details

Category	22341-CONTACTOR,D,K,&F ACCESS
----------	-------------------------------

Discount Schedule	I12
GTIN	3389110745825
Returnability	No
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.09 in (5.3 cm)
Package 1 Width	1.97 in (5.0 cm)
Package 1 Length	2.56 in (6.5 cm)
Package 1 Weight	3.39 oz (96.0 g)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------

Recommended replacement(s)