

ELECTRONIC AND *SensoPlus*® ELECTRONIC PLIERS

The Electronics Industry demands the highest quality and precision from all its components and tools.

The C.K Electronic Range of pliers and cutters conforms perfectly to market requirements. C.K attention to detail and quality specification has produced the ultimate range for use in the electronics and precision engineering industries. Each plier is individually tested by a skilled craftsman to ensure accuracy of movement and cut.






The *SensoPlus*® range


improved handle design, tailored to your hand's shape and feel. This perfect shape is designed with your hand in mind. It has a grip which feels like a fine kid glove, fatigue free with safe control for the most-exacting work demands.



The C.K Electronics catalogue contains the complete range of pliers, screwdrivers, tweezers and other products specially designed and manufactured for this sector.

KEY REFERENCE:

 Mini Bevel cut	Designed for the cutting of hard and soft steel wires as well as softer materials like copper wire and cable.	 Extra Full Flush cut (EF)	For absolutely flat cuts of softer steel, copper wires and cables. Extremely fine.
 Full Flush cut (F)	Almost full flush cutting, with fine cutting edges. Side cutters for softer steel as well as copper wires and cables.	 Smooth cut	 Serrated

 For use in ESD compatible areas. **S** Indicates a SensoPlus product.

ITEM NO: "D" refers to a SensoPlus handle.


LIFETIME GUARANTEE



- 1 PVC coated handles - comfort and non slip use
- 2 High grade alloy steel, Hot drop forged, Oil hardened and tempered
- 3 long life and perfect precision
- 4 Soft, comfortable and slip free thermoplastic material compound grips.
- 5 Spot-welded double leaf spring ensures consistently repeatable functioning for a lifetime of top performance.
- 6 Anti-slip bow enhances pin-point control.
- 7 Precision box joint means butter smooth action for exact guidance of jaws without the need for readjustment.
- 8 Mirror polishing notable reduces risks of corrosion, chrome flaking, and is easy to clean.
- 9 Long-life cutting edges are induction hardened to maintain cutting ease.
- 10 The SensoPlus range is ESD compatible

SNIPE NOSE PLIER 3772

Serrated and smooth jaws.



3772




3772D



	DESCRIPTION	ITEM NO		BOX QTY	WEIGHT
	130mm/5 1/4"	Smooth	T3772	3	49g
	130mm/5 1/4"	Serrated	T3772 1	3	49g
	135mm/5 1/4"	Smooth	T3772D 120	3	59g
	135mm/5 1/4"	Serrated	T3772 1D120	3	59g

SNIPE NOSE PLIERS 3767

Bent. Short fine jaws.



3767




3767D



	DESCRIPTION	ITEM NO		BOX QTY	WEIGHT
	120mm/4 3/4"	Smooth Jaws	T3767	3	46g
	135mm/5 1/4"	Smooth Jaws	T3767D 120	3	56g

SNIPE NOSE PLIERS 3777

Long head snipe nose pliers with serrated inside jaws.



3777




3777D



	DESCRIPTION	ITEM NO		BOX QTY	WEIGHT
	150mm/6"	Serrated	T3777	3	84g
	165mm/6 1/2"	Serrated	T3777D 150	3	94g

SNIPE NOSE PLIERS 3769

Bent, long jaws, serrated.



3769




3769D



	DESCRIPTION	ITEM NO		BOX QTY	WEIGHT
	150mm/6"	Serrated	T3769	3	86g
	165mm/6 1/2"	Serrated	T3769D 150	3	96g

SNIPE NOSE PLIERS 3795

Straight, with smooth jaws, without springs.




3795



	DESCRIPTION	ITEM NO		BOX QTY	WEIGHT
	190mm/7 1/2"	Smooth Jaws.	T3795	3	131g

ROUND NOSE PLIERS 3771

Smooth inside jaws.



3771



3771D



	DESCRIPTION	ITEM NO		BOX QTY	WEIGHT
120mm/4 1/4"	Smooth	T3771		3	67g
135mm/5 1/4"	Smooth	T3771D 120	S	3	77g

FLAT NOSE PLIERS 3770

Short smooth jaws.




3770D



	DESCRIPTION	ITEM NO		BOX QTY	WEIGHT
135mm/5 1/4"	Smooth	T3770D 120	S	3	73g

FLAT NOSE PLIERS 3789

Smooth jaws.



3789



	DESCRIPTION	ITEM NO		BOX QTY	WEIGHT
145mm/5 3/4"	Smooth Jaws.	T3789		3	78g

SIDE CUTTER 3740

Half oval head. For confined spaces. High cutting capacity. Mini bevel cut.




3740D



	CUTTING CAPACITY: mm Ø AWG			ITEM NO		BOX QTY	WEIGHT
	HARD WIRE	SOFT STEEL	COPPER				
125mm/5"	0.4/26	1.0/18	1.5/15	T3740D 115	S	3	63g

SIDE CUTTER 3766

Tapered and relieved head. Also for SMD-use. Full & extra full cut options.



3766D



	CUTTING CAPACITY: mm Ø AWG			ITEM NO		BOX QTY	WEIGHT
	HARD WIRE	SOFT STEEL	COPPER				
120mm/4 1/4"	-	0.6/22	1.0/18	T3766DF 110	S	3	48g
120mm/4 1/4"	-	0.6/22	1.0/18	T3766DEF 110	S	3	58g

SIDE CUTTERS 3768

Tapered head, heavy pattern, high cutting capacity and mini bevel cut.





3768




	CUTTING CAPACITY: mm Ø AWG			ITEM NO		BOX QTY	WEIGHT
	HARD WIRE	SOFT STEEL	COPPER				
135mm/5 1/4"	0.5/24	1.2/16	1.8/13	T3768		3	100g

SIDE CUTTERS 3773


Oval head for use in confined areas. Three cut options.

3773





3773D




CUTTING CAPACITY: mm Ø AWG	CUTTING CAPACITY: mm Ø AWG			ITEM NO	BOX QTY	WEIGHT
	HARD WIRE	SOFT STEEL	COPPER			
115mm/4½"	0.4/26	1.0/18	1.5/15	T3773	3	65g
115mm/4½"	-	1.0/18	1.5/15	T3773F	3	65g
115mm/4½"	-	1.0/18	1.5/15	T3773EF	3	65g
125mm/5"	0.4/26	1.0/18	1.5/15	T3773D 115	3	75g
125mm/5"	-	1.0/18	1.5/15	T3773DF 115	3	75g
125mm/5"	-	1.0/18	1.5/15	T3773DEF 115	3	75g

SIDE CUTTER - TUNGSTEN CARBIDE 3779


Oval head. Tungsten Carbide edges. For very hard and tough materials. Mini bevel cut.

3779





3779D




CUTTING CAPACITY: mm Ø AWG	CUTTING CAPACITY: mm Ø AWG			ITEM NO	BOX QTY	WEIGHT
	PIANO WIRE	HARD STEEL	NICKEL			
115mm/4½"	0.6/22	1.0/18	1.2/16	T3779	3	65g
125mm/5"	0.6/22	1.0/18	1.2/16	T3779D 115	3	75g

SIDE CUTTERS 3774


Laid on joint construction. Oval head with mini bevel cut.

3774





3774D




CUTTING CAPACITY: mm Ø AWG	CUTTING CAPACITY: mm Ø AWG			ITEM NO	BOX QTY	WEIGHT
	HARD WIRE	SOFT STEEL	COPPER			
120mm/4¾"	0.4/26	1.0/18	1.5/15	T3774	3	67g

SIDE CUTTERS 3780


Small tapered head. Full flush cut.

3780





3780D




CUTTING CAPACITY: mm Ø AWG	CUTTING CAPACITY: mm Ø AWG			ITEM NO	BOX QTY	WEIGHT
	HARD WIRE	SOFT STEEL	COPPER			
110mm/4½"	-	0.6/22	1.0/18	T3780F	3	47g
120mm/4¾"	-	0.6/22	1.0/18	T3780DF 110	3	57g

HEAVY DUTY SIDE CUTTERS 3775


Heavy duty oval head side cutters with mini bevel cut, or extra full flush cut.

3775



3775D




CUTTING CAPACITY: mm Ø AWG	CUTTING CAPACITY: mm Ø AWG			ITEM NO	BOX QTY	WEIGHT
	HARD WIRE	SOFT STEEL	COPPER			
135mm/5¼"	0.7/21	1.5/15	2.0/12	T3775	3	100g
135mm/5¼"	-	1.5/15	2.0/12	T3775EF	3	101g



SIDE CUTTERS 3781

Tapered head, 3 cut options.



3781




3781D



CUTTING CAPACITY: mm Ø AWG	CUTTING CAPACITY: mm Ø AWG			ITEM NO		BOX QTY	WEIGHT
	HARD WIRE	SOFT STEEL	COPPER				
115mm/4½"	0.4/26	1.0/18	1.2/16	T3781		3	48g
125mm/5"	0.4/26	1.0/18	1.2/16	T3781D 115	S	3	58g
125mm/5"	-	1.0/18	1.2/16	T3781DF 115	S	3	58g
125mm/5"	-	1.0/18	1.2/16	T3781DEF 115	S	3	58g

SIDE CUTTER 3880

Oval head. Full flush cut.



3880




3880DF



CUTTING CAPACITY: mm Ø AWG	CUTTING CAPACITY: mm Ø AWG			ITEM NO		BOX QTY	WEIGHT
	HARD WIRE	SOFT STEEL	COPPER				
110mm/4¼"	-	0.6/22	1.2/16	T3880F		3	60g
120mm/4¾"	-	0.6/22	1.2/16	T3880DF 110	S	3	70g

TOP CUTTERS 3776

Wide head with extra long cutting edges giving a full flush cut.




3776



CUTTING CAPACITY: mm Ø AWG	CUTTING CAPACITY: mm Ø AWG			ITEM NO		BOX QTY	WEIGHT
	HARD WIRE	SOFT STEEL	COPPER				
115mm/4½"	0.5/24	1.2/16	1.6/14	T3776F		3	72g

OBLIQUE CUTTERS 3778

Wide head, extra long cutting edges with full flush cut.




3778



CUTTING CAPACITY: mm Ø AWG	CUTTING CAPACITY: mm Ø AWG			ITEM NO		BOX QTY	WEIGHT
	HARD WIRE	SOFT STEEL	COPPER				
120mm/4¾"	0.5/24	1.2/16	1.6/14	T3778F		3	75g

OBLIQUE CUTTER 3786

Slim head. For confined spaces. Full flush cut.



3786D




CUTTING CAPACITY: mm Ø AWG	CUTTING CAPACITY: mm Ø AWG			ITEM NO		BOX QTY	WEIGHT
	HARD WIRE	SOFT STEEL	COPPER				
135mm/5¼"	-	0.6/22	0.8/20	T3786DF 120	S	3	47g

OBLIQUE CUTTERS

3799

Oblique head angled at 29° for horizontal or vertical use on PCB's.
Full flush & extra full flush cut.



3799



3799D




CUTTING CAPACITY: mm Ø AWG	CUTTING CAPACITY: mm Ø AWG			ITEM NO		BOX QTY	WEIGHT
	HARD WIRE	SOFT STEEL	COPPER				
110mm/4¼"	0.4/26	1.0/18	1.2/16	T3799F		3	47g
120mm/4¾"	0.4/26	1.0/18	1.2/16	T3799DF 110	S	3	57g
120mm/4¾"	-	1.0/18	1.2/16	T3799DEF 110	S	3	57g

OBLIQUE CUTTER

3871

Extra long, slim jaws, for very confined spaces. Also for SMD-use. Full flush cut.



3871D



CUTTING CAPACITY: mm Ø AWG	CUTTING CAPACITY: mm Ø AWG			ITEM NO		BOX QTY	WEIGHT
	HARD WIRE	SOFT STEEL	COPPER				
135mm/5¼"	-	-	0.6/22	T3871DF 120	S	3	48g

