

## Measuring instrument - EEM-MB371-24DC - 1127055


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Multi-functional energy measuring device without display with 24 V DC supply, with direct Rogowski connection and integrated Modbus/TCP interface for measuring electrical parameters in low-voltage installations up to 690 V



### Key Commercial Data

Packing unit	1 pc
GTIN	 4 063151 055127
GTIN	4063151055127
Weight per Piece (excluding packing)	310.000 g
Custom tariff number	90303100
Country of origin	Germany
Sales Key	CK4C21

### Technical data

#### Dimensions

Width	90 mm
Height	80 mm
Depth	64 mm

#### Ambient conditions

Ambient temperature (operation)	-10 °C ... 55 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Maximum altitude	≤ 2000 m
Max. permissible relative humidity (operation)	≤ 95 % (non-condensing)
Degree of protection	IP20 (Housing)

#### Input data

Measuring principle	True r.m.s. value measurement
Acquisition of harmonics	up to 63rd harmonic

# Measuring instrument - EEM-MB371-24DC - 1127055

## Technical data

### Input data

Measured value	AC sine (50/60 Hz)
Input name	Voltage measuring input V1, V2, V3
Input voltage range	35 V AC ... 690 V AC (Phase/Phase)
	20 V AC ... 400 V AC (Phase/neutral conductor)
	60 V AC ... 2000000 V AC (primary)
	60 V AC ... 400 V AC (secondary)
Surge voltage capacity	760 V AC (Phase/Phase)
Precision	0.2 %
Input name	Current measurement RC1, RC2, RC3
Input current	4000 A
Response threshold from measuring range nominal value	5 A
Precision	< 1 %
	1 %
Reactive power (IEC 62053-23)	Class 2
Description of the input	Digital input in accordance with IEC/EN 61131-2 (type 3)
Number	1
Voltage input signal	0 V DC ... 30 V DC
Current input signal	2 mA ... 15 mA

### Output data

Output description	Digital output in accordance with IEC/EN 61131-2 (type 3)
Number	1
Current output signal	≤ 100 mA

### Device interface

Designation	Network interface
Communication protocol	Modbus/TCP
	REST
Connection method	RJ45

### General

Supply voltage	24 V DC ±25 %
Supply voltage range	18 V DC ... 30 V DC
Power consumption	< 4 W
Mains type	3-phase (3 or 4-conductor), 2-phase (2-conductor), and single-phase (1-conductor)
Color	gray
Conformance	CE-compliant
Test voltage	4 kV AC (50 Hz, 1 min.)
Product family	EMpro

### Connection data

Connection name	Current / voltage / supply
-----------------	----------------------------

## Measuring instrument - EEM-MB371-24DC - 1127055

### Technical data

#### Connection data

Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3
Conductor cross section solid	0.2 mm <sup>2</sup> ... 6 mm <sup>2</sup>
Conductor cross section flexible	0.2 mm <sup>2</sup> ... 4 mm <sup>2</sup>
Conductor cross section AWG	24 ... 10
Torque	0.5 Nm ... 0.6 Nm

#### Connection data 2

Connection name	Digital I/O / communication
Connection method	Screw connection
Stripping length	7 mm
Screw thread	M3
Conductor cross section solid	0.14 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross section flexible	0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross section AWG	26 ... 14
Torque	0.5 Nm ... 0.6 Nm

#### UL data

Operating mode	Indoor use
----------------	------------

#### Standards and Regulations

Conformance	CE-compliant
-------------	--------------

#### Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

### Classifications

#### eCl@ss

eCl@ss 10.0.1	27142330
eCl@ss 11.0	27142330
eCl@ss 8.0	27142330
eCl@ss 9.0	27142330

#### ETIM

ETIM 5.0	EC002301
----------	----------

### Approvals

#### Approvals

---

## Measuring instrument - EEM-MB371-24DC - 1127055

### Approvals

#### Approvals

UL Listed / cUL Listed / cULus Listed

---

#### Ex Approvals

---

### Approval details

UL Listed



<http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm> FILE E 357804

cUL Listed



<http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm> FILE E 357804

cULus Listed



### Accessories

#### Accessories

#### Mounting material

Holder - PACT RCP-CLAMP - 2904895



The optional holding device ensures the Rogowski coil is securely seated on busbars with a thickness of 10 ... 15 mm. During installation, the coil housing is pushed onto the flange of the holding device and snaps in automatically.

### Rogowski coil

Coil - PACT RCP-D95 - 2904890



300 mm long Rogowski coil. The measuring coil diameter when installed is 95 mm. The Rogowski coil is used for AC current measurement for busbars and power lines.

## Measuring instrument - EEM-MB371-24DC - 1127055

### Accessories

#### Coil - PACT RCP-D140 - 2904891

450 mm long Rogowski coil. The measuring coil diameter when installed is 140 mm. The Rogowski coil is used for AC current measurement for busbars and power lines.



---

#### Coil - PACT RCP-D190 - 2904892

600 mm long Rogowski coil. The measuring coil diameter when installed is 190 mm. The Rogowski coil is used for AC current measurement for busbars and power lines.



---

#### Coil - PACT RCP-D95-5M - 2910322

300 mm long Rogowski coil. The measuring coil diameter when installed is 95 mm. The Rogowski coil is used for AC current measurement for busbars and power lines.



---

#### Coil - PACT RCP-D95-10M - 2910323

300 mm long Rogowski coil. The measuring coil diameter when installed is 95 mm. The Rogowski coil is used for AC current measurement for busbars and power lines.



---

#### Coil - PACT RCP-D190-10M - 2910324

600 mm long Rogowski coil. The measuring coil diameter when installed is 190 mm. The Rogowski coil is used for AC current measurement for busbars and power lines.

