



2.2
kW


1 Yr
guarantee

UWS

10-15 Litre Unvented Water Storage Heaters

Application	Hot water storage
Key Features	High quality glass-lined tank Copper immersion element 2.20kW (240V) Large magnesium anode Unique ohmic resistance for a reinforced protection against corrosion CFC-free high density insulation foam Expansion relief valve Externally adjustable rod type thermostat Indicator light when operating Easy installation
Safety Features	Thermal cut-out manual reset
Capacities	10 and 15 litre
Rating	2.2kW @ 230V
Outer Casing	White plastic coated finish and corrosion resistant base and lid
Insulation	CFC-free high density foam
Heat Unit	Long-life copper sheathed elements
Anode	Large magnesium anode
Pressure	Operating pressure - 3 bar
Approvals	CE
Guarantee	1 year guarantee (UK)

Dimensions



Technical Specification

Electrical rating 2200W 240V or 2000W 230V | Weight when full (kg) - 10L - 17.5, 15L - 25 | Rated pressure 6 bar | Minimum recommended supply pressure 1.5 bar | 2 dielectric union | Electrical connection 230-240V AC 3kW (13 amps) is required

Product Variant	Dimensions (mm)					Nett Weight (kg)
	A	B	C	D	E	
UWS10	456	255	218	262	64	7
UWS15	496	287	218	294	70	9

Product Range

Product Reference	Short Code	Cat No.
UWS 10 Litre	UWS10	47784570
UWS 15 Litre	UWS15	47784571

