

Socket-outlet, New Unica, 2P+E, 16A, Italian, with shutter, white

NU302318

Main

Range	New Unica
Product or component type	Socket-outlet Socket-outlet
Device presentation	Mechanism
Device mounting	Flush
Socket number	1
Outlet poles configuration	2P + E
Outlet standard deviation	Italian
Rated current	16 A

Complementary

Device application	Power supply	
Cover type	With shutter	
[Ue] rated operational voltage	250 V	
Network type	AC	
Network frequency	50/60 Hz	
Number of modules	1 module	
Fixing mode	Clip-in	
Colour tint	White (RAL 9003)	
Connections - terminals	Screw terminals	
Cable cross section	04 mm² cable(s), 2 - cable stiffness: flexible 04 mm² - cable stiffness: rigid	
Minimum load breaking capacity	100 operations 1.25 In and 1.1 Un, cos phi = 0.6	
Electrical durability	10000 cycles, cos phi = 0.8	
Insulation resistance	> 5 MOhm at 500 V	
Dielectric strength	2000 V	
Material	PC: mechanism cover PC (polycarbonate) GF10 FR: casing	
Surface finish	Glossy	
Quantity per set	Set of 1 flow-pack	
Standards	IEC 60884-1	
Embedding depth	24 mm	
Depth	35.5 mm	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Width	22.5 mm	
Height	45 mm	
Net weight	0.0275 kg	
surface treatment	Untreated	
resistance to chemical agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane	

Environment

Ambient air temperature for operation	-535 °C
Ambient air temperature for storage	-550 °C
IK degree of protection	IK01
IP degree of protection	IP21D
Environmental characteristic	Bleach
	Liquid soap
	Acetone
	Window-cleaning fluid
	Alcohol
	Petrol
	Oil
	UV resistant

Packing Units

racking Office	
Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2 cm
Package 1 Width	3.5 cm
Package 1 Length	4.5 cm
Package 1 Weight	28 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	7 cm
Package 2 Width	12 cm
Package 2 Length	18.5 cm
Package 2 Weight	345 g
Unit Type of Package 3	S03
Number of Units in Package 3	160
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	5.908 kg



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

⊘ Environmental footprint	
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	1
Environmental Disclosure	Product Environmental Profile

Use Better

Minimum percentage of recycled plastic content	60
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No

Use Again

○ Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins