

M23-09P1N8AA500S - Device connector front mounting



1341930

<https://www.phoenixcontact.com/in/products/1341930>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Device connector front mounting, series: M23 PRO Signal, angled rotatable, shielded: yes, for standard and ONECLICK fast locking system, No. of pos.: 8+1, Direction of rotation: Standard, contact connection type: Pin, Crimp connection, flange dimensions: 26 mm x 26 mm, coding: N, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

Your advantages

- Solutions with cross-manufacturer compatibility for standard and fast locking systems
- Modern, consistent design for highly convenient operation
- Crimping connection: vibration- and temperature-resistant assembly
- All housing can be fitted with pin or socket contacts
- Safe use in the field, thanks to high degree of protection

Commercial data

Item number	1341930
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	*****
Product key	ABRABM
GTIN	4063151652005
Weight per piece (including packing)	117.4 g
Weight per piece (excluding packing)	117.4 g
Customs tariff number	85366990
Country of origin	DE

M23-09P1N8AA500S - Device connector front mounting



1341930

<https://www.phoenixcontact.com/in/products/1341930>

Technical data

Notes

Order information:	Order crimp contacts 8 x Ø 1 mm, 1 x Ø 2 mm separately
Notes on operation	Please observe the derating curve.

Safety note

Safety note	<p>WARNING: The connectors may not be plugged in or disconnected under load. Ignoring the warning or improper use may damage persons and/or property.</p> <ul style="list-style-type: none">• WARNING: Commission properly functioning products only. The products must be regularly inspected for damage. Decommission defective products immediately. Replace damaged products. Repairs are not possible.• WARNING: Only electrically qualified personnel may install and operate the product. They must observe the following safety notes. The qualified personnel must be familiar with the basics of electrical engineering. They must be able to recognize and prevent danger. The relevant symbol on the packaging indicates that only personnel familiar with electrical engineering are allowed to install and operate the product.• The products are suitable for applications in plant, controller, and electrical device engineering.• When operating the connectors in outdoor applications, they must be separately protected against environmental influences.• Assembled products may not be manipulated or improperly opened.• Only use mating connectors that are specified in the technical data of the standards listed (e.g. the ones listed in the product accessories online at phoenixcontact.com/products).• When using the product in direct connection with third-party manufacturers, the user is responsible.• For operating voltages > 50 V AC, conductive connector housings must be grounded• Ensure that the protective or functional ground has been properly connected.• VDE 0100/1.97 § 411.1.3.2 and DIN EN 60 204/11.98 § 14.1.3 are applicable when combining several circuits in a cable and/or connector• Only use tools recommended by Phoenix Contact• The installation notes/Design In documents online on the download page at phoenixcontact.com/products must be observed for this product.• Operate the connector only when it is fully plugged in and interlocked.• Ensure that when laying the cable, the tensile load on the connectors does not exceed the upper limit specified in the standards.• Observe the minimum bending radius of the cable. Lay the cable without twisting it.• The connector warms up in normal operation. Depending on the ambient conditions, the surface of the connector can continue to
-------------	-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

M23-09P1N8AA500S - Device connector front mounting



1341930

<https://www.phoenixcontact.com/in/products/1341930>

warm up. In this case, the user is responsible for posting warnings (e.g. DIN EN ISO 13732-1:2008-12).

Product properties

Product type	Circular connectors (device side)
--------------	-----------------------------------

Material specifications

Flammability rating according to UL 94	V0
----------------------------------------	----

Connector

Insulating body

Note	Order information: Order crimp contacts 8 x Ø 1 mm, 1 x Ø 2 mm separately
Coding	N
Insulation body material	PA 6.6
Insertion/withdrawal cycles	100
Connection method	Crimp connection
Contact switching type	Pin
Application	Signal
Number of positions	9
Direction of rotation	Standard
Connection profile	8+1
Contact diameter	2 mm
Litz wire cross-section	0.5 mm ²
Litz wire cross-section	2.5 mm ²
Rated current	20 A
Note	for max. connection cross section
Rated voltage	300 V
Rated surge voltage	2.5 kV
Overvoltage category	II
Degree of pollution	3
Contact diameter	1 mm
Litz wire cross-section	0.08 mm ²
Litz wire cross-section	1 mm ²
Nominal current per signal contact	8 A
Note	for max. connection cross section
Rated voltage Signal contact	300 V
Rated surge voltage	2.5 kV
Overvoltage category	II
Degree of pollution	3
Installation height	2000 m

M23-09P1N8AA500S - Device connector front mounting



1341930

<https://www.phoenixcontact.com/in/products/1341930>

Housing

Housing material	GD-Zn
Flange dimensions	26 mm x 26 mm
Type of locking	for standard and ONECLICK fast locking system
Pg screw connection	none
Degree of protection (plugged in)	IP66 / IP68 (2 m / 24 h)
Thread type	M23

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP68
Ambient temperature (operation)	-40 °C ... 105 °C (see to derating)
Permanent temperature	125 °C (DIN EN 60512-9-2 / 1000 h)


M23-09P1N8AA500S - Device connector front mounting

1341930

<https://www.phoenixcontact.com/in/products/1341930>

Drawings

Dimensional drawing




Installation dimensions

M23-09P1N8AA500S - Device connector front mounting

1341930

<https://www.phoenixcontact.com/in/products/1341930>

Schematic diagram




Connector pin assignment

M23-09P1N8AA500S - Device connector front mounting



1341930

<https://www.phoenixcontact.com/in/products/1341930>



I = current strength, θ = ambient temperature, 9x 8 A

M23-09P1N8AA500S - Device connector front mounting



1341930

<https://www.phoenixcontact.com/in/products/1341930>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/1341930>



cUL Recognized

Approval ID: E335019-20141210



UL Recognized

Approval ID: E335019-20141210

cULus Recognized

M23-09P1N8AA500S - Device connector front mounting



1341930

<https://www.phoenixcontact.com/in/products/1341930>

Classifications

ECLASS

ECLASS-11.0	27440109
ECLASS-12.0	27440109
ECLASS-13.0	27440109

ETIM

ETIM 9.0	EC003569
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

1341930
<https://www.phoenixcontact.com/in/products/1341930>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

M23-09P1N8AA500S - Device connector front mounting



1341930

<https://www.phoenixcontact.com/in/products/1341930>

Accessories

M23-Z0001 - Screw

1035117

<https://www.phoenixcontact.com/in/products/1035117>

Anchor screw, self-tapping, for M23-PRO series angled device connectors



RC-Z2220 - Contact insertion and removal tool

1604360

<https://www.phoenixcontact.com/in/products/1604360>

Positioning and removal tool for RC crimp contacts, pin/socket diameter: 2 mm



M23-09P1N8AA500S - Device connector front mounting



1341930

<https://www.phoenixcontact.com/in/products/1341930>

RC-Z2490 - Contact insertion and removal tool

1611803

<https://www.phoenixcontact.com/in/products/1611803>



Positioning and unlocking tool for RC crimp contacts (D-SUB) for pin/socket, diameter: 2 mm

RC-Z2097 - Contact insertion and removal tool

1604251

<https://www.phoenixcontact.com/in/products/1604251>



Insertion and removal tool for RC crimp contacts for pin/socket, diameter: 1 mm, connection cross-section: 0.08 mm² ... 0.56 mm²

M23-09P1N8AA500S - Device connector front mounting



1341930

<https://www.phoenixcontact.com/in/products/1341930>

RC-Z2494 - Contact insertion and removal tool

1614123

<https://www.phoenixcontact.com/in/products/1614123>



Positioning and removal tool for RC crimp contacts, pin/socket diameter: 1 mm

RC-5SP2000 - Crimp contact

1603529

<https://www.phoenixcontact.com/in/products/1603529>



Crimp contact, Pin, turned, contact diameter: 2 mm, crimp range: 0.5 mm² ... 0.75 mm², Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1241632

M23-09P1N8AA500S - Device connector front mounting



1341930

<https://www.phoenixcontact.com/in/products/1341930>

RC-59P2000 - Crimp contact

1603498

<https://www.phoenixcontact.com/in/products/1603498>



Crimp contact, Pin, turned, Single contact, contact diameter: 2 mm, crimp range: 0.75 mm² ... 1 mm², Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1241632

RC-5CP2000 - Crimp contact

1603513

<https://www.phoenixcontact.com/in/products/1603513>



Crimp contact, Pin, turned, contact diameter: 2 mm, crimp range: 1 mm² ... 1.5 mm², Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1241634

M23-09P1N8AA500S - Device connector front mounting



1341930

<https://www.phoenixcontact.com/in/products/1341930>

RC-5AP2000 - Crimp contact

1603505

<https://www.phoenixcontact.com/in/products/1603505>



Crimp contact, Pin, turned, contact diameter: 2 mm, crimp range: 1.5 mm² ... 2.5 mm², Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1241634

RC-11P2000 - Crimp contact

1596770

<https://www.phoenixcontact.com/in/products/1596770>



Crimp contact, Pin, turned, Single contact, contact diameter: 1 mm, crimp range: 0.08 mm² ... 0.22 mm², Contact release tool not necessary for the 12- and 17-pos. crimp versions of the M23-PRO series, Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1240882

M23-09P1N8AA500S - Device connector front mounting



1341930

<https://www.phoenixcontact.com/in/products/1341930>

RC-12P2000 - Crimp contact

1597862

<https://www.phoenixcontact.com/in/products/1597862>



Crimp contact, Pin, turned, Single contact, contact diameter: 1 mm, crimp range: 0.14 mm² ... 0.56 mm², Contact release tool not necessary for the 12- and 17-pos. crimp versions of the M23-PRO series, Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1240882

RC-1KP2000 - Crimp contact

1602996

<https://www.phoenixcontact.com/in/products/1602996>



Crimp contact, Pin, turned, Single contact, contact diameter: 1 mm, crimp range: 0.5 mm² ... 1 mm², Contact release tool not necessary for the 12- and 17-pos. crimp versions of the M23-PRO series, Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1241571

M23-09P1N8AA500S - Device connector front mounting



1341930

<https://www.phoenixcontact.com/in/products/1341930>

RC-22P2000 - Crimp contact

1603321

<https://www.phoenixcontact.com/in/products/1603321>



Crimp contact, Pin, rolled, Single contact, contact diameter: 1 mm, crimp range: 0.22 mm² ... 0.56 mm², Single contact, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

RC-22P2300 - Crimp contact

1603324

<https://www.phoenixcontact.com/in/products/1603324>



Crimp contact, Pin, rolled, Taped product, number of pieces per reel: 500, contact diameter: 1 mm, crimp range: 0.22 mm² ... 0.56 mm², Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

M23-09P1N8AA500S - Device connector front mounting



1341930

<https://www.phoenixcontact.com/in/products/1341930>

RC-22P2400 - Crimp contact

1603325

<https://www.phoenixcontact.com/in/products/1603325>



Crimp contact, Pin, rolled, Taped product, number of pieces per reel: 10000, contact diameter: 1 mm, crimp range: 0.22 mm² ... 0.56 mm², Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

RC-21P2000 - Crimp contact

1603310

<https://www.phoenixcontact.com/in/products/1603310>



Crimp contact, Pin, rolled, Single contact, contact diameter: 1 mm, crimp range: 0.08 mm² ... 0.22 mm², Single contact

M23-09P1N8AA500S - Device connector front mounting



1341930

<https://www.phoenixcontact.com/in/products/1341930>

RC-21P2300 - Crimp contact

1603313

<https://www.phoenixcontact.com/in/products/1603313>



Crimp contact, Pin, rolled, Taped product, number of pieces per reel: 500, contact diameter: 1 mm, crimp range: 0.08 mm² ... 0.22 mm²

RC-21P2400 - Crimp contact

1611637

<https://www.phoenixcontact.com/in/products/1611637>



Crimp contact, Pin, rolled, Taped product, number of pieces per reel: 10000, contact diameter: 1 mm, crimp range: 0.08 mm² ... 0.22 mm²

M23-09P1N8AA500S - Device connector front mounting

1341930

<https://www.phoenixcontact.com/in/products/1341930>

PROT-M23PRO-OT-IP20 - Plastic protective cap

1055753

<https://www.phoenixcontact.com/in/products/1055753>

Plastic protective cap, M23, series: M23 PRO



PROT-M23PRO-OT-IP67 - Plastic protective cap

1055749

<https://www.phoenixcontact.com/in/products/1055749>

Plastic protective cap, M23, series: M23 PRO Signal



M23-09P1N8AA500S - Device connector front mounting



1341930


<https://www.phoenixcontact.com/in/products/1341930>

M23PRO-VIB-ORING-GN - Sealing ring

1521138

<https://www.phoenixcontact.com/in/products/1521138>

Vibration O-ring, optional accessory for M23 PRO device connectors



M23PRO-VIB-ORING-OR - Sealing ring

1521137

<https://www.phoenixcontact.com/in/products/1521137>

Vibration O-ring, optional accessory for M23 PRO device connectors



Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.
A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420
info@phoenixcontact.co.in