

Parker Product Datasheet



Parker Legris PFA tubing offers 10 times greater durability than other fluoropolymer tubings under severe chemical and mechanical conditions. This tubing range is available in three material grades, offering perfect compatibility with all applications.

PART NUMBER: 1050T06P12
TUBE I.D. (MM): 4
LENGTH (M): 50
TUBE O.D. (MM): 6
TUBING MATERIAL: PFA COLOURED
COLOR: GREEN CRYSTAL

PRODUCT OVERVIEW

Parker Legris PFA tubing offers 10 times greater durability than other fluoropolymer tubings under severe chemical and mechanical conditions. This tubing range is available in three material grades, offering perfect compatibility with all applications.

Features/Benefits:

- Great Versatility

- Exceptional chemical inertia

- A flexible alternative to stainless steel tubing
- Broad range of working temperatures, from cryogenic to extreme heat
- Non-stick properties allowing conveyance of many fluids & gases
- Outstanding resistance to ageing
- Fluoropolymer with the lowest permeability
- Non-flammable
- UV-transparent
- Tube marking on request
- Silicone-free

- Three Material Grades

- Clear PFA: to cover all applications, including those requiring maximum mechanical resistance
- Colored PFA: for circuit identification
- Black Antistatic PFA: eliminates all risk of electrostatic discharge

Markets:

- Food and Beverage
- Power Generation Equipment
- Aircraft
- Pharmaceutical
- Medical
- Oil and Gas

Applications:

- Applications Subjected to Severe Mechanical and Chemical Conditions
- Medical Fluids Conveying
- Gas and Compressed Air Conveying
- Applications Requiring Very Low and High Temperature
- Fire Hazard Zones
- Applications Subjected to Intensive Cleaning
- Suitable for Fuel Cells and Clean Rooms
- Thermal Management

Technologies:

- Fluoropolymer Tubing
- PFA Tubing
- Perfluoro alkoxy Tubing
- Anti Static Tubing
- Industrial Tubing

TECH SPECIFICATIONS

SPECIFICATIONS MET

REACH 1907/2006 (Industrial)

MEDIA

Compressed Air

APPLICATION

Pharmaceutical

MAXIMUM OPERATING TEMPERATURE	150 °C See the Graph “Working Pressure/Working Temperature”
MEDIA	Food & Beverage
APPLICATION	Oil & Gas
APPLICATION	Chemicals
APPLICATION	Food Processing
SPECIFICATIONS MET	PED 97/23/EC (Industrial)
MEDIA	Medical Fluids
SPECIFICATIONS MET	RoHS 2002/95/EC, 2011/65/EC (Industrial)
APPLICATION	Aircraft
APPLICATION	Clean Rooms
MINIMUM OPERATING TEMPERATURE	-40 °C
SPECIFICATIONS MET	FDA 21 CFR 177.1550 (clear)
MAXIMUM OPERATING PRESSURE	33 bar
MEDIA	Industrial Gases
APPLICATION	Medical
SPECIFICATIONS MET	UL 94 V-0 (Fire Resistance, Industrial)
SPECIFICATIONS MET	USP Class VI (A). Medical: External Communication Devices
DIVISION	Low Pressure Connectors Europe Division
WEIGHT	1.751 kg/package
VACUUM PRESSURE RATING	755 mm-Hg