



Field-wireable connectors

Field-wireable connectors ensure high flexibility in device installation

SICK
Sensor Intelligence.



Product description

SICK now also offers field-wireable plug connectors with insulation displacement contact (IDC) technology. An enormous advantage: Installation of these plug connectors is simple and saves time. And they work just as reliably as the proven SICK plug connectors with screw terminals.

At a glance

- Variants available for relevant solution segments: Signal, data and cable transmission
- Displacement and spring clamp, screw, solder or crimp connection possible
- Demanding applications: Leak tightness up to IP69 and addressable stainless steel housing
- Comprehensive portfolio of M8, M12, M16 and M23 plug connectors

Your benefits

- Flexibility – Choice of different connection technologies
- Performance – Equivalent transmission of signals, data and power compared to encapsulated plug connectors
- Simplicity – Ability to reduce complex inventory by implementing the wiring solution in the field

Ordering information

Other models and accessories → www.sick.com/Field-wireable_connectors

- **Connection type head A:** female connector, DIN 43650, 4-pin, angled

Description	Connection systems	Permitted cross-section	Type	Part no.
Unshielded	Screw-type terminals	0.14 mm ² ... 0.5 mm ²	DOS-0303-W	6005698

- **Connection type head A:** female connector, M26, 7-pin, angled, A-coded

Description	Connection systems	Permitted cross-section	Type	Part no.
Unshielded	Screw contacts	0.5 mm ² ... 1.5 mm ²	DOS-0607W000IA3KU0	6007363

- **Connection type head A:** female connector, M26, 12-pin, straight, A-coded
- **Description:** unshielded
- **Connection systems:** crimp contacts

Permitted cross-section	Note	Type	Part no.
0.5 mm ² ... 1.5 mm ²	12 crimping contacts enclosed	DOS-0612G000GA3KM0	6020757
≤ 0.5 mm ²	LABS-free	DOS-0612G000GA3KM6	6053198

- **Connection type head A:** female connector, M8, 3-pin, angled, A-coded
- **Description:** unshielded

Connection systems	Permitted cross-section	Type	Part no.
Screw-type terminals	0.14 mm ² ... 0.5 mm ²	DOS-0803-WSK	6053168
Solder connection	≤ 0.25 mm ²	DOS-0803-W	7902078

- **Connection type head A:** female connector, M8, 4-pin, angled, A-coded
- **Description:** unshielded

Connection systems	Permitted cross-section	Type	Part no.
Screw-type terminals	0.14 mm ² ... 0.5 mm ²	DOS-0804-WSK	6053169
Solder connection	≤ 0.25 mm ²	DOS-0804-W	6009975

- **Connection type head A:** female connector, M12, 4-pin, straight, A-coded
- **Description:** unshielded

Connection systems	Permitted cross-section	Application	Type	Part no.
Cutting technology	0.14 mm ² ... 0.34 mm ²	–	DOS-1204-GQU6	6042088
	0.34 mm ² ... 0.75 mm ²	–	DOS-1204-GQU8	6053328
Screw-type terminals	≤ 0.75 mm ²	–	DOS-1204-G	6007302
		–	DOS-1204-GX	6026528
		Hygienic and washdown zones	DOS-1204-GN	6028357

- **Connection type head A:** female connector, M12, 4-pin, straight, D-coded
- **Signal type:** PROFINET

Cable	Description	Connection systems	Permitted cross-section	Type	Part no.
CAT5, CAT5e	PROFINET, shielded	IDC quick connection	0.14 mm² ... 0.34 mm²	DOS-1204-GZ	6048263

- **Connection type head A:** female connector, M12, 4-pin, angled, A-coded
- **Description:** unshielded
- **Connection systems:** screw-type terminals
- **Permitted cross-section:** ≤ 0.75 mm²

Application	Type	Part no.
–	DOS-1204-W	6007303
	DOS-1204-WX	6025570
Hygienic and washdown zones	DOS-1204-WN	6028358

- **Connection type head A:** female connector, M12, 4-pin, angled, D-coded
- **Signal type:** PROFINET

Cable	Description	Connection systems	Permitted cross-section	Type	Part no.
CAT5, CAT5e	PROFINET, shielded	IDC quick connection	0.14 mm² ... 0.34 mm²	DOS-1204-WZ	6048264

- **Connection type head A:** female connector, M12, 8-pin, straight, A-coded
- **Connection systems:** screw-type terminals
- **Permitted cross-section:** 0.25 mm² ... 0.5 mm²

Description	Application	Type	Part no.
Shielded	–	DOS-1208-GA	6028369
	Hygienic and washdown zones	YF12ES8-0050S5586A	2097334
Unshielded	–	DOS-1208-G	6028422

- **Connection type head A:** female connector, M12, 8-pin, angled, A-coded

Description	Connection systems	Permitted cross-section	Type	Part no.
Unshielded	Screw-type terminals	0.25 mm² ... 0.5 mm²	DOS-1208-W	2092035

- **Connection type head A:** male connector, M8, 3-pin, angled, A-coded

Description	Connection systems	Permitted cross-section	Type	Part no.
Unshielded	Screw-type terminals	0.14 mm² ... 0.5 mm²	STE-0803-WSK	6053170

- **Connection type head A:** male connector, M8, 4-pin, straight, A-coded
- **Description:** unshielded

Connection systems	Permitted cross-section	Type	Part no.
Piercecon fast connection	–	STE-0804-GPC	6042091
Screw-type terminals	0.14 mm ² ... 0.5 mm ²	STE-0804-G	6037323

- **Connection type head A:** male connector, M8, 4-pin, angled, A-coded

Description	Connection systems	Permitted cross-section	Type	Part no.
Unshielded	Screw-type terminals	0.14 mm ² ... 0.5 mm ²	STE-0804-WSK	6053171

- **Connection type head A:** male connector, RJ45, 4-pin, straight
- **Signal type:** Ethernet, PROFINET

Cable	Description	Connection systems	Permitted cross-section	Type	Part no.
CAT5, CAT5e	Ethernet, shielded PROFINET	IDC quick connection	4 mm ² ... 8 mm ²	STE-0J04-GZ	6048260

- **Connection type head A:** male connector, M12, 4-pin, straight, D-coded
- **Signal type:** Ethernet, PROFINET

Description	Connection systems	Permitted cross-section	Application	Type	Part no.
Ethernet, shielded PROFINET	Spring-cage connection	≤ 0.5 mm ²	Hygienic and wash-down zones	STE-1204-GE	6032802

- **Connection type head A:** male connector, M12, 4-pin, straight, A-coded

Description	Connection systems	Permitted cross-section	Note	Application	Type	Part no.
–	Cutting technology	0.14 mm ² ... 0.34 mm ²	Test voltage 1.25 kV eff/60 s, insulation group C to VDE 0110, for field bus technology	–	STE-1204-GQU6	6042089
Unshielded	Cutting technology	0.34 mm ² ... 0.75 mm ²	–	–	STE-1204-GQU8	6044998
	Screw-type terminals	≤ 0.75 mm ²	–	–	STE-1204-G	6009932
				Hygienic and wash-down zones	STE-1204-GN	6028359
				For 2 cable connections	STE-1204-TN	6028360

- **Connection type head A:** male connector, M12, 4-pin, straight, D-coded
- **Signal type:** PROFINET
- **Description:** PROFINET, shielded

Cable	Connection systems	Permitted cross-section	Type	Part no.
–	–	–	Male connector (ready to assemble)	6047860
CAT5, CAT5e	IDC quick connection	0.14 mm ² ... 0.34 mm ²	STE-1204-GZ	6048261

- **Connection type head A:** male connector, M12, 4-pin, angled, D-coded
- **Signal type:** PROFINET

Cable	Description	Connection systems	Permitted cross-section	Type	Part no.
CAT5, CAT5e	PROFINET, shielded	IDC quick connection	0.14 mm ² ... 0.34 mm ²	STE-1204-WZ	6048262

- **Connection type head A:** male connector, M12, 8-pin, straight, A-coded
- **Connection systems:** screw-type terminals

Description	Permitted cross-section	Note	Application	Type	Part no.
Shielded	≤ 0.5 mm ²	–	–	STE-1208-GA	6028370
			Hygienic and wash-down zones	YM12ES8-0050S5586A	2097337
Unshielded	0.25 mm ² ... 0.5 mm ²	For field bus technology	–	STE-1208-G	6033269

- **Connection type head A:** male connector, M12, 8-pin, angled, B-coded

Description	Connection systems	Permitted cross-section	Note	Type	Part no.
Unshielded	Screw-type terminals	0.25 mm ² ... 0.5 mm ²	For field bus technology	STE-1208-W	2092036

- **Connection type head A:** male connector, M12, 8-pin, straight, X-coded
- **Signal type:** Ethernet

Description	Connection systems	Type	Part no.
Ethernet	Piercecon fast connection	MALE CONNECTOR,YL.LTG.SK 8P. M12 CAT6A IP67	6054376

- **Connection type head A:** female connector, M8, 3-pin, straight, A-coded
- **Signal type:** Sensor/actuator cable

Description	Connection systems	Permitted cross-section	Type	Part no.
Sensor/actuator cable	IDC quick connection	0.14 mm ² ... 0.34 mm ²	YF08U13-1434K2551A	2109288

- **Connection type head A:** female connector, M8, 4-pin, straight, A-coded
- **Signal type:** Sensor/actuator cable

Description	Connection systems	Permitted cross-section	Type	Part no.
Sensor/actuator cable	IDC quick connection	0.14 mm ² ... 0.34 mm ²	YF08U14-1434K2551A	2109289

- **Connection type head A:** female connector, M12, 5-pin, straight, A-coded
- **Connection systems:** screw-type terminals
- **Permitted cross-section:** ≤ 0.75 mm²

Description	Note	Application	Type	Part no.
Shielded	–	Hygienic and washdown zones	YF12ES5-0075S5586A	2097335
Unshielded	–	–	DOS-1205-G	6009719
	Test voltage 1.0 kV eff/60 s, insulation group C to VDE 0110	–	DOS-1205-GX	6047950

- **Connection type head A:** female connector, M12, 4-pin, straight, L-coded

Description	Connection systems	Permitted cross-section	Type	Part no.
Unshielded	Screw-type terminals	1.5 mm ² ... 2.5 mm ²	YF12PA5-0003S0003L	2141091

- **Connection type head A:** female connector, M12, 3-pin, straight, A-coded
- **Signal type:** Sensor/actuator cable

Description	Connection systems	Permitted cross-section	Application	Type	Part no.
Sensor/actuator cable	IDC quick connection	0.25 mm ² ... 0.5 mm ²	Zones with oils and lubricants	YF12U13-2550K4051A	2109292

- **Connection type head A:** female connector, M12, 4-pin, straight, A-coded
- **Signal type:** Sensor/actuator cable

Description	Connection systems	Permitted cross-section	Application	Type	Part no.
Sensor/actuator cable	IDC quick connection	0.25 mm ² ... 0.5 mm ²	Zones with oils and lubricants	YF12U14-2550K4051A	2109293

- **Connection type head A:** female connector, M12, 3-pin, angled, A-coded
- **Signal type:** Sensor/actuator cable
- **Description:** Sensor/actuator cable
- **Connection systems:** IDC quick connection
- **Permitted cross-section:** 0.25 mm² ... 0.5 mm²
- **Application:** Zones with oils and lubricants

Type	Part no.
YG12U13-2550K4051A	2109296
YI12U13-2550K4051A	2109297

- **Connection type head A:** female connector, M12, 4-pin, angled, A-coded
- **Signal type:** Sensor/actuator cable
- **Description:** Sensor/actuator cable
- **Connection systems:** IDC quick connection
- **Permitted cross-section:** 0.25 mm² ... 0.5 mm²
- **Application:** Zones with oils and lubricants

Type	Part no.
YG12U14-2550K4051A	2109298
YI12U14-2550K4051A	2109299

- **Connection type head A:** male connector, M8, 3-pin, straight, A-coded
- **Signal type:** Sensor/actuator cable
- **Description:** Sensor/actuator cable
- **Connection systems:** IDC quick connection

Permitted cross-section	Type	Part no.
0.08 mm ² ... 0.25 mm ²	YM08U13-0002K1823A	2122277
0.14 mm ² ... 0.34 mm ²	YM08U13-1434K2551A	2109286

- **Connection type head A:** male connector, M8, 4-pin, straight, A-coded
- **Signal type:** Sensor/actuator cable

Description	Connection systems	Permitted cross-section	Type	Part no.
Sensor/actuator cable	IDC quick connection	0.14 mm ² ... 0.34 mm ²	YM08U14-1434K2551A	2109287

- **Connection type head A:** male connector, M12, 4-pin, straight, D-coded

Description	Connection systems	Permitted cross-section	Application	Type	Part no.
Shielded	Screw-type terminals	≤ 0.75 mm ²	Hygienic and wash-down zones	YM12ES4-0075S5586D	2109773

- **Connection type head A:** male connector, M12, 5-pin, straight, A-coded

Description	Connection systems	Permitted cross-section	Note	Application	Type	Part no.
Shielded	Screw-type terminals	≤ 0.75 mm ²	–	Hygienic and wash-down zones	YM12ES5-0075S5586A	2097336
Unshielded	Spring-cage connection	0.14 mm ² ... 0.5 mm ²	Test voltage 1.25 kV eff/60 s, insulation group C to VDE 0110	–	STE-1205-GFE	6044999
	Screw-type terminals	≤ 0.75 mm ²	For field bus technology	–	STE-1205-G	6022083

- **Connection type head A:** male connector, M12, 4-pin, straight, L-coded

Description	Connection systems	Permitted cross-section	Type	Part no.
Unshielded	Screw-type terminals	1.5 mm ² ... 2.5 mm ²	YM12PA5-0003S0003L	2141090

- **Connection type head A:** male connector, M12, 3-pin, straight, A-coded
- **Signal type:** Sensor/actuator cable

Description	Connection systems	Permitted cross-section	Application	Type	Part no.
Sensor/actuator cable	IDC quick connection	0.25 mm ² ... 0.5 mm ²	Zones with oils and lubricants	YM12U13-2550K4051A	2109290

- **Connection type head A:** male connector, M12, 4-pin, straight, A-coded
- **Signal type:** Sensor/actuator cable
- **Description:** Sensor/actuator cable
- **Connection systems:** IDC quick connection

Permitted cross-section	Application	Type	Part no.
0.14 mm ² ... 0.34 mm ²	–	YM12U14-1434K2951A	2115540
0.25 mm ² ... 0.5 mm ²	Zones with oils and lubricants	YM12U14-2550K4051A	2109291

- **Connection type head A:** male connector, M12, 3-pin, angled, A-coded
- **Signal type:** Sensor/actuator cable

Description	Connection systems	Permitted cross-section	Application	Type	Part no.
Sensor/actuator cable	IDC quick connection	0.25 mm ² ... 0.5 mm ²	Zones with oils and lubricants	YN12U13-2550K4051A	2109294

- **Connection type head A:** male connector, M12, 4-pin, angled, A-coded
- **Signal type:** Sensor/actuator cable

Description	Connection systems	Permitted cross-section	Application	Type	Part no.
Sensor/actuator cable	IDC quick connection	0.25 mm ² ... 0.5 mm ²	Zones with oils and lubricants	YN12U14-2550K4051A	2109295

- **Connection type head A:** female connector, M8, 3-pin, straight, A-coded
- **Description:** unshielded

Connection systems	Permitted cross-section	Type	Part no.
Piercecon fast connection	–	DOS-0803-GPC	6042092
Screw-type terminals	0.14 mm ² ... 0.5 mm ²	DOS-0803-G	7902077

- **Connection type head A:** male connector, M8, 3-pin, straight, A-coded
- **Description:** unshielded

Connection systems	Permitted cross-section	Type	Part no.
Piercecon fast connection	–	STE-0803-GPC	6042093
Screw-type terminals	0.14 mm ² ... 0.5 mm ²	STE-0803-G	6037322

- **Connection type head A:** female connector, M8, 4-pin, straight, A-coded
- **Description:** unshielded

Connection systems	Permitted cross-section	Type	Part no.
Piercecon fast connection	–	DOS-0804-GPC	6042090
Screw-type terminals	0.14 mm ² ... 0.5 mm ²	DOS-0804-G	6009974

- **Connection type head A:** male connector, 7/8", 5-pin, straight, A-coded
- **Signal type:** DeviceNet™, CANopen

Description	Permitted cross-section	Note	Type	Part no.
DeviceNet™, shielded CANopen	≤ 1.5 mm ²	For field bus technology	STE-7805-GK	6028332

- **Connection type head A:** female connector, M16, 8-pin, straight, A-coded

Description	Connection systems	Type	Part no.
Shielded	Solder connection	DOS-1608-GA	6025726

- **Connection type head A:** male connector, M12, 4-pin, angled, A-coded

Description	Connection systems	Permitted cross-section	Type	Part no.
Unshielded	Screw-type terminals	≤ 0.75 mm ²	STE-1204-W	6022084

- **Connection type head A:** female connector, M16, 8-pin, angled, A-coded

Description	Connection systems	Type	Part no.
Shielded	Solder connection	DOS-1608-WA	6025727

- **Connection type head A:** female connector, M12, 5-pin, angled, A-coded
- **Description:** unshielded

Connection systems	Permitted cross-section	Note	Type	Part no.
–	–	Test voltage 1.0 kV eff/60 s, insulation group C to VDE 0110	DOS-1205-WX	6047951
Screw-type terminals	≤ 0.75 mm ²	–	DOS-1205-W	6009720

- **Connection type head A:** male connector, M12, 5-pin, straight, B-coded
- **Signal type:** PROFIBUS DP

Description	Connection systems	Permitted cross-section	Type	Part no.
PROFIBUS DP, shielded	Screw-type terminals	≤ 0.75 mm ²	STE-1205-GQ	6021354

- **Connection type head A:** female connector, M16, 12-pin, angled, A-coded
- **Permitted cross-section:** $\leq 0.25 \text{ mm}^2$

Description	Type	Part no.
Shielded	DOS-1612-WA	6022370
Unshielded	DOS-1612-W	6007988

- **Connection type head A:** male connector, M12, 5-pin, angled, A-coded

Description	Connection systems	Permitted cross-section	Note	Type	Part no.
Unshielded	Screw-type terminals	$\leq 0.75 \text{ mm}^2$	For field bus technology	STE-1205-W	6022082

- **Connection type head A:** female connector, M12, 5-pin, straight, B-coded
- **Signal type:** PROFIBUS DP

Description	Connection systems	Permitted cross-section	Type	Part no.
PROFIBUS DP, shielded	Screw-type terminals	$\leq 0.75 \text{ mm}^2$	DOS-1205-GQ	6021353

- **Connection type head A:** female connector, M18, 4-pin, angled, X-coded

Description	Type	Part no.
Unshielded	DOS-1804-W	6009437

- **Connection type head A:** male connector, M26, 12-pin, straight, A-coded

Description	Connection systems	Permitted cross-section	Note	Type	Part no.
Unshielded	Crimp contacts	0.5 mm ² ... 1.5 mm ²	12 crimping contacts enclosed	STE-0612G000GA3KM0	6021191

- **Connection type head A:** female connector, M12, 4-pin, straight, D-coded
- **Signal type:** Ethernet

Cable	Description	Connection systems	Permitted cross-section	Type	Part no.
CAT5, CAT5e	Ethernet, shielded	IDC quick connection	0.14 mm ² ... 0.34 mm ²	DOS-1204-GE	6048153

- **Connection type head A:** male connector, M26, 12-pin, angled, A-coded

Description	Connection systems	Permitted cross-section	Note	Type	Part no.
Unshielded	Crimp contacts	0.5 mm ² ... 1.5 mm ²	12 crimping contacts enclosed	STE-0612W000GA3KM0	6021192

- **Connection type head A:** female connector, M12, 4-pin, angled, D-coded
- **Signal type:** Ethernet

Cable	Description	Connection systems	Permitted cross-section	Type	Part no.
CAT5, CAT5e	Ethernet, shielded	IDC quick connection	0.14 mm ² ... 0.34 mm ²	DOS-1204-WE	6048154

- **Connection type head A:** female connector, M12, 8-pin, angled, A-coded
- **Signal type:** Ethernet

Cable	Description	Connection systems	Permitted cross-section	Type	Part no.
CAT5, CAT5e	Ethernet, shielded	QUICKON connection	0.14 mm ² ... 0.34 mm ²	DOS-1208-WA	6043358

- **Connection type head A:** female connector, Q6, 6-pin, angled, DC-coded

Description	Connection systems	Permitted cross-section	Type	Part no.
Unshielded	Solder connection	0.14 mm ² ... 0.5 mm ²	DOS-1306-W	6006710

- **Connection type head A:** male connector, M12, 4-pin, straight, D-coded
- **Signal type:** Ethernet

Cable	Description	Connection systems	Permitted cross-section	Type	Part no.
CAT5, CAT5e	Ethernet, shielded	IDC quick connection	0.14 mm ² ... 0.34 mm ²	STE-1204-GE01	6048151

- **Connection type head A:** female connector, M12, 5-pin, straight, A-coded
- **Signal type:** CANopen, DeviceNet™

Description	Connection systems	Permitted cross-section	Type	Part no.
CANopen, shielded DeviceNet™	Screw-type terminals	≤ 0.75 mm ²	DOS-1205-GA	6027534

- **Connection type head A:** female connector, Q6, 6-pin, angled, AC-coded

Description	Connection systems	Permitted cross-section	Type	Part no.
Unshielded	Solder connection	0.14 mm ² ... 0.5 mm ²	DOS-1406-W	6006685

- **Connection type head A:** male connector, M12, 4-pin, angled, D-coded
- **Signal type:** Ethernet

Cable	Description	Connection systems	Permitted cross-section	Type	Part no.
CAT5, CAT5e	Ethernet, shielded	IDC quick connection	0.14 mm ² ... 0.34 mm ²	STE-1204-WE	6048152

- **Connection type head A:** female connector, M12, 5-pin, angled, B-coded
- **Signal type:** PROFIBUS DP

Description	Connection systems	Permitted cross-section	Type	Part no.
PROFIBUS DP, shielded	Spring-cage connection	0.14 mm ² ... 0.5 mm ²	DOS-1205-WQ	6041429

- **Connection type head A:** female connector, Q7, 7-pin, angled, DC-coded

Description	Connection systems	Permitted cross-section	Type	Part no.
Unshielded	Screw-type terminals	0.25 mm ² ... 1 mm ²	DOS-2107-W	6006823

- **Connection type head A:** male connector, M12, 8-pin, straight, A-coded
- **Signal type:** Incremental

Cable	Description	Connection systems	Permitted cross-section	Type	Part no.
CAT5, CAT5e	Incremental, shielded	IDC quick connection	0.14 mm ² ... 0.34 mm ²	STE-1208-GA01	6044892

- **Connection type head A:** female connector, Q7, 7-pin, angled, AC-coded

Description	Connection systems	Permitted cross-section	Type	Part no.
Unshielded	Screw-type terminals	0.25 mm ² ... 1 mm ²	DOS-2207-W	6006821

- **Connection type head A:** male connector, M12, 5-pin, straight, A-coded
- **Signal type:** CANopen, DeviceNet™

Description	Connection systems	Permitted cross-section	Type	Part no.
CANopen, shielded DeviceNet™	Screw-type terminals	≤ 0.75 mm ²	STE-1205-GA	6027533

- **Connection type head A:** female connector, 7/8", 5-pin, straight, A-coded
- **Signal type:** DeviceNet™, CANopen

Description	Permitted cross-section	Type	Part no.
DeviceNet™, shielded CANopen	≤ 1.5 mm ²	DOS-7805-GK	6028331

- **Connection type head A:** male connector, M12, 5-pin, angled, B-coded
- **Signal type:** PROFIBUS DP

Description	Connection systems	Permitted cross-section	Type	Part no.
PROFIBUS DP, shielded	Spring-cage connection	0.14 mm ² ... 0.5 mm ²	STE-1205-WQ	6041428

- **Connection type head A:** female connector, M26, 7-pin, straight, A-coded

Description	Connection systems	Permitted cross-section	Note	Type	Part no.
Unshielded	Crimp contacts	0.5 mm² ... 1.5 mm²	7 crimping contacts enclosed	DOS-0607G000GA3KM0	6006612

- **Connection type head A:** female connector, M26, 12-pin, angled, A-coded

Description	Connection systems	Permitted cross-section	Note	Type	Part no.
Unshielded	Crimp contacts	0.5 mm² ... 1.5 mm²	12 crimping contacts enclosed	DOS-0612W000GA3KM0	6020758

- **Connection type head A:** male connector, RJ45, 8-pin, straight
- **Signal type:** Gigabit Ethernet

Cable	Description	Connection systems	Permitted cross-section	Type	Part no.
CAT6A	Gigabit Ethernet, shielded	IDC quick connection	4.5 mm² ... 8 mm²	STE-0J08-GE	6048150

- **Connection type head A:** female connector, M23, 9-pin, straight, A-coded
- **Signal type:** HIPERFACE®, SSI, Incremental

Description	Connection systems	Type	Part no.
HIPERFACE®, shielded SSI Incremental	Solder connection	DOS-2309-G	6028533

- **Connection type head A:** female connector, M23, 12-pin, straight, A-coded
- **Signal type:** HIPERFACE®, SSI, Incremental
- **Description:** HIPERFACE®, shielded, SSI, Incremental
- **Connection systems:** solder connection

Type	Part no.
DOS-2312-G	6027538
DOS-2312-G02	2077057
DOS-2312-GS02	2071778

- **Connection type head A:** female connector, M23, 12-pin, angled, A-coded
- **Signal type:** HIPERFACE®, SSI, Incremental

Description	Connection systems	Type	Part no.
HIPERFACE®, shielded SSI Incremental	Solder connection	DOS-2312-W01	2072580

- **Connection type head A:** female connector, M12, 7-pin, straight, A-coded

Description	Connection systems	Permitted cross-section	Type	Part no.
Unshielded	Screw-type terminals	$\leq 1.5 \text{ mm}^2$	Connector	6049886

- **Connection type head A:** female connector, MS/06, 6-pin, straight, A-coded

Description	Type	Part no.
Unshielded	DOS-MS06-G	7102136

- **Connection type head A:** female connector, MS/07, 7-pin, straight, A-coded

Description	Type	Part no.
Unshielded	DOS-MS07-G	7102143

Type	Part no.
RLYO-ACC0100	6059567
RLYO-ACC0300	6072328
RLYO-ACC0400	6072329
RLYO-ACC0500	6072331

- **Connection type head A:** male connector, M23, 12-pin, straight, A-coded
- **Signal type:** HIPERFACE[®], SSI, Incremental
- **Description:** HIPERFACE[®], shielded, SSI, Incremental
- **Connection systems:** solder connection

Type	Part no.
STE-2312-G01	2077273
STE-2312-GX	6028548

- **Connection type head A:** male connector, M12, 7-pin, straight, A-coded

Description	Permitted cross-section	Type	Part no.
Unshielded	$\leq 1.5 \text{ mm}^2$	Male connector	6049036

- **Connection type head A:** male connector, R16, A-coded

Description	Type	Part no.
Unshielded	STE-2606	6004193

- **Connection type head A:** female connector, M16, 12-pin, straight, A-coded

Description	Permitted cross-section	Type	Part no.
Shielded	$\leq 0.25 \text{ mm}^2$	DOS-1612-GA	6022369

- **Connection type head A:** male connector, 7/8", 4-pin, straight, A-coded

Description	Permitted cross-section	Note	Type	Part no.
Unshielded	≤ 1.5 mm²	Auxiliary power supply	Male connector	6030804

- **Connection type head A:** female connector, M18, 4-pin, straight, X-coded

Description	Type	Part no.
Unshielded	DOS-1804-G	6009436

- **Connection type head A:** male connector, M23, 12-pin, straight, B-coded

Description	Connection systems	Permitted cross-section	Note	Type	Part no.
Unshielded	Crimp contacts	0.08 mm² ... 0.82 mm²	SDL connection	Interconnectron male connector	6024742

- **Connection type head A:** female connector, M12, 8-pin, straight, A-coded
- **Signal type:** Incremental, SSI

Cable	Description	Connection systems	Permitted cross-section	Type	Part no.
CAT5, CAT5e	Incremental, shielded SSI	IDC quick connection	0.14 mm² ... 0.34 mm²	DOS-1208-GA01	6045001

- **Connection type head A:** male connector, D-Sub
- **Signal type:** PROFIBUS DP

Description	Type	Part no.
PROFIBUS DP, unshielded	PROFIBUS male connector	6029030

- **Connection type head A:** male connector, RJ45, 4-pin

Description	Type	Part no.
Unshielded	Male connector (ready to assemble)	6028386

- **Connection type head A:** female connector, 7/8", 5-pin, straight, A-coded

Cable	Description	Type	Part no.
AWG16	Unshielded	Female connector (ready to assemble)	6045310

- **Connection type head A:** female connector, MS/10, 10-pin, straight, A-coded

Description	Type	Part no.
Unshielded	DOS-MS10-G	7102129

- **Connection type head A:** female connector, M14, 7-pin, straight, A-coded
- **Signal type:** PROFIBUS DP, PROFIBUS DP, PROFIBUS DP

Description	Connection systems	Type	Part no.
PROFIBUS DP, shielded PROFIBUS DP PROFIBUS DP	Solder connection	DOS-1507-G	6027536

- **Connection type head A:** male connector, M14, 7-pin, straight, A-coded
- **Signal type:** PROFIBUS DP

Description	Connection systems	Type	Part no.
PROFIBUS DP, shielded	Solder connection	STE-1507-G	6027535

- **Connection type head A:** female connector, M23, 21-pin, straight, A-coded
- **Signal type:** SSI

Description	Connection systems	Type	Part no.
SSI, shielded	Crimp contacts	DOS-2321-G	6027539

- **Connection type head A:** male connector, M23, 12-pin, straight, A-coded
- **Signal type:** HIPERFACE[®], SSI, Incremental, RS-422

Description	Connection systems	Type	Part no.
HIPERFACE [®] , shielded SSI Incremental RS-422	Solder connection	STE-2312-G	6027537

- **Connection type head A:** female connector, D-Sub, 37-pin, straight
- **Signal type:** SSI

Description	Type	Part no.
SSI, shielded	DOS-0D37-G	2029224

- **Connection type head A:** male connector, D-Sub, 15-pin, straight
- **Signal type:** SSI

Description	Connection systems	Type	Part no.
SSI, shielded	Solder connection	STE-0D15-G	2029223

- **Connection type head A:** male connector, 12-pin
- **Connection type head B:** terminal connector, 12-pin

Description	Connection systems	Note	Type	Part no.
Unshielded	Spring terminal	Terminal strip for AOD5-P/N1 (OD Precision)	TERM.-AOD5	6035989

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

WORLDWIDE PRESENCE:

Contacts and other locations –www.sick.com