



Technical Datasheet

Dräger X-plore 8000

Standard hoods (Short & Long)

1. General Data

1.1	Manufacturer	Dräger Safety AG & Co. KGaA Revalstraße 1, D – 23 560 Luebeck, Germany
1.2	Designation	Dräger X-plore 8000 Standard hood
1.3	Dräger part no.	
	R59800	Dräger X-plore 8000 Standard hood short (S/M)
	R59810	Dräger X-plore 8000 Standard hood short (L/XL)
	R59820	Dräger X-plore 8000 Standard hood long (S/M)
	R59830	Dräger X-plore 8000 Standard hood long (L/XL)
1.4	GTIN / EAN	
	R59800	04026056008711
	R59810	04026056008742
	R59820	04026056008759
	R59830	04026056008766
1.5	Intended use	The X-plore® 8000 standard hood serves as a facepiece for the use with the Powered Air-Purifying Respirator Dräger X-plore® 8000 and the Airline System Dräger X-plore® 9300.
1.6	Functional description	The Dräger X-plore® 8000 hood provides breathing air supplied via the respirator. Breathing air is supplied through a breathing hose at the back of the hood. The breathing air flows from the back over the wearer's head to the inhalation area. The resulting overpressure prevents polluted ambient air from penetrating.
1.7.	Approvals	Approved in combination with Dräger X-plore 8000 (please see technical data sheet Dräger X-plore 8500 and Dräger X-plore 8700) Approved in combination with Dräger X-plore 9300 (please see technical data sheet Dräger X-plore 9300)
	Respiratory Protection	EN 12941 TH3
	Eye protection	EN 166:2002; Marking: 1 F 3
1.8.	Use due to electrostatic properties (measured according to IEC/TS 60079-32-1*)	The tests and evaluations were carried out by DEKRA Exam GmbH, specialist for explosion protection, mining test track. The results given were achieved with the protective foil (R59863) attached. The protective foil must be applied or removed outside the potentially explosive atmosphere.

	Standard hood short		Standard hood long	
	Potentially explosive area (zone)	Explosion group	Potentially explosive area (zone)	Explosion group
	Zone 20, 21, 22	IIIA, IIIB, IIIC	Zone 20, 21, 22	IIIA, IIIB, IIIC
	Zone 0	IIA	Zone 0	-
	Zone 1, 2	IIA, IIB, IIC	Zone 1, 2	-

2. Technical Data

2.1	Materials	
	Visor	PC (Polycarbonat)
	Hood	PP (Polypropylene) /PE (Polyethylene)
	Protective cover	PET (Polyethylene terephthalate)
	Additional information	Latex-free
2.2	Head circumference	
	Size S/M	52 cm to 59 cm
	Size L/XL	57 cm to 64 cm
2.3	Colour	White
2.4	Weight	
	Short hood	Approx. 145 g
	Long hood	Approx. 205 g
2.5	Operating temperature	-10 °C to 60 °C
2.6	Storage temperature	-20 °C to 60 °C
2.7	Operating / storage humidity	≤ 95 % relative humidity

3. Documentation

3.1 Labelling

The label contains the following information:

- Approval markings
 - CE-mark
 - UKCA-mark
 - Symbol "Follow the instructions for use", "Storage conditions"
 - Manufacturer
 - Country of production ("Made in China")
 - Date of manufacture
 - Part number
 - Batch number
-

3.2 Instructions for use

Each packaging unit contain instructions for use in the following languages:

English, German, French, Spanish, Italian, Dutch, Danish, Polish

The instructions for use for the following languages are available online:

Bulgarian, Chinese, Estonian, Finnish, Greek, Japanese, Korean, Croatian, Hungarian, Latvian, Lithuanian, Norwegian, Portuguese, Romanian, Russian, Swedish, Slovak, Slovenian, Serbian, Thai, Czech, Turkish

4. Other

4.1. User instructions and restrictions	The devices conform to the minimum requirements of the standard indicated by the class and type of the filter it is marked with. It must be noted that laboratory values can differ from those measured in practice. This may result in longer or shorter breakthrough times. The user must read and understand the instructions for use. Additionally, the knowledge of all relevant application rules is mandatory (see in particular, the restrictions on the use of filtering devices). Further information upon request.
---	---

Mentioned Trademarks are only registered in certain countries and not necessarily in the country in which this material is released.
Go to www.draeger.com/trademarks to find the current status.

Corporate Headquarters
Drägerwerk AG & Co. KGaA
Moislinger Allee 53-55
23558 Lübeck, Germany

www.draeger.com

Region Europe
Dräger Safety AG & Co. KGaA
Revalstraße 1
23560 Lübeck, Germany
☎ +49 451 882 0
☎ +49 451 882 2080
✉ info@draeger.com

Region Asia Pacific
Draeger Singapore Pte. Ltd.
Science Park Road
The Galen #04-01
Singapore 117525
☎ +65 6872 9288
☎ +65 6259 0398

Region Middle East, Africa
Dräger Safety AG & Co. KGaA
Branch Office
P.O. Box 505108
Dubai, United Arab Emirates
☎ +971 4 4294 600
☎ +971 4 4294 699
✉ contactuae@draeger.com

Region Central and South America
Dräger Indústria e Comércio Ltda.
AL. Pucuruí - 51 - Tamboré
06460-100 - Barueri - São Paulo
☎ +55 (11) 4689-4900
✉ relacionamento@draeger.com



Locate your Regional Sales Representative at:
www.draeger.com/contact