

# C11E4TM032B

Circuit breaker ComPacT NSXm E (16kA at 415VAC), 4 Poles 4d, 32A rating TMD trip unit, compression lugs and busbar connectors



## Main

|  |   |
|--|---|
| Range  | ComPacT new generation  |
| Product name   | ComPacT NSXm new generation   |
| Range of product                                     | ComPacT NSXm new generation   |
| Device short name                                    | NSXm 100E   |
| Product or component type                            | Circuit breaker   |
| Device application                                   | Distribution  |
| Poles description                                    | 4P  |
| Protected poles description                          | 4D  |
| Neutral position                                     | Left  |
| [In] rated current                                   | 32 A at 40 °C   |
| [Ue] rated operational voltage                       | 690 V AC 50/60 Hz   |
| Network type   | AC  |
| Network frequency                                    | 50/60 Hz  |
| Suitability for isolation                            | Yes conforming to IEC 60947-2   |
| Utilisation category                                 | Category A  |
| [Icu] rated ultimate short-circuit breaking capacity | 25 KA Icu at 220...240 V AC 50/60 Hz conforming to IEC 60947-2<br>16 KA Icu at 380...415 V AC 50/60 Hz conforming to IEC 60947-2<br>10 KA Icu at 440 V AC 50/60 Hz conforming to IEC 60947-2<br>8 kA Icu at 500 V AC 50/60 Hz conforming to IEC 60947-2 |
| Performance level                                    | E 16 kA 415 V AC  |
| Trip unit name                                       | TM-D  |
| Trip unit technology                                 | Thermal-magnetic  |
| Trip unit protection functions                       | LI  |
| Control type   | Toggle  |
| Circuit breaker mounting mode                        | Fixed   |

## Complementary

|   |   |
|---|---|
| [Ui] rated insulation voltage                       | 800 V AC 50/60 Hz   |
| [Uimp] rated impulse withstand voltage              | 8 kV  |
| [Ics] rated service short-circuit breaking capacity | 25 KA at 220...240 V AC 50/60 Hz conforming to IEC 60947-2<br>16 KA at 380...415 V AC 50/60 Hz conforming to IEC 60947-2<br>10 KA at 440 V AC 50/60 Hz conforming to IEC 60947-2<br>8 kA at 500 V AC 50/60 Hz conforming to IEC 60947-2 |
| Mechanical durability                               | 20000 cycles  |
| Electrical durability                               | 20000 Cycles at 440 V In/2<br>10000 Cycles at 440 V In<br>10000 Cycles at 690 V In/2<br>5000 cycles at 690 V In   |
| Power dissipation per pole                          | 2.94 W  |
| Mounting support                                    | Backplate   |
| Mounting position                                   | Horizontal and vertical<br>Flat on the back   |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

|   |  |
|---|--|
| Upside connection   | Front  |
| Downside connection   | Front  |
| Connection terminals  | Compression lug/busbar   |
| Connection pitch  | 35 Mm with spreaders<br>27 mm without spreaders  |
| 9 mm pitches  | 12 module  |
| Trip unit rating  | 32 A at 40 °C  |
| Long-time pick-up adjustment type I <sub>r</sub> (thermal protection) | Adjustable   |
| [I <sub>r</sub> ] long-time protection pick-up adjustment range       | 0.7...1 x I <sub>n</sub>   |
| Long-time protection delay adjustment type t <sub>r</sub>             | Fixed  |
| Neutral protection settings   | 1 x I <sub>r</sub> (4D)  |
| Instantaneous protection pick-up adjustment type I <sub>i</sub>       | Fixed  |
| [I <sub>i</sub> ] instantaneous protection pick-up adjustment range   | 600 A  |
| Earth-leakage protection  | Without  |
| Number of slots for electrical auxiliaries                            | 1 slot(s) for auxiliary switch OF<br>1 slot(s) for alarm switch SD<br>1 slot(s) for voltage release MN or MX |
| Local signalling  | Flag (green) for presence of auxiliary contacts  |
| Width (W)   | 108 mm   |
| Height (H)  | 137 mm   |
| Depth (D)   | 80 mm  |
| Net weight  | 1.42 kg  |
| Colour  | Grey (RAL 7016)  |

## Environment

|                                       |   |
|---------------------------------------|---|
| Standards                             | EN/IEC 60947                                    |
| Pollution degree                      | 3 conforming to IEC 60664-1                     |
| IP degree of protection               | IP40 conforming to IEC 60529                    |
| IK degree of protection               | IK07 conforming to IEC 62262                    |
| Ambient air temperature for operation | -25...70 °C                                     |
| Ambient air temperature for storage   | -50...85 °C                                     |
| Relative humidity                     | 0...95 %  |
| Operating altitude                    | 2000 m without derating<br>5000 m with derating |

## Packing Units

|                              |           |
|------------------------------|-----------|
| Unit Type of Package 1       | PCE       |
| Number of Units in Package 1 | 1         |
| Package 1 Height             | 12.0 cm   |
| Package 1 Width              | 13.0 cm   |
| Package 1 Length             | 22.0 cm   |
| Package 1 Weight             | 1.6 kg    |
| Unit Type of Package 2       | P12       |
| Number of Units in Package 2 | 144       |
| Package 2 Height             | 150.0 cm  |
| Package 2 Width              | 80.0 cm   |
| Package 2 Length             | 120.0 cm  |
| Package 2 Weight             | 254.49 kg |
| Unit Type of Package 3       | S03       |
| Number of Units in Package 3 | 6         |
| Package 3 Height             | 30.0 cm   |
| Package 3 Width              | 30.0 cm   |
| Package 3 Length             | 40.0 cm   |
| Package 3 Weight             | 10.19 kg  |

## Offer Sustainability

|                             |   |
|-----------------------------|---|
| Sustainable offer status    | Green Premium product                         |
| REACH Regulation            | <a href="#">REACH Declaration</a>             |
| EU RoHS Directive           | Compliant <a href="#">EU RoHS Declaration</a> |
| Mercury free                | Yes   |
| RoHS exemption information  | <a href="#">Yes</a>                           |
| China RoHS Regulation       | <a href="#">China RoHS Declaration</a>        |
| Environmental Disclosure    | <a href="#">Product Environmental Profile</a> |
| Circularity Profile         | <a href="#">End Of Life Information</a>       |
| Halogen content performance | Halogen free plastic parts product            |