



Price* : 246.33 GBP



Main

Range	TeSys
Product name	TeSys LE
Device short name	LE4D
Product or component type	Enclosed DOL starter
Device application	Standard
Material	Polycarbonate
Utilisation category	AC-3
Device composition	Thermal overload relay ordered separately Fuse disconnecter Contactor
[Ie] rated operational current	18 A AC-3
Motor power kW	10 kW at 500 V AC 50/60 Hz 4 kW at 220/230 V AC 50/60 Hz 9 kW at 415 V AC 50/60 Hz 9 kW at 440 V AC 50/60 Hz 7.5 kW at 380/400 V AC 50/60 Hz
[Uc] control circuit voltage	400 V AC 50/60 Hz
[Ithe] conventional enclosed thermal current	18 A
Associated fuse rating	20 A 10 x 38 mm aM
Control type	Push-button start green I Push-button stop/reset red O

Complementary

Cable entry number	2 cable entry : ISO20 top 2 cable entry : ISO20 bottom 2 cable entry : ISO25 top 2 cable entry : ISO25 bottom 2 cable entry : ISO32 top 2 cable entry : ISO40 top 2 cable entry : ISO32 bottom
--------------------	--

2 cable entry : ISO40 bottom

Width	186 mm
Height	330 mm
Depth	175.5 mm
Product weight	2.2 kg

Environment

IP degree of protection	IP65 conforming to IEC 60529
IK degree of protection	IK07 conforming to IEC 60529
Standards	IEC 60947-4-1
Ambient air temperature for operation	-5...40 °C
Environmental characteristic	Standard environment

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0925 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product environmental
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------