

Eaton 265305

Catalog Number: 265305

Eaton Distribution parts. Impulse relay, 230AC, 2NO+2NC, 16A, 50Hz, 2SU

General specifications



Product Name

Eaton Distribution parts

EAN

4015082653057

Product Height

70 mm

Product Weight

0.263 kg

Catalog Number

265305

Product Length/Depth

80 mm

Product Width

35 mm

Compliances

RoHS conform

Product specifications

Mounting method

DIN rail

Control voltage 1 type

AC

Ambient operating temperature - max

45 °C

Ambient operating temperature - min

-20 °C

Control voltage 1 - max

230 V

Control voltage 1 - min

230 V

Control voltage 2 - max

0 V

Control voltage 2 - min

0 V

Frequency control voltage 1 - max

50 Hz

Frequency control voltage 1 - min

50 Hz

Frequency control voltage 2 - max

0 Hz

Frequency control voltage 2 - min

0 Hz

Heat dissipation per pole, current-dependent

1.5 W

Incandescent lamp load - max

0 W

Load fluorescent lamp - max

0 VA

Load fluorescent lamp (duo circuit) - max

0 VA

Load fluorescent lamp (parallel compensated) - max

0 VA

Number of contacts (change-over contacts)

Resources

Declarations of conformity

[DA-DC-03_Z-S_SC_SB](#)

[DA-DC-03_Z-S](#)

Drawings

[eaton-dimensions-mas-z-s230.jpg](#)

[eaton-wiring-diagram-z-s-2te.jpg](#)

[eaton-3d-drawing-z-s230-scha2.jpg](#)

[122I163](#)

[eaton-mcb-dimensions-122x137.eps](#)

0

Number of contacts (normally closed contacts)

2

Number of contacts (normally open contacts)

2

Rated operational current for specified heat dissipation (In)

16 A

Rated switch current

16 A

Equipment heat dissipation, current-dependent

6 W

Supply voltage - max

415 V

Supply voltage - min

240 V

Switching current (cos phi = 0.6) - max

0 A

Width in number of modular spacings

2

Built-in depth

60 mm

Operating mode

Manual operation possible

Control voltage 2 type

AC

Voltage type

AC

Functions

Mechanical switch



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)