

213.3237RV**PLUG**

32A 3P+N+E 6h 346-415V 60Hz 50Hz
Screw terminals With REVERSE
device



* Product image may be indicative



EN IEC 60309-1 (2022)

EN IEC 60309-2 (2022)

Low voltage direct. 2014/35/EU

■ GENERAL CHARACTERISTICS

Commercial Series	OPTIMA-REVERSE Series
-------------------	-----------------------

Synthetical description	PLUG
-------------------------	------

Description

The plug from the OPTIMA-REVERSE Series is designed for a rated voltage of 346-415V and a current of 32A. It features 3P+N+E poles and operates at both 50Hz and 60Hz frequencies, with a 6h hour position. The plug offers a protection degree of IP44/IP54, ensuring reliable performance in various environments. Equipped with screw terminals, it includes a REVERSE device for enhanced functionality. Compatible with straight type outlets, the plug incorporates the operating principle of the phase inverter, providing dependable performance for professional applications.

Mounting version	PORTABLE
------------------	----------

■ TECHNICAL CHARACTERISTICS

Rated current	32A
---------------	-----

Poles	3P+N+E
-------	--------

Hour position	6h
---------------	----

Rated voltage	346-415V
---------------	----------

Working frequency	60Hz
-------------------	------

	50Hz
--	------

Terminals	Screw terminals
-----------	-----------------

■ PHYSICAL CHARACTERISTICS

Mounting version	PORTABLE
------------------	----------

Colour	RED
--------	-----

Material	THERMOPLASTIC
----------	---------------

Protection degree	Splash proof
-------------------	--------------

Protection degree IP	IP44/IP54
----------------------	-----------

Protection degree IK	IK08
----------------------	------

Types of available outlets	STRAIGHT
----------------------------	----------

Contact material	CuZn (brass)
------------------	--------------

Surface treatment contacts	Nickel-plated
----------------------------	---------------

Cable entry	CABLE GLAND
-------------	-------------

■ DOWNLOAD

[Technical drawing \[PDF\]](#)

[Technical drawing \[STP\]](#)

[Technical drawing \[DWG\]](#)

■ OPTIONS & VARIOUS NOTES

Options	With REVERSE device
---------	---------------------

Catalogue notes	Phase inverter
-----------------	----------------

	Operating principle of the phase inverter
--	---