

LS-WMTB-V4A (D50) - Cable marker




1099826

<https://www.phoenixcontact.com/gb/products/1099826>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Cable marker, Stainless steel label, silver, unlabeled, can be labeled with: TOPMARK NEO, TOPMARK LASER, mounting type: Assembly with cable ties, cable diameter: > 2.9 mm, Number of individual labels: 9, text field height: 22 mm, text field width: 44 mm



Your advantages

- Stainless steel cable marking for assembly with cable ties
- Easy-to-clean and permanent identification that also meets stringent hygiene requirements
- High resistance to corrosion, acids, and temperatures
- Suitable for large-surface marking of wires and cables, > 2.9 mm in diameter

Commercial data

Item number	1099826
Packing unit	5 pc
Minimum order quantity	5 pc
Sales key	BG231D
Product key	BG231D
GTIN	4055626950310
Weight per piece (including packing)	118.7 g
Weight per piece (excluding packing)	107.8 g
Customs tariff number	73269098
Country of origin	CN

LS-WMTB-V4A (D50) - Cable marker



1099826

<https://www.phoenixcontact.com/gb/products/1099826>

Technical data

Product properties

Product type	Conductor marking
Type	circular
Type	Laser sheet

Marking

Number of individual labels	9
Identification technology	Direct laser marking

Dimensions

Width	50 mm
Length	50 mm
Hole diameter	5.00 mm
Material strength	0.50 mm

External dimensions

Outside diameter	1 mm ... 136 mm
------------------	-----------------

Text field

Text field width	44 mm
Text field height	22 mm

Material specifications

Color	Steel/stainless steel color
Material	V4A (1.4404; AISI 316L)
Components	free from silicone, halogen, and cadmium

Cable/line

External cable diameter	> 2.90 mm
-------------------------	-----------

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

Scratch test for the determining scratch resistance

Specification	DIN EN ISO 1518-1:2019-10 (following)
Requirements	≥ 5 N
Result	Test passed

Tesafilm test

Specification	DIN EN ISO 2409:2013 (following)
---------------	----------------------------------

LS-WMTB-V4A (D50) - Cable marker



1099826

<https://www.phoenixcontact.com/gb/products/1099826>

Result	Test passed
--------	-------------

UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h
Specification	IEC 60068-2-2:2007-07
Result	Test passed
Duration	240 h
Temperature for testing	350 °C

Temperature resistance

Specification	ANSI/UL 969-2018:03 (following)
Test duration	240 h
Rating 225 °C (250 °C)	Test passed

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropyl [CAS No. 67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
Acetone (99 %) [CAS No. 67-64-1]	Test passed
Specification	ISO 175:2010 (following)
Test duration	168 h
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
Acetone (99 %) [CAS No. 67-64-1]	Test passed
IRM 901	Test passed
IRM 902	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN 50018:2013-05 (following)
Result	Test passed
Climate level	AHT 1.0 S
Cycles	2

Salt spray test

Specification	DIN EN 60068-2-11:2000-02
---------------	---------------------------

LS-WMTB-V4A (D50) - Cable marker



1099826

<https://www.phoenixcontact.com/gb/products/1099826>

Result	Test passed
Test duration	96 h

Salt spray test

Specification	ISO 9227:2017-03
Result	Test passed
Test duration	336 h

High pressure test

Specification	ISO 20653:2013-02
Result	Test passed

Ambient conditions

Ambient temperature (operation)	-80 °C ... 350 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)
Shelf life	24 months

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	Assembly with cable ties
---------------	--------------------------

LS-WMTB-V4A (D50) - Cable marker



1099826

<https://www.phoenixcontact.com/gb/products/1099826>

Classifications

ECLASS

ECLASS-11.0	27281102
ECLASS-12.0	27281102
ECLASS-13.0	27281102

ETIM

ETIM 9.0	EC001530
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

LS-WMTB-V4A (D50) - Cable marker



1099826

<https://www.phoenixcontact.com/gb/products/1099826>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd

Halesfield 13, Telford

Shropshire, TF7 4PG

01952 681700

info@phoenixcontact.co.uk