

Capacitive sensor switch with IO-Link Standard

Distribution by
Rs-online



84-ASKS-B14-04A0



<https://rs-online.eao.com/component/84-ASKS-B...>

Your product:



84-ASKS-B14-04A0

Capacitive sensor switch with IO-Link
Standard

FRONT

Front dimension:	Ø 30 mm
Front form:	Round
Front bezel material:	Plastic

MOUNTING

Design:	Flush
Mounting cut-out:	Ø 22.5 mm
Mounting type:	Panel mounting

OPERATING-/INDICATION PART

Lens material:	Plastic
Lens illumination:	Illuminated
Lens shape:	Flush
Lens optics:	transparent
Symbol:	Standby (B14)

ELECTRICAL CHARACTERISTICS

Operating voltage:	8.4 - 32 V DC
Communication interface:	IO-Link specification

MECHANICAL CHARACTERISTICS

Terminal:	Connector M12
-----------	---------------

Switching system:	Capacitive
Operating force:	No actuating force necessary
Weight:	0.015 kg

AMBIENT CONDITION

IP front protection:	IP69K
IK front protection:	IK08
Operating temperature:	– 30 °C ... + 65 °C
Climate resistance:	Relative humidity, max. 95%, non-condensing

CERTIFICATE

Approbations:	CSA, EHEDG
Conformities:	CE, UKCA
REACH:	REACH compliant
RoHS:	RoHS compliant




OTHER

Short Description:	Capacitive sensor switch with IO-Link Standard, Ø 22.5 mm, Ø 30 mm, Flush, Illuminated, Plastic, transparent, Round, Plastic, Connector M12, IP69K, IK08, Standby (B14)
---------------------------	---


Housing colour:	Black
------------------------	-------

Housing material:	Plastic
--------------------------	---------

Wiring diagrams:



Component layouts:



Technical drawing of the M12x1.5 screw. The drawing shows two views: a front view (left) and a side view (right). The front view shows a circular head with a diameter of $\varnothing 30$ and a central hole with a diameter of $\varnothing 17.8$. The head has a thickness of 1.8. The side view shows the screw with a thread length of 4.1 and a total length of 25.8. The thread is labeled M12x1.5. The head has a diameter of 17.8 and a thickness of 1.8. The side view also shows a dimension of 2.2 for the head's width.