# An outstanding design - with a convincing technology!







The new Klauke mini® series







## The new KI

## Large comfort, small package


The **Klauke® mini** is the new lightweight battery powered crimping and cutting tool platform and a specialist for smaller cross sections, e.g. in control cabinets. The ergonomic design with a 2-component housing and the one button operation make sure that every job can be done with ease - even in hard to reach areas.




## **Characteristics:**

- Crimping and cutting heads rotatable
- Automatic retraction when the operation is complete
- Manual retraction in case of need
- Environmentally-friendly hydraulic oil, quickly biodegradable
- All mini tools have a sound pressure level of 70.6 dB(A), measured at a distance of 1 m, the vibrations on the tools much lower than 2.5 m/s².

# auke® mini series





Multifunction LED for maintenance control and analysis of data via optical interface and USB adapter

## More comfort:

 Ergonomic two-component housing with soft linings for comfortable one hand operation

Warranty World wide

Tool

Service

- Optimal centre of gravity
- One button operation concept for easy handling
- LED for work place illumination

#### More power:

- Powerful 10.8 V Li-lon battery
- The batteries and chargers are interchangeable within the entire tool family - including the Klauke® micro

# More security :

- Multifunction LED for maintenance control and analysis of data via optical interface and USB adapter
- Direct readability of battery status
- Quick motor stop guarantees highest safety for the operator





## The new Klauke mini® series All tools at a glance

## Crimping tools:









KI	auk	<b>E</b> pro
----	-----	--------------

		-	
Technical data	EK 35/4 ML	EK 15/50 ML	EKP 1 ML
Crimping force:	35 kN	13 kN	10 kN
Stroke / opening width:	9 mm	9 mm	9 mm
Crimping range:	6 - 150 mm <sup>2</sup>	0,14 - 50 mm <sup>2</sup>	0,14 - 16 mm <sup>2</sup>
Number of crimps:	approx. 145 @ 120 mm <sup>2</sup>	approx. 230 @ 10 mm <sup>2</sup>	approx. 230 @ 10 mm <sup>2</sup>
Weight incl. battery:	1.6 kg	1.5 kg	1.2 kg
Variants:	EK354MLSETHR, EK354MLSETHD		

## **Cutting tools:**



20 mm dia. Cu, AI, AI/St (ACSR)







8 mm dia. Steel solid



Technical data	ES 20 ML	ES 32 ML	ES 32F ML	EBS 8 ML	EBS 12 ML
Shape of head:	open scissor	open scissor	open scissor	open	open
Cutting range:	20 mm	32 mm	32 mm	8 mm	12 mm
Type of cables:	Al/St-ropes, Cu flexible bus-bars	Cu- and Al-cable	finest stranded Cu-cable	cable channels, studs, steel wire	cable channels, studs, steel wire
Number of cuts:	approx. 190 @ ACSR conductor 120/20	approx. 135 @ 150 mm² NYY	approx. 100 @ H07V-K 1x240 mm²	approx. 310 @ 5 mm dia.	approx. 310 @ 12 mm dia.
Weight incl. battery:	1.6 kg	1.8 kg	1.8 kg	1.2 kg	1.8 kg

### Scope of supply:







- Battery 10.8 V / 1.5 Ah, Li-lon (16,2 Wh)
- Charger for 10.8 V / 1,5 Ah Li-lon batteries, 230 V  $\,$
- Sturdy plastic box for storage of tool and

## Accessory:



• USB adapter PGA 1 including i-press software

## Variants:

- EK354MLSETHR EK354ML with crimping die set HR 4; 6-150 mm<sup>2</sup>
- EK354MLSETHD EK354ML with crimping die set HD 4; 6-120 mm<sup>2</sup>

#### **Gustav Klauke GmbH**

Auf dem Knapp 46 D-42855 Remscheid

Phone: +49 (0) 2191/907-0 Fax: +49 (0) 2191/907-205

info@klauke.textron.com email:

Internet: www.klauke.com