

Data Sheet | Item Number: 721-140/001-000


THT male header; 1.0 x 1.0 mm solder pin; straight; 100% protected against mismating;

Pin spacing 5 mm; 10-pole; light gray

<https://www.wago.com/721-140/001-000>




Color: ■ light gray



Dimensions in mm

$L = (\text{Polzahl} - 1) \times \text{Rastermaß} + 8,2 \text{ mm}$



Male connector, 721 Series, light gray

Seamless electrical installations are guaranteed with this male connector (item number 721-140/001-000). Dimensions: (53.2 x 17 x 11.4) mm (width x height x depth).

The contact surface is tin-coated The PCB connector is designed for THT soldering.

- 10 connection points
- The right solution for every wiring task
- Pin spacing: 5 mm
- Soldering via THT
- Ready to install, immediately usable

Notes	
Safety Information	The MCS – <i>MULTI CONNECTION SYSTEM</i> includes connectors without breaking capacity in accordance with DIN EN 61984. When used as intended, these connectors must not be connected/disconnected when live or under load. When used as intended, these connectors must not be connected/disconnected when live or under load. The circuit design should ensure header pins, which can be touched, are not live when unmated.
Variants:	Other pole numbers 3.8 mm pin projection for male headers with straight solder pins Gold-plated or partially gold-plated contact surfaces Other versions (or variants) can be requested from WAGO Sales or configured at https://configurator.wago.com/ .

Electrical data				
Ratings per		IEC/EN 60664-1		
Overvoltage category		III	III	II
Pollution degree		3	2	2
Nominal voltage		320 V	320 V	630 V
Rated impulse withstand voltage		4 kV	4 kV	4 kV
Rated current		12 A	12 A	12 A
Approvals per		UL 1059		
Use group		B	C	D
Rated voltage		300 V	-	300 V
Rated current		10 A	-	10 A

Ratings	
Approvals per	UL 1977
Rated voltage	600 V
Rated current	10 A

Approvals per		CSA		
Use group		B	C	D
Rated voltage		300 V	-	300 V
Rated current		10 A	-	10 A

Connection Data		
Total number of potentials	10	
Number of connection types	1	
Number of levels	1	

Connection 1	
Pole number	10

Physical data	
Pin spacing	5 mm / 0.197 inches
Width	53.2 mm / 2.094 inches
Height	17 mm / 0.669 inches
Height from the surface	12 mm / 0.472 inches
Depth	11.4 mm / 0.449 inches
Solder pin length	5 mm
Solder pin dimensions	1 x 1 mm
Drilled hole diameter	1.4 (+0.1) mm

Mechanical data	
Variable coding	Yes
Anti-rotation protection	Yes



Plug-in connection	
Contact type (pluggable connector)	Male connector/plug
Connector (connection type)	for PCB
Mismating protection	Yes
Mating direction to the PCB	90 °

PCB contact	
PCB contact	THT
Solder pin arrangement	over the entire male connector (in-line)
Number of solder pins per potential	1

Material data	
Note (material data)	Information on material specifications can be found here
Color	light gray
Material group	I
Insulation material (main housing)	Polyamide (PA66)
Flammability class per UL94	V0
Contact material	Electrolytic copper (E _{Cu})
Contact Plating	Tin
Fire load	0.051 MJ
Weight	3.2 g

Environmental requirements	
Limit temperature range	-60 ... +100 °C
Processing temperature	-35 ... +60 °C
Environmental Testing	
Test specification: Railway applications – Rolling stock – Electronic equipment	DIN EN 50155 (VDE 0115-200):2022-06
Test procedure: Railway applications – Rolling stock equipment – Vibration and shock tests	DIN EN 61373 (VDE 0115-0106):2011-04
Spectrum/Mounting location	Service life test, Category 1, Class A/B
Functional test with noise-like oscillations	Test passed according to Section 8 of the standard
Frequency	f ₁ = 5 Hz to f ₂ = 150 Hz
Acceleration	0.101g (highest test level used for all axes)
Test duration per axis	10 min.
Test directions	X, Y and Z axes
Monitoring of contact faults and interruptions	Passed
Voltage drop measurement before and after each axis	Passed
Simulated service life test through increased levels of noise-like oscillations	Test passed according to Section 9 of the standard
Frequency	f ₁ = 5 Hz to f ₂ = 150 Hz
Acceleration	0.572g (highest test level used for all axes)
Test duration per axis	5 h
Test directions	X, Y and Z axes
Extended testing: Monitoring of contact faults and interruptions	Passed
Extended testing: Voltage drop measurement before and after each axis	Passed
Shock test	Test passed according to Section 10 of the standard
Shock pulse form	Half sine
Acceleration	5g (highest test level used for all axes)



Environmental Testing	
Shock duration	30 ms
Number of shocks (per axis)	3 pos. und 3 neg.
Test directions	X, Y and Z axes
Extended testing: Monitoring of contact faults and interruptions	Passed
Extended testing: Voltage drop measurement before and after each axis	Passed
Vibration and shock stress for rolling stock equipment	Passed

Commercial data	
Product Group	3 (Multi Conn. System)
PU (SPU)	100 pcs
Packaging type	Box
Country of origin	PL
GTIN	4044918869058
Customs tariff number	85366930000

Product Classification	
UNSPSC	39121409
eCl@ss 10.0	27-44-04-02
eCl@ss 9.0	27-44-04-02
ETIM 9.0	EC002637
ETIM 10.0	EC002637
ECCN	NO US CLASSIFICATION

Environmental Product Compliance	
RoHS Compliance Status	Compliant, No Exemption

Approvals / Certificates

General approvals

Declarations of conformity and manufacturer's declarations



Approval	Standard	Certificate Name
CB DEKRA Certification B.V.	IEC 61984	NL-113351
CSA DEKRA Certification B.V.	C22.2	1466354
KEMA/KEUR DEKRA Certification B.V.	EN 61984	71-130478 REV.1
UL Underwriters Laboratories Inc.	UL 1059	UL-US-L45172-6187117-81111991-4
UR Underwriters Laboratories Inc.	UL 1977	E45171

Approval	Standard	Certificate Name
Railway WAGO GmbH & Co. KG	-	Railway Ready



Approvals for marine applications



Approval	Standard	Certificate Name
ABS American Bureau of Ship- ping	-	24-0095975-PDA
BV Bureau Veritas S.A.	IEC 60998	11915/E0 BV
DNV DNV GL SE	-	TAE000016Z
PRS Polski Rejestr Statków	-	TE/1095/880590/23

Downloads

Environmental Product Compliance

Compliance Search
Environmental Product Compliance 721-140/001-000

Documentation

Additional Information
Technical Section
03.04.2019
pdf 2027.26 KB

CAD/CAE-Data

CAD data
2D/3D Models 721-140/001-000

CAE data
EPLAN Data Portal 721-140/001-000
ZUKEN Portal 721-140/001-000

PCB Design
Symbol and Footprint via SamacSys 721-140/001-000
Symbol and Footprint via Ultra Librarian 721-140/001-000



1 Compatible Products

1.1 System counterpart

1.1.1 Female connector/socket



Item No.: 722-110/026-000
1-conductor female connector, angled; CAGE CLAMP®; 2,5 mm²; Pin spacing 5 mm; 10-pole; 100% protected against mismatching; 2,50 mm²; light gray



Item No.: 722-210/026-000
1-conductor female connector, angled; CAGE CLAMP®; 2,5 mm²; Pin spacing 5 mm; 10-pole; 100% protected against mismatching; 2,50 mm²; light gray



Item No.: 721-310/031-000
1-conductor female connector, angled; CAGE CLAMP®; 2,5 mm²; Pin spacing 5 mm; 10-pole; 100% protected against mismatching; clamping collar; 2,50 mm²; light gray



Item No.: 721-310/008-000
1-conductor female connector, angled; CAGE CLAMP®; 2,5 mm²; Pin spacing 5 mm; 10-pole; 100% protected against mismatching; Snap-in mounting feet; 2,50 mm²; light gray



Item No.: 721-110/026-000
1-conductor female connector; CAGE CLAMP®; 2,5 mm²; Pin spacing 5 mm; 10-pole; 100% protected against mismatching; 2,50 mm²; light gray



Item No.: 721-110/027-000
1-conductor female connector; CAGE CLAMP®; 2,5 mm²; Pin spacing 5 mm; 10-pole; 100% protected against mismatching; clamping collar; 2,50 mm²; light gray



Item No.: 721-110/031-000
1-conductor female connector; CAGE CLAMP®; 2,5 mm²; Pin spacing 5 mm; 10-pole; 100% protected against mismatching; clamping collar; 2,50 mm²; light gray



Item No.: 721-110/037-000
1-conductor female connector; CAGE CLAMP®; 2,5 mm²; Pin spacing 5 mm; 10-pole; 100% protected against mismatching; Lateral locking levers; 2,50 mm²; light gray



Item No.: 2721-1110/326-000
1-conductor female connector; lever; Push-in CAGE CLAMP®; 2,5 mm²; Pin spacing 5 mm; 10-pole; 100% protected against mismatching, coding finger; 2,50 mm²; light gray



Item No.: 2721-1110/326-047
1-conductor female connector; lever; Push-in CAGE CLAMP®; 2,5 mm²; Pin spacing 5 mm; 10-pole; 100% protected against mismatching, coding finger; direct marking; light gray



Item No.: 2721-1110/326-9037
1-conductor female connector; lever; Push-in CAGE CLAMP®; 2,5 mm²; Pin spacing 5 mm; 10-pole; 100% protected against mismatching, coding finger; direct marking; light gray



Item No.: 2721-1110/037-000
1-conductor female connector; lever; Push-in CAGE CLAMP®; 2,5 mm²; Pin spacing 5 mm; 10-pole; 100% protected against mismatching, coding finger; Lateral locking levers; 2,50 mm²; light gray



Item No.: 2721-1110/037-000/335-000
1-conductor female connector; lever; Push-in CAGE CLAMP®; 2,5 mm²; Pin spacing 5 mm; 10-pole; 100% protected against mismatching, coding finger; Lateral locking levers; Strain relief plate; light gray



Item No.: 2721-1110/326-000/335-000
1-conductor female connector; lever; Push-in CAGE CLAMP®; 2,5 mm²; Pin spacing 5 mm; 10-pole; 100% protected against mismatching, coding finger; Strain relief plate; light gray



Item No.: 2721-110/026-000
1-conductor female connector; push-button; Push-in CAGE CLAMP®; 2,5 mm²; Pin spacing 5 mm; 10-pole; 100% protected against mismatching; 2,50 mm²; light gray



Item No.: 2721-110/031-000
1-conductor female connector; push-button; Push-in CAGE CLAMP®; 2,5 mm²; Pin spacing 5 mm; 10-pole; 100% protected against mismatching; clamping collar; 2,50 mm²; light gray



Item No.: 721-110/037-000
1-conductor female connector; push-button; Push-in CAGE CLAMP®; 2,5 mm²; Pin spacing 5 mm; 10-pole; 100% protected against mismatching; Lateral locking levers; 2,50 mm²; light gray



Item No.: 721-2110/037-000
2-conductor female connector; Push-in CAGE CLAMP®; 2,5 mm²; Pin spacing 5 mm; 10-pole; 100% protected against mismatching; Lateral locking levers; 2,50 mm²; light gray



Item No.: 721-2110/026-000
2-conductor female connector; Push-in CAGE CLAMP®; 2,5 mm²; Pin spacing 5 mm; 10-pole; 100% protected against mismatching; with integrated end plate; 2,50 mm²; light gray



Item No.: 721-2110/026-000/135-000
2-conductor female connector; Push-in CAGE CLAMP®; 2,5 mm²; Pin spacing 5 mm; 10-pole; 100% protected against mismatching; with integrated end plate; Strain relief plate; 2,50 mm²; light gray

1.2 Optional Accessories

1.2.1 Coding

1.2.1.1 Coding



Item No.: 231-129
Coding key; snap-on type; light gray

1.2.2 Marking

1.2.2.1 Marking strip




Item No.: 210-833
Marking strips; 25 m on roll; 6 mm wide;
plain; Self-adhesive; white



Item No.: 210-834
Marking strips; on reel; 5 mm wide; plain;
Self-adhesive; white

Installation Notes

Coding



Coding a male header – fitting coding key(s).