


For mating dimensions see MIL-DTL-38999 Series III

Reference MIL-STD-1560 for insert arrangement details.

PANEL THICKNESS  
.062-.125  
[1,58-3,17]



For rear shell features and accessories see MIL-DTL-38999 Series III


**NOTE:**  
-DRAWING NOT TO SCALE  
-DIMENSIONS SUBJECT TO CHANGE  
-DIMENSIONS ARE IN INCHES [MM]

PROPERTY OF AMPHENOL AEROSPACE. ALL RIGHTS RESERVED.

Meets requirements of MIL-DTL-38999  
Base Material: Composite  
Plating: Electroless, Nickel

<b>AMPHENOL CORPORATION</b> <small>40-60 DELAWARE AVENUE SIDNEY, N.Y. 13838</small>			
<b>RECEPTACLE</b> Electrical Connector D38999/24			<b>U</b>
<small>SIZE</small> <b>C</b>	<small>CAGE CODE</small> <b>77820</b>	<small>CODED NUMBER</small> <b>D38999/24MA35PN</b>	<small>REV</small> <b>P1</b>
SHEET 1 OF 1			

# Insert Arrangement



No. of Contacts	6
Contact Size	22D
Wire Size	28, 26, 24, 22

Shell Size	A
Arrangement	35
Service Rating	M
Test Current	5 AMPS

**NOTE:**  
 -DRAWING NOT TO SCALE  
 -DIMENSIONS SUBJECT TO CHANGE  
 -DIMENSIONS ARE IN INCHES [MM]

PROPERTY OF AMPHENOL AEROSPACE. ALL RIGHTS RESERVED.

<b>AMPHENOL CORPORATION</b> <small>40-60 DELAWARE AVENUE SIDNEY, N.Y. 13838</small>			
RECEPTACLE Electrical Connector D38999/24			U
SIZE <b>C</b>	CAGE CODE <b>77820</b>	CODED NUMBER <b>D38999/24MA35PN</b>	REV <b>P1</b>
SHEET 1 OF 1			