

# integrated drive ILA with servo motor - 24..36 V - CANopen - indus connector

ILA1F572TC1A0

! Discontinued on: 9 Feb 2023

① Discontinued

EAN Code: 3389119225595

### Main

Range of product	Lexium integrated drive	
Product or component type	Motion integrated drive	
Device short name	ILA	
Motor type	AC synchronous servo motor	
Number of motor poles	6	
Network number of phases	Single phase	
[Us] rated supply voltage	36 V 24 V	
Network type	СС	
Communication interface	CANopen DS301, integrated	
Length	163.8 mm	
Winding type	High speed of rotation and medium torque	
Electrical connection	Industrial connector	
Holding brake	Without	
Gear box type	Without	
Nominal speed	3100 rpm at 24 V 5000 rpm at 36 V	
Nominal torque	0.41 N.m	

# **Complementary**

Transmission rate	50, 100, 125, 250, 500, 800 and 1000 kbauds
Mounting support	Flange
Motor flange size	57 mm
Number of motor stacks	2
Centring collar diameter	50 mm
centring collar depth	1.6 mm
Number of mounting holes	4
Mounting holes diameter	5.2 mm
Circle diameter of the mounting holes	66.6 mm
Feedback type	Single turn encoder
Shaft end	Untapped

Second shaft	Without second shaft end
Shaft diameter	9 mm
Shaft length	20 mm
Supply voltage limits	1840 V
Current consumption	7500 mA maximum continuous 9000 mA peak
Associated fuse rating	10 A
Input/output type	4 signals (each be used as input or output)
Voltage state 0 guaranteed	-34.5 V
Voltage state 1 guaranteed	1530 V
Discrete input current	10 mA at 24 V on/STO_A for safety input 3 mA at 24 V on/STO_B for safety input 2 mA at 24 V for 24 V signal interface
Discrete output voltage	2325 V
Maximum switching current	100 mA per output 200 mA total
Protection type	Short circuit of the output voltage Safe torque off Overload of output voltage
Peak stall torque	0.61 N.m
Continuous stall torque	0.41 N.m
Speed feedback resolution	16384 points/turn
Accuracy error	+/- 0.05 °
Rotor inertia	0.18 kg.cm²
Maximum radial force Fr	107 N
Maximum axial force Fa	104 N (force pressure) 104 N (tensile force)
Service life in hours	20000 h bearing
Marking	CE
type of cooling	Natural convection
Net weight	1.7 kg

# **Environment**

Standards	IEC 60072-1 EN 61800-3 : 2001-02 IEC 61800-3, Ed 2 EN 61800-3:2001, second environment IEC 50178 IEC 50347 IEC 61800-3
Product certifications	TÜV UL cUL
Ambient air temperature for operation	5065 °C (with power derating of 2 % per °C) 050 °C (without derating)
Permissible ambient air temperature around the device	105 °C power amplifier 110 °C motor
Ambient air temperature for storage	-2570 °C
Operating altitude	<= 1000 m without derating

Relative humidity	1585 % without condensation	
Vibration resistance	20 m/s² (f= 10500 Hz) 10 cycles conforming to IEC 60068-2-6	
Shock resistance	150 m/s² 1000 shocks conforming to IEC 60068-2-29	
IP degree of protection	IP41 shaft bushing: conforming to IEC 60034-5	

# **Packing Units**

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.5 cm
Package 1 Width	19 cm
Package 1 Length	39.5 cm
Package 1 Weight	1.7 kg

# **Contractual warranty**

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

#### Environmental Data explained >

How we assess product sustainability >

☑ Environmental footprint	
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	472
Environmental Disclosure	Product Environmental Profile

#### **Use Better**

Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
REACh Regulation	REACh Declaration
PVC free	Yes


#### **Use Again**

○ Repack and remanufacture	
Circularity Profile	End of Life Information
Take-back	No
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

### **Dimensions Drawings**

### **Integrated Drive without Holding Brake**


#### **Dimensions**



- 1 Accessories: I/O signal insert with industrial connectors
- 2 Option: industrial connectors
- 3 Earth (ground) terminal
- 4 Accessories: cable entries  $\emptyset = 3 \dots 9 \text{ mm}/0.12 \dots 0.35 \text{ in.}$
- 5 Centring hole DIN 332 DS M3
- L 163.8 mm/6.45 in.

Connections and Schema

## Connection Example with 4 I/O Signals




# **Product datasheet**

## ILA1F572TC1A0

#### Performance Curves

## **Torque Characteristics**



- X Speed of rotation in rpm
- Y Torque in Nm
- 1.1 Max. torque at 24 V
- 1.2 Max. torque at 36 V
- 2 Continuous torque