


## FEATURES

- **Fluorinated Ethylene Propylene Material:** Offers excellent chemical resistance and durability
- **Shore A Hardness 90 to 95:** Provides optimal sealing performance and wear resistance
- **Temperature Range -20 °C to 140 °C:** Suitable for a wide range of operating conditions
- **Compliance with BS ISO 3601-1 and FDA Standards:** Ensures high quality and safety for various applications
- **Inside Diameter 33 mm:** Fits securely in designated spaces for effective sealing

## RS PRO 33 mm O-Ring Seal, Shore A 90 to 95

RS Stock No: 732-041



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

This RS PRO O-Ring Seal is designed for high-performance sealing applications, providing reliable protection against leaks and contamination. Made from robust materials like Fluorinated Ethylene Propylene and Viton, it is ideal for use in demanding environments. With a Shore A hardness of 90 to 95, it ensures durability and longevity.

## General Specifications

Colour	Black
Hardness	Shore A 90 to 95
Product Type	O-Ring Seal
Sub Type	O-Ring

## Mechanical Specifications

Inside Diameter	33 mm
Material	Fluorinated Ethylene Propylene, Fluoroelastomer, Viton
Outside Diameter	38.24 mm
Thickness	2.62 mm

## Operation Environment Specifications

Maximum Operating Temperature	140 °C
Minimum Operating Temperature	-20 °C

## Approvals

Standards/Approvals	BS ISO 3601-1, AS 568, EC 1935:2004, FDA, ISO 14001:2015, ISO 45001:2015, ISO 9001:2015, LABS, TSCA, USP Class VI, WRAS
---------------------	---

