



## 900W 8mm ( 1/4" ) Premium Plunge & Fixed Base Router Combination

D26204K-QS

Full wave electronic speed control with feedback ensures the selected speed is maintained under any load for a consistent finish in all grades of timber, aluminium and plastics

Variable speed control 16,000 to 27,000 which enables the router bit to be optimised for application

Compact, light weight design that increase ease of use and user comfort  
Aluminium motor housing can be transitioned quickly to a fixed base attachment increasing the versatility of the machine

Plunge base incorporates fine tune rod for precise depth adjustment



Sound Pressure Uncertainty	3 dB(A)
----------------------------	---------

Sound Pressure	77 dB(A)
----------------	----------

Uncertainty K 1 (Vibration)	2.7 m/s <sup>2</sup>
-----------------------------	----------------------

Power Input	900W
-------------	------

Power Source	Corded
--------------	--------

No Load Speed	16000–27000 Rpm
---------------	-----------------