



AMPLIMITE


TE Internal #: 788800-1

TE Internal Description: 25 HTMSFL ASSY RA 318 (IN,BL)

D-Sub Receptacle Assembly: Right Angle, Shell Size 3, 2.77mm

[View on TE.com >](#)

Connectors > D-Shaped Connectors > D-Sub Receptacle Assembly: Right Angle, Shell Size 3, 2.77mm



Number of Positions: **25**

Connector & Housing Type: **Receptacle**

Connector System: **Board-to-Board**

Connector Mounting Type: **Board Mount**

Connector Shell Size: **3**

[All D-Sub Receptacle Assembly: Right Angle, Shell Size 3, 2.77mm \(47\)](#)

Features

Product Type Features

Shell Material Configuration	Front Metal Shell
Connector & Housing Type	Receptacle
Connector System	Board-to-Board
Connector Shell Size	3
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Positions	25
Number of Rows	2
PCB Mount Orientation	Right Angle

Body Features

Assembly Process Feature Material	Copper Alloy
Shell Plating Material	Tin over Copper
Mating Retention Feature Material	Zinc
Primary Product Color	Black
Connector Profile	Standard

Contact Features

	30 µin
--	--------

Contact Underplating Material	Nickel
Contact Mating Area Plating Material	Gold (Au)
Contact Base Material	Phosphor Bronze
PCB Contact Termination Area Plating Material	Tin-Lead
Contact Shape & Form	Round
Contact Current Rating (Max)	6 A
Contact Options	Installed

Termination Features

Termination Post & Tail Diameter	.63 mm[.025 in]
Termination Method to PCB	Through Hole - Solder
Termination Post & Tail Length	3.18 mm[.125 in]

Mechanical Attachment

	.125 in
Mating Retention Feature Plating Material	Clear Chromate
Mounting Feature Plating Material	Tin
Mounting Feature Material	Brass
Assembly Process Feature Plating Material	Tin-Lead over Nickel
Connector Mounting Type	Board Mount
PCB Mount Retention	With
PCB Mount Retention Type	Boardlock
Mating Retention	With
Mating Retention Type	Threaded Inserts

Housing Features

Housing Material	Thermoplastic
Shell Material	Carbon Steel
Centerline (Pitch)	2.74 mm[.108 in]

Dimensions

PCB Thickness (Recommended)	1.57 mm[.062 in]
Row-to-Row Spacing	2.84 mm[.112 in]

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application



Circuit Application

Signal

Industry Standards

UL Flammability Rating

UL 94V-0

Packaging Features

Packaging Quantity

65

Packaging Method

Bag

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU

Not Compliant

EU ELV Directive 2000/53/EC

Compliant with Exemptions

China RoHS 2 Directive MIIT Order No 32, 2016

Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JAN 2025 (247)

Candidate List Declared Against: JUNE 2024 (241)

SVHC > Threshold:

Pb (13% in Component Part)

Article Safe Usage Statements:

Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Not Low Halogen - contains Br or Cl > 900 ppm.

Solder Process Capability

Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-AM7-248H3
IDC D-Sub: Plug Assembly, Wire to Wire, Signal, 2.77 mm



TE Part # CAT-AM7-H3
IDC D-Sub: Plug Assembly, Low Profile, Signal, 2.77 mm

Customers Also Bought



TE Part #403289-000
CWT-3



TE Part #1-480698-9
02P UMNL PLUG HSG BLK



TE Part #827914-1
2P SHUNTSTECKER



TE Part #3-1393118-8
KUP-14D55-24=KU




TE Part #2-1393254-3
W91-X112-15=M6/M7/M9/W6/W7




TE Part #1393255-2
W93-X112-15=M6/M7/M9/W6/W7



TE Part #1445048-3
PANEL MT SNGL ROW HSG 3 POS



TE Part #1586024-5
5P S/R FH PLUG VAL-U-LOK V2



TE Part #5499922-4
A/L UNIV HDR 20P VERT LAT



TE Part #5787745-2
USB A R/A STAK ASSY THRU HOLE

Documents

Product Drawings

[25 HTMSFL ASSY RA 318 \(IN,BL\)](#)

English

CAD Files

[3D PDF](#)

English

[Customer View Model](#)

[ENG_CVM_788800-1_A.2d_dxf.zip](#)



English

Customer View Model

[ENG_CVM_788800-1_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_788800-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English

Agency Approvals

[UL Report](#)

English