


# NSYTRR44BL

## SPRING TERMINAL, FEED THROUGH, 4 POINTS, 4MM<sup>2</sup>, BLUE



### Main

Range	Linergy
Product name	Linergy TR
Product or component type	Terminal block
Device short name	TRR
Accessory / separate part category	Connection accessory
Terminal block type	Passthrough
Terminal block level	1
Mounting mode	Clip-on
Nominal cross section	4 mm <sup>2</sup>
Length	87 mm
Colour	Blue
Quantity per set	Set of 50

### Complementary

Width	6.2 mm
Height	36.5 mm
Connections - terminals	2 x spring terminal: downstream 2 x spring terminal: upstream
Number of connections	4
Connection position	Top
Number of measurement input	2
Cable cross section	0.08...4 Mm <sup>2</sup> , solid without cable end 0.08...4 Mm <sup>2</sup> , flexible without cable end 0.08...6 Mm <sup>2</sup> , solid with cable end 0.2...4 mm <sup>2</sup> , flexible with cable end
Wire stripping length	10 mm
Tool type	Connection: flat screwdriver Disconnection: flat screwdriver
[Ue] rated operational voltage	600 V CSA 800 V conforming to EN/IEC 60947-7-1 600 V cURus
[In] rated current	32 A conforming to EN/IEC 60947-7-1 30 A CSA 30 A cURus
Material	Polyamide 6/6: insulating case Copper alloy: connector and screw Copper alloy: commoning link Chromium-nickel steel: spring
Dielectric loss	0.01 at 1 MHz conforming to IEC 60250 0.01 at 1 MHz conforming to VDE 0303-T4
Dielectric constant	3.7 at 1 MHz
Resistivity	10000 MΩ.M conforming to IEC 60093 10000 MΩ.m conforming to VDE 0303-T30
Surface resistance	1000 GΩ conforming to IEC 60093 1000 GΩ conforming to VDE 0303-T30
Creep resistance	500 CTI (> 400 kV) conforming to IEC 60093 500 CTI (> 400 kV) conforming to VDE 0303-T30
Flame retardance	V0, thickness 0.8 mm conforming to UL 94
Net weight	13.4 g

Range compatibility	Prisma G Prisma P Prisma PH Prisma Pack Spacial Kaedra Pragma TeSys
Product compatibility	Spacial enclosures

## Environment

Product certifications	VDE ATEX DNV CURus EAC CSA GL LR IEC-Ex
Dielectric strength	1000 V conforming to IEC 60243-1
Ambient air temperature for operation	-40...130 °C conforming to IEC 60216-1 -40...130 °C conforming to VDE 0304-T21

## Packing Units

Package 1 Weight	13 g
Package 2 Weight	722 g
Package 3 Weight	3.966 kg

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Halogen content performance	Halogen free product

## Contractual warranty

Warranty	18 months
----------	-----------