




Visual Signals AUTOMOTIVE BEACONS

Automotive Rotating Beacons > R88 Series

Product overview

The R88 Series uses a parabolic reflector which, driven by an electric motor, revolves around a continuously illuminated lamp on the vertical axis of the beacon creating a powerful beam of light travelling through 360 degrees. Generally, this type of beacon has a greater degree of light output than

other models but this is off-set by the fact that the parabolic reflector only illuminates one give point at a time. The R88 is available as either a permanent fixed unit or with a magnetic base and vehicle lighter socket lead for temporary and occasional use. This is ideal for when the beacon is not required to be fixed permanently to the roof of the vehicle.



Features

- Continuously rated
- Choice of magnetic or fixed mounting options
- Worm drive system
- IP65

Material

- UV Stable Polycarbonate Lens
- Acetal Base with Neoprene Cover

Code No:	Voltage:	Light Source:	Current:
ROTATING MB (Magnetic Base)			
R88-34	12v Dc ---	H1 x 55w	4.70 A
R88-38	24v Dc ---	H1 x 70w	3.00 A
ROTATING SF (Fixed Base)			
R88-37	12v Dc ---	H1 x 55w	4.70 A
R88-39	24v Dc ---	H1 x 70w	3.00 A

ROTATING MB (Magnetic Base)

R88-34	12v Dc ---	H1 x 55w	4.70 A
R88-38	24v Dc ---	H1 x 70w	3.00 A

ROTATING SF (Fixed Base)

R88-37	12v Dc ---	H1 x 55w	4.70 A
R88-39	24v Dc ---	H1 x 70w	3.00 A



Kg 1.11 MB
0.67 SF

°C -25+55

IP 65

FPM 160±30

AUTOMOTIVE

APPROVED AND
CONFORMITIES



ADD THE FOLLOWING LENS CODES
TO THE PRODUCT WHEN ORDERING

01 **02** **03** **04** **05**