


# RMR-018 ◇ Unregulated Transformer

1W ◇ SMD ◇ 5kVAC Isolation

## FEATURES

- Small-sized isolation transformer
- SMD surface mount installation
- Isolation voltage: 5000VAC/1 minute
- Operating temperature: -40~125°C
- Maximum product dimensions: 19.9mm × 9.5mm × 7.6mm


## DIMENSIONS AND SCHEMATIC DIAGRAM [mm]



## PRODUCT MARKING

|         |               |
|---------|---------------|
| Pin1    | ○             |
| Marking | Company Logo  |
|         | Product Model |

## RECOMMENDED LAND PATTERN [mm]



**RMR-018** ♦ Unregulated Transformer

1W ♦ SMD ♦ 5kVAC Isolation

**BASIC CHARACTERISTIC** (measured @ TAMB= 25°C, nominal Input and full load after warm-up time unless otherwise stated)

| Properties               |                  | Test Conditions                           | Value    | Unit |
|--------------------------|------------------|-------------------------------------------|----------|------|
| Inductance               | L                | N2/10kHz/0.1V                             | 108 min. | μH   |
| Turns Ratio              | n                | N1:N2                                     | 2.56:1   |      |
| DC Resistance 1          | R <sub>DC1</sub> | N1/25°C                                   | 0.7 max. | Ω    |
| DC Resistance 2          | R <sub>DC2</sub> | N2/25°C                                   | 0.4 max. | Ω    |
| Voltage-μSecond          | ∫ <sub>Udt</sub> | N2/ bipolar waveform                      | 23       | Vμs  |
| Interwinding Capacitance | C <sub>WW</sub>  | PIN1-6 / 100kHz / 0.1V / 25°C             | 15 max.  | pF   |
| Leakage Inductance       | L <sub>S</sub>   | N2/100kHz/0.1V, all other terminals short | 0.5 max. | μH   |
| Isolation Test Voltage   | V <sub>T</sub>   | N1: N2/60s/1mA                            | 5000     | VAC  |
| Creepage Distance        |                  |                                           | 15.3     | mm   |

**GENERAL INFORMATION**

|                                                    |              |
|----------------------------------------------------|--------------|
| Operating Temperature (including temperature rise) | -40~125°C    |
| Storage Temperature                                | -40~125°C    |
| Storage Conditions (in original packaging)         | <40°C/<75%RH |
| Moisture Sensitivity Level (MSL)                   | 1            |
| Insulation Grade                                   | Basic        |

**MATERIAL CERTIFICATION**

| ITEM      | UL NO   |
|-----------|---------|
| 1 Case    | E150608 |
| 2 Wire    | E315265 |
| 3 Varnish | E314793 |
| 4 Glue    | E304477 |

**ENVIRONMENTAL COMPLIANCE**

|                |                                     |
|----------------|-------------------------------------|
| RoHS Approval  | Compliant [2011/65/EU&2015/863]     |
| REACH Approval | Conform or declared [(EC)1907/2006] |
| Halogen Free   | Conform [EN 14582:2016]             |

**TYPICAL APPLICATION**

| Parameter           |                     | Value | Unit |
|---------------------|---------------------|-------|------|
| Input Voltage       | V <sub>IN</sub>     | 5     | VDC  |
| Output Voltage 1    | V <sub>OUT1</sub>   | 12    | VDC  |
| Output Current 1    | I <sub>OUT1</sub>   | 83    | mA   |
| Switching Frequency | f <sub>switch</sub> | 340   | kHz  |

Input: N2


Output 1: N1

Table and graph show a typical application. Values may vary by application.

# RMR-018 ♦ Unregulated Transformer


1W ♦ SMD ♦ 5kVAC Isolation

## REFERENCE CIRCUIT DIAGRAM




Typical Curve:

Typical Efficiency vs. Output Current



Typical Output Voltage vs. Output Current





# RMR-018 ◇ Unregulated Transformer


1W ◇ SMD ◇ 5kVAC Isolation

## PACKAGING SPECIFICATION - TAPE & REEL [mm]

| ITRM | W              | A0             | B0             | K0             | K1             | P              | F              | E              | S0             | D0             | P0             | P2             | T              |
|------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|
| DIM  | 44.00          | 9.30           | 20.30          | 7.00           | --             | 16.00          | 20.20          | 1.75           | 40.40          | 1.50           | 4.00           | 2.00           | 0.40           |
| TOLE | +0.30<br>-0.30 | +0.15<br>-0.15 | +0.15<br>-0.15 | +0.10<br>-0.10 | +0.10<br>-0.10 | +0.10<br>-0.10 | +0.10<br>-0.10 | +0.10<br>-0.10 | +0.10<br>-0.10 | +0.10<br>-0.00 | +0.10<br>-0.10 | +0.15<br>-0.15 | +0.05<br>-0.05 |




|               |      |      |      |      |      |
|---------------|------|------|------|------|------|
|               |      |      |      | ✓    |      |
| SPEC          | 16   | 24   | 32   | 44   | 56   |
| DIM A'' ± 0.5 | 16.5 | 24.5 | 32.5 | 44.5 | 56.5 |
| DIM B'' ± 0.3 | 2.10 | 2.10 | 2.10 | 2.10 | 2.10 |
| DIM C'' ± 0.5 | 100  | 100  | 100  | 100  | 100  |



**RMR-018** ◇ Unregulated Transformer

1W ◇ SMD ◇ 5kVAC Isolation

**REFLOW SOLDERING**

| Profile Feature                                      |              | Value                                           |
|------------------------------------------------------|--------------|-------------------------------------------------|
| Preheat Temperature Min                              | $T_{s \min}$ | 150°C                                           |
| Preheat Temperature Max                              | $T_{s \max}$ | 200°C                                           |
| Preheat Time $t_s$ from $T_{s \min}$ to $T_{s \max}$ | $t_s$        | 100 seconds                                     |
| Ramp-up Rate ( $T_L$ to $T_p$ )                      |              | 3°C/second max.                                 |
| Liquidous Temperature                                | $T_L$        | 217°C                                           |
| Time $t_L$ maintained above $T_L$                    | $t_L$        | 100 seconds                                     |
| Peak package body temperature                        | $T_p$        | $T_p \leq T_c$ , see Table below                |
| Time within 5°C of actual peak temperature           | $t_p$        | 30 seconds                                      |
| Ramp-down Rate ( $T_p$ to $T_L$ )                    |              | 6°C/second max.                                 |
| Time 25°C to peak temperature                        |              | 5 minutes max.                                  |
| Reflow soldering temperature                         |              | Peak Temperature $\leq 250^\circ\text{C}$ (10s) |
| Reflow Soldering Cycles                              |              | Recommended $\leq 2$ Cycles                     |

Refer to IPC/JEDEC J-STD-020F

**PACKAGE CLASSIFICATION REFLOW TEMPERATURE ( $T_c$ )**

| Properties                                           | Volume mm <sup>3</sup> <350 | Volume mm <sup>3</sup> 350-2000 | Volume mm <sup>3</sup> >2000 |
|------------------------------------------------------|-----------------------------|---------------------------------|------------------------------|
| PB-Free Assembly   Package Thickness < 1.6 mm        | 260°C                       | 260°C                           | 260°C                        |
| PB-Free Assembly   Package Thickness 1.6 mm - 2.5 mm | 260°C                       | 250°C                           | 245°C                        |
| PB-Free Assembly   Package Thickness > 2.5 mm        | 250°C                       | 245°C                           | 245°C                        |

Refer to IPC/JEDEC J-STD-020F

**RMR-018** ♦ Unregulated Transformer

1W ♦ SMD ♦ 5kVAC Isolation

**ORDER INFORMATION**

| Order Code      | Marking Code* | Weight (g/pcs) | Package Type         | Quantity (pcs/Reel) |
|-----------------|---------------|----------------|----------------------|---------------------|
| RMR-018-F5AS-R  | RMR-018       | 1.5g           | Tape & Reel          | 500pcs              |
| RMR-018-F5AS-CT | RMR-018       | 1.5g           | Moisture Barrier Bag | 5pcs                |

\*Marking Code

RMR-018 — Product Code

The product information and specifications may be subject to changes even without prior written notice. The product has been designed for various applications; its suitability lies in the responsibility of each customer. The products are not authorized for use in safety-critical applications without RECOM's explicit written consent. A safety-critical application is an application where a failure may reasonably be expected to endanger or cause loss of life, inflict bodily harm or damage property. The applicant shall indemnify and hold harmless RECOM, its affiliated companies and its representatives against any damage claims in connection with the unauthorized use of RECOM products in such safety-critical applications.