



739-8458 Data Sheet

ENGLISH

RS stock number : 739-8458
Type of tool : Mini 3" Air Angle Cutter
Power source : Compressed air
Maximum permissible operating pressure : 90 psi (6.2 bar)
Recommended operating pressure : 90 psi (6.2 bar)

739-8458

Mini 3" Air Angle Cutter

Technical Data

Features

Palm size cutter allows the operator to reach small areas
Compact and lightweight design allows maximum operator control and performance
Rear exhaust to keep airflow away from work area
High power motor for consistent performance

Specifications

Disc Size: 3" / 75mm
Free Speed: 16,500RPM
Weight: 0.37kgs / 0.81lbs
Length: 4.33" / 110mm
Min Hose Size: 3/16
Air inlet thread: 1/4"
Sound: 81dBA
Vibration: 4.8m/s²
Ave Air Consumption: 1.68cfm / 48 l/min
Recommended lubrications: 10 Weight SAE Oil



Declaration of Conformity

We	RS Components Ltd
declare under our sole responsibility that the	739-8458 – Mini 3" Air Angle Cutter
conforms with the directive and the standards	2006/42/EEC EN 792-6 ISO 28927