

40VMax Disc Cutter XGT®

CE004G

305 mm

Model CE004G is a cordless disc cutter with a blade diameter of 305 mm and powered by a 40Vmax XGT Li-Ion battery.

Model CE004G with a blade diameter of 305mm offers a significant weight reduction compared to engine models, making this machine remarkably lightweight. Feature and benefits: Active Feedback sensing Technology (AFT), Water supply kit can be connected, Electric brake, Lock-off button, Rotatable guard can be adjusted to suit working posture.



Technical specifications

Voltage XGT	✓
Nominal Battery Voltage	40 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Brushless Motor	✓
No load speed	5000 min ⁻¹
Max. Depth of Cut	121 mm
Bore Size (Arbor Diameter)	20 / 25,4 mm
Disc Diameter	305 mm
Electronic brake	✓
Vibration Level, Concrete Cutting	3,8 / ≤ 2,5 m/s ²
Vibration Uncertainty (K Factor), Concrete Cutting	1,5 m/s ²
Sound Power Level (L _{WA})	110 dB(A)
Sound Pressure Level (L _{pA})	99 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)

User benefits

- Lightweight & high power
- Active Feedback sensing Technology (AFT) stops the engine if the rotation suddenly stops
- Electric brake for maximum productivity and increased operator safety
- Lock-off button prevents accidental startup
- LED job light for easy operation in the dark

Link to product - www.makita.uk.com



Related products

Other

User manual

Parts drawing