

FEATURES

- **Polyacrylic material:** Offers excellent durability and resistance to wear
- **Maximum operating pressure of 2000 kPa:** Suitable for high-pressure applications
- **Maximum operating temperature of 200 °C:** Performs well in high-temperature environments
- **Rotary speed of 10 m/s:** Efficient in dynamic sealing applications
- **3.2 mm section:** Provides a compact and effective sealing solution

RS PRO 8m Polyacrylic Gland Packing, 3.2mm Section

RS Stock No: 606-578



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO gland packing is designed for sealing applications in pumps and valves, providing reliable performance in high-pressure and high-temperature environments. Made from durable polyacrylic material, it ensures effective sealing and longevity, making it ideal for industrial use.

General Specifications

Maximum Operating Pressure	2000 kPa
Product Type	Gland & Valve Packing
Rotary Speed	10 m/s
Section	3.2 mm
Sub Type	Gland Packing

Mechanical Specifications

Length	8 m
Material	Polyacrylic

Operation Environment Specifications

Maximum Operating Temperature	200 °C
-------------------------------	--------

Approvals

Standards/Approvals	ANSI-ESD S20.20:2021, RoHS
---------------------	----------------------------