

FEATURES

- **LED Bulb Type:** Provides energy-efficient and long-lasting illumination
- **Current Consumption of 0.04 A:** Ensures low power usage, reducing operational costs
- **AC Current Type:** Compatible with standard AC power supplies
- **Grey ABS Housing:** Offers durability and resistance to environmental factors
- **IP43 Rating:** Protects against solid objects over 1mm and water spray
- **Orange Lens Colour:** Enhances visibility for clear signalling
- **Steady Light Effect:** Provides consistent visual alerts
- **Operating Temperature Range -20 °C to 50 °C:** Suitable for a wide range of environments
- **Sound Level 88-92 dB:** Delivers clear audible alerts
- **Screw Mount Type:** Allows easy and secure installation

RS PRO LED Horn-Beacon Combination, IP43
Grey Housing

RS Stock No: 658-301



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO Horn-Beacon Combination is designed to provide both visual and audible alerts in industrial environments. It combines a steady LED light with a powerful sounder, making it ideal for signalling and warning applications. The unit is housed in a durable ABS enclosure, ensuring reliability and longevity.

General Specifications

Bulb Type	LED
Housing Colour	Grey
Lens Colour	Orange
Light Effect	Steady
Mount Type	Screw
Number of Tones	1
Product Type	Horn-Beacon Combination
Sounder Type	Sounder Beacon

Electrical Specifications

Current Consumption	0.04 A
Current Type	AC
Maximum Supply Voltage	240 V ac

Mechanical Specifications

Housing Material	ABS
------------------	-----

Protection Category

IP Rating	IP43
-----------	------

Operation Environment Specifications

Maximum Operating Temperature	50 °C
Minimum Operating Temperature	-20 °C

Measurement Specifications

Maximum Sound Level	92 dB
Minimum Sound Level	88 dB

Approvals

Standards/Approvals	CE, EAC
---------------------	---------