


SMF550



Magnetic-inductive flow meter

SMG65KGFFRKG/UST



Product characteristics				
Measuring range	20...2000 l/min	1.2...120 m³/h	5.28...528.4 gpm	0.33...32.8 ft/s
Nominal diameter	DN65 (2 1/2")			
Process connection	ifm-specific device flange			
Application				
Special feature	Gold-plated contacts			
Application	food and beverage industry			
Media	conductive liquids; water; hydrous media			
Note on media	food products such as beer, milk, fruit juices, soft drinks, ketchup, yoghurt, yoghurt toppings, ice cream			
	conductivity: ≥ 5 µS/cm			
Medium temperature	[°C]	-20...150		
Min. bursting pressure	37.5 bar	543.75 psi	3.75 MPa	
Pressure rating	25 bar	362.5 psi	2.5 MPa	
Electrical data				
Operating voltage	[V]	18...32 DC		
Current consumption	[mA]	250; (24V)		
Protection class		III		
Reverse polarity protection		yes		
Power-on delay time	[s]	< 5		



Magnetic-inductive flow meter

SMG65KGFFRKG/UST

Measuring principle	magnetic-inductive			
Inputs / outputs				
Total number of inputs and outputs	2			
Inputs				
Inputs	OUT2		external totaliser reset	
Outputs				
Total number of outputs	2			
Output signal	OUT1	pulse signal; totaliser switching signal; diagnostic signal; IO-Link		
	OUT2	analogue signal; pulse signal; totaliser switching signal; diagnostic signal		
Electrical design	PNP/NPN			
Pulse output	flow rate meter			
Short-circuit protection	yes			
Type of short-circuit protection	pulsed			
Overload protection	yes			
Analogue				
Number of analogue outputs	1			
Analogue current output [mA]	4...20; (skalierbar)			
Max. load [Ω]	500			
Resolution of analogue output	0.38 µA			
Digital				
Number of digital outputs	2			
Max. voltage drop switching output DC [V]	2			
Permanent current rating of switching output DC [mA]	100			
Switching frequency DC [Hz]	0...10000			
Measuring/setting range				
Measuring range	20...2000 l/min	1.2...120 m³/h	5.28...528.4 gpm	0.33...32.8 ft/s
Note on factory setting	0...30,0 m³/h			
Analogue start point ASP	-2000...1600 l/min	-120...96 m³/h	-528.4...422.72 gpm	-32.8...26.24 ft/s
Analogue end point AEP	-1600...2000 l/min	-96...120 m³/h	-422.72...528.4 gpm	-26.24...32.8 ft/s
Low flow cut-off LFC	0...1600 l/min	0...96 m³/h	0...422.72 gpm	0...26.24 ft/s
Pulse length [s]	0.00005...2			
Pulse value	0.001...99990000 l			
Temperature monitoring				
Measuring range	-20...150 °C		-4...302 °F	
Analogue start point	-20...116 °C		-4...240.8 °F	
Analogue end point	14...150 °C		57.2...302 °F	
Conductivity monitoring				
Measuring range [µS/cm]	100...100000			
Resolution [µS/cm]	1			
Analogue start point [µS/cm]	0...80000			



Magnetic-inductive flow meter

SMG65KGFFRKG/UST

Analogue end point	[μS/cm]	20000...100000
--------------------	---------	----------------

Accuracy / deviations

Volumetric flow monitoring		
Accuracy (under reference conditions)	with optional factory calibration (availability is being planned)	± (0,2 % MW + 2 mm/s)
	standard	± (0,5 % MW + 1,5 mm/s)
Repeatability	0,1% MW	
Temperature monitoring		
Accuracy	[K]	± 1
Repeatability	[K]	± 0,5
Conductivity monitoring		
Accuracy (in the measuring range)	in the range of 100...20000 µS/cm	±10% MW
	in the range of 20000...100000 µS/cm	±20% MW
Repeatability	± 5% MW	

Response times

Volumetric flow monitoring		
Response time	[s]	< 0.3
Damping process value dAP	[s]	0...5
Temperature monitoring		
Response time	[s]	< 3; (flow velocity: ≥ 0,5m/s)
Conductivity monitoring		
Response time	[s]	< 2

Software / programming

Diagnostic functions	direction of flow detection; liquid detection
----------------------	---

Interfaces

Communication interface	IO-Link	
Transmission type	COM3 (230,4 kBaud)	
IO-Link revision	1.1.3	
SDCI standard	IEC 61131-9	
Profiles	Common - I&D	Identification and Diagnosis
	Smart Sensor - SSP 4.3.4	Measuring and Switching Sensor, floating point, 4 channel
SIO mode	yes	
Required master port type	A	
Process data analogue	6	
Process data binary	8	
Min. process cycle time	[ms]	1.9
IO-Link process data (cyclical)	function	bit length
	totaliser	32
	flow	32
	temperature	32
	conductivity	32
	status	4
	binary switching information	8

SMF550



Magnetic-inductive flow meter

SMG65KGFFRKG/UST

IO-Link functions (acyclical)	direction of flow detection; totaliser; memory; operating hours counter; internal temperature; simulation function	
Supported DeviceIDs	Type of operation default	DeviceID 1797
Operating conditions		
Ambient temperature	-20...65 °C	-4...149 °F
Storage temperature	-20...80 °C	-4...176 °F
Protection	IP 67; IP 69	
Tests / approvals		
EMC	DIN 61326-1	
Shock resistance	DIN IEC 68-2-27	20 g (18ms)
Vibration resistance	DIN IEC 68-2-6	5 g (10...2000Hz)
MTTF [years]	82	
UL approval	UL approval no.	I032
Pressure Equipment Directive	Sound engineering practice; can be used for group 2 fluids; group 1 fluids on request	
Mechanical data		
Weight [g]	6979	
Inlet pipe length	5 x DN	
Outlet pipe length	2 x DN	
Materials	housing: stainless steel (316L/1.4404); flange: stainless steel (304/1.4301); electronics fixture: stainless steel (304/1.4301); electronics: stainless steel (316L/1.4404); LED ring: PP	
Materials (wetted parts)	Pipe section: PFA; electrodes: stainless steel (316L/1.4435)	
Nominal diameter	DN65 (2 1/2")	
Process connection	ifm-specific device flange	
Surface characteristics Ra/Rz of the wetted parts	≤ 0.4 µm	
Displays / operating elements		
Display	operating status	LED ring, three-colour
Factory setting	m³/h; °C; µS/cm	
Remarks		
Remarks	MW = measured value	
	MEW = Final value of the measuring range	
	pulse and totaliser signal are only available for one of the two outputs	
	reference conditions (1/2): water (free of gas bubbles), 15...35 °C, process connection: DIN32676 series A, pipe standard suitable for process connection	
	reference conditions (2/2): inlet pipe length 10xDN, outlet pipe length 5xDN, device settling time: 30 minutes, device orientation: horizontal, display orientation: up	
Pack quantity	1 pcs.	

SMF550



Magnetic-inductive flow meter


SMG65KGFFRKG/UST

Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated



Connection



Electrical connection - plug

1	L+	
2	OUT2	MP2, DO, AO, reset
3	L-	
4	OUT1	MP1, DO, IO-Link

AO: analogue output; DO: digital output; MP: multi-function connection